



Rev	AWO #	Description	Date	Appr
-		RELEASED	12/08/10	



APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT

Ø.075 [1.90]



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-2

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250V AC,DC

Current rating: 7A AC,DC

Contact resistance: 10 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Temperature Rating:

Anti-static plastic bags

Environmental:

Lead free, RoHS compliant

Recommended soldering temp: 235°C for 5 seconds

Positions: 2 thru 10
A = .200 [5.08] x No. of Positions
B = .200 [5.08] x No. of Spaces

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

.200 [5.08] POWER HEADER, STRAIGHT

TITLE

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES Holes
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DATE

DRAWN DY 12/08/10

CHECKED

APPROVED

SIZE PART NO.

X

LHF-XX-SA2

REF: S00099T

SCALE: NTS

SHEET 1 OF 1