


Dust proof with sharp operational feel suitable for general purpose.



■ Typical Specifications

Items	Specifications
Rating (max.)	50mA 12V DC
Rating (min.)	10μA 1V DC
Initial contact resistance	100mΩ max.
Travel (mm)	0.25

■ Product Line

Toppush Type

Product No.	Operating force	Operating direction	Operating life (5mA 5V DC)	Stem color	Stem height	Minimum order unit (pcs.)		Drawing No.
						Japan	Export	
SKQJAAA010	0.98N	Toppush	1,000,000cycles	Black	h=5mm	1,000	1,000	1
SKQJABA010	1.57N		500,000cycles	Dark gray				
SKQJADA010	0.98N		1,000,000cycles	Black	h=7mm			
SKQJAEA010	1.57N		500,000cycles	Dark gray				
SKQJAJA010	0.98N		200,000cycles	Black	h=9.5mm			
SKQJAKA010	1.57N			Dark gray				

Sidepush Type

Product No.	Operating force	Operating direction	Operating life (5mA 5V DC)	Stem color	Minimum order unit (pcs.)		Drawing No.
					Japan	Export	
SKQJLAA010	0.98N	Sidepush	1,000,000 cycles	Black	1,000	1,000	2
SKQJLBA010	1.57N		500,000cycles	Dark gray			

■ Packing Specifications

Bulk

Number of packages (pcs.)		Export package measurements (mm)
1 case / Japan	1 case / export packing	
10,000	30,000	309 × 476 × 347

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line Package Type

TACT Switch™

Sharp Feeling

Soft Feeling

Snap-in Type

Surface Mount Type

Radial Type

Dimensions

Unit:mm

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™





Sharp
Feeling

Soft
Feeling

Snap-in
Type

Surface
Mount Type


Radial
Type

No.	Photo	Style	PC board mounting hole dimensions (Viewed from switch mounting face)								
1		 <table border="1" data-bbox="871 360 1098 573"> <thead> <tr> <th>h</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>5</td> <td>3.5</td> </tr> <tr> <td>7</td> <td>3.3</td> </tr> <tr> <td>9.5</td> <td>3</td> </tr> </tbody> </table>	h	A	5	3.5	7	3.3	9.5	3	
h	A										
5	3.5										
7	3.3										
9.5	3										
2											

Note

Please use 1.6mm thick PC boards.

Circuit Diagram



List of Varieties

Type		Sharp Feeling Type										
		Snap-in										
Series		SKHR	SKHL	SKHH	SKHW	SKQJ	SKQB	SKQE	SKHC	SKHL	SKHH	
Detector	Photo											
Push	Features	—	—	—	—	—	—	Long Life	—	—	—	
Slide	Water-proof	—	—	—	○	—	●	—	—	—	—	
Rotary	Dust-proof	—	—	—	●	●	●	●	—	—	—	
Encoders	Operating direction	Top push	●	●	●	●	●	●	●	—	—	
Power		Side push	—	—	—	—	—	—	—	●	●	
Dual-in-line Package Type	Dimensions (mm)	W	□ 4.5	6	□ 6	□ 6.6	□ 10	□ 12	7.3	7.5	7.22	7.85
		D		3.5								
		H	3.8	4.3	5	5	4.3	7.4				
TACT Switch™	Operation force coverage	~1N	↕	↕	↕	↕	↕	↕	↕	↕	↕	
		1N~2N	↕	↕	↕	↕	↕	↕	↕	↕	↕	
		2N~3N	↕	↕	↕	↕	↕	↕	↕	↕	↕	
		3N~4N	↕	↕	↕	↕	↕	↕	↕	↕	↕	
		4N~5N	↕	↕	↕	↕	↕	↕	↕	↕	↕	
Travel (mm)		0.25			0.3	0.25	0.3			0.25		
Ground terminal		—	—	●	—	—	—	—	—	●	●	
Operating temperature range		-30°C to +85°C	-40°C to +90°C			-30°C to +85°C	-40°C to +90°C			-40°C to +85°C	-40°C to +90°C	
Automotive use		—	●	●	—	—	—	—	—	—	—	
Life Cycle												
Rating (max.) (Resistive load)		50mA 12V DC										
Rating (min.) (Resistive load)		10μA 1V DC										
Electrical performance	Insulation resistance	100M Ω min. 100V DC for 1min.										
	Voltage proof	250V AC for 1min.										
Durability	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z for 2hours respectively										
	Lifetime	Shall be in accordance with individual specifications.										
Environmental performance	Cold	-40 ± 2°C for 96h				-30 ± 2°C for 96h	-40 ± 2°C for 96h					
	Dry heat	90 ± 2°C for 96h				-80 ± 2°C for 96h	90 ± 2°C for 96h					
	Damp heat	60 ± 2°C, 90 to 95%RH for 96h				60 ± 2°C, 90 to 95%RH for 1000h	60 ± 2°C, 90 to 95%RH for 96h					
Page		229	230	232	236	237	239	241	243	230	232	

W : Width. The most outer dimension excluding terminal portion.
 D : Depth. The most outer dimension excluding terminal portion.
 H : Height. The minimum dimension if there are variances.

- TACT Switch™ Soldering Conditions 288
- TACT Switch™ Cautions 289

Notes

1. The automotive operating temperature range to be individually discussed upon request.
2. ● indicates applicability to all products in the series, while ○ indicates applicability to some products in the series.

■ List of Varieties

Type		Sharp Feeling Type											
		Snap-in		Surface Mount									
Series		SKQJ	SKQB	SKSH	SKRW	SKRM	SKRB	SKRR	SKQG	SKTC	SKSK	SKSD	
Photo													
Features		—	—	Low-profile			Low-profile and long life	Low-profile	Double action				
Water-proof		—	●	—	○	—	—	—	—	●	—	—	
Dust-proof		●	●	○	○	○	○	○	○	●	—	—	
Operating direction	Toppush	—	—	●	●	●	●	●	●	●	●	●	
	Sidepush	●	●	—	—	—	—	—	—	—	—	—	
Dimensions (mm)	W	7.5	11.5	3.3	□3.7	□4.5	□4.8	7.5	□5.2	3.4	3.5	4.1	
	D	7.85	11.9	2.9				7		2.2	3.2	3.9	
	H	7.3	11.3	0.35		0.4	0.55	0.6	0.8	0.62	0.6		
Operation force coverage	~1N	↕	↕	↕	↕	↕	↕	↕	↕	↕	※	↕	
	1N~2N												
	2N~3N												
	3N~4N												
4N~5N													
Travel (mm)		0.25	0.3	0.15		0.15/0.2		0.25		※			
Ground terminal		—	—	—	—	—	—	—	—	●	●		
Operating temperature range		-20°C to +70°C	-40°C to +90°C	-30°C to +85°C								—	
Automotive use		—	●	—	—	—	●	—	○	—	—	—	
Life Cycle													
Rating (max.) (Resistive load)		50mA 12V DC											
Rating (min.) (Resistive load)		10μA 1V DC											
Electrical performance	Insulation resistance	100MΩ min. 100V DC for 1min.											
	Voltage proof	250V AC for 1min.	100V AC for 1min.	250V AC for 1min.	100V AC for 1min.	250V AC for 1min.	100V AC for 1min.	250V AC for 1min.	100V AC for 1min.	250V AC for 1min.	100V AC for 1min.		
Durability	Vibration	10 to 55 to 10Hz/min., the amplitude is 1.5mm for all the frequencies, in the 3 direction of X, Y and Z for 2hours respectively											
	Lifetime	Shall be in accordance with individual specifications.											
Environmental performance	Cold	-30 ± 2°C for 96h	-40 ± 2°C for 96h	-30 ± 2°C for 96h									
	Dry heat	80 ± 2°C for 96h	90 ± 2°C for 96h	80 ± 2°C for 96h									
	Damp heat	60 ± 2°C, 90 to 95%RH for 96h	60 ± 2°C, 90 to 95%RH for 1000h	60 ± 2°C, 90 to 95%RH for 96h									
Page		237	239	245	246	247	248	249	250	252	253	254	

W : Width. The most outer dimension excluding terminal portion.
D : Depth. The most outer dimension excluding terminal portion.
H : Height. The minimum dimension if there are variances.

● TACT Switch™ Soldering Conditions 288

● TACT Switch™ Cautions 289

Notes

1. The automotive operating temperature range to be individually discussed upon request.
2. ● indicates applicability to all products in the series, while ○ indicates applicability to some products in the series.
3. ※ See the relevant pages for respective product descriptions

Detector

Push

Slide

Rotary

Encoders

Power

Dual-in-line
Package Type

TACT Switch™

Sharp
Feeling

Soft
Feeling

Snap-in
Type

Surface
Mount Type

Radial
Type


TACT Switch™ Soldering Conditions

Condition for Reflow

Available for Surface Mount Type.

1. Heating method: Double heating method with infrared heater.
2. Temperature measurement: Thermocouple 0.1 to 0.2 φ CA (K) or CC (T) at solder joints (copper foil surface).
A heat resistive tape should be used to fix thermocouple.

3. Temperature profile



Notes

1. The above temperature shall be measured of the top of switch. There are cases where the PC board's temperature greatly differs from that of the switch, depending on the material, size, thickness of PC boards and others. The above-stated conditions shall also apply to switch surface temperatures.
2. Soldering conditions differ depending on reflow soldering machines. Prior verification of soldering condition is highly recommended.

Conditions for Auto-dip

Available for Snap-in Type and Radial Type

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

SKHH、SKPD Series

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 110°C max.
Preheating time	60s max.
Soldering temperature	260°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

SKQJ、SKQK、SKEG Series

Items	Condition
Flux built-up	Mounting surface should not be exposed to flux
Preheating temperature	Ambient temperature of the soldered surface of PC board. 100°C max.
Preheating time	45s max.
Soldering temperature	255°C max.
Duration of immersion	5s max.
Number of soldering	2times max.

Notes

1. Consult with us for availability of TACT Switch™ washing.
2. Prevent flux penetration from the top side of the TACT Switch™.
3. Switch terminals and a PC board should not be coated with flux prior to soldering.
4. The second soldering should be done after the switch is stable with normal temperature.
5. Use the flux with a specific gravity of min 0.81.
(EC-19S-8 by TAMURA Corporation, or equivalents.)

Manual Soldering (Except SKRT Series)

Items	Condition
Soldering temperature	350°C max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

SKHH、SKHW、SKRG、SKPD Series

Items	Condition
Soldering temperature	360°C max.
Duration of soldering	3s max.
Capacity of soldering iron	60W max.

SKQJ、SKQK、SKEG Series

Items	Condition
Soldering temperature	350°C max.
Duration of soldering	3s max.
Capacity of soldering iron	20W max.

Detector
Push
Slide
Rotary
Encoders
Power
Dual-in-line Package Type
TACT Switch™

Sharp Feeling
Soft Feeling
Snap-in Type
Surface Mount Type
Radial Type