




SPECIFICATIONS

Current Rating: 3AMP
 Contact Resistance: 20mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstand Voltage: 1000V AC/minute
 Operation Temperature: -40 degree up +105 degree

Contact: Brass
 plating: Au or Sn Over 50u" Ni
 Insulator: High Temperature Thermoplastic
 UL94V-0 Rated
 Standard: PBT+30%G.F



Recommended PCB Layout

Box Header:
2.54mm Pitch

Housing Color
0: Grey
1: Black

No of Positions:
06: 6 positions
:
64: 64 positions

Plating Options:
A1: Flash Gold
A2: 15u"/0.4um Gold
A3: 30u"/0.8um Gold
SN: Tin

Termination:
S1: Straight THT
R1: Right Angled THT

EU: RoHS Compliant
C: Fixed Index

Variation Code:
00: Standard

T821 X XX XX R1 00 C EU



TOLERANCE (mm)	APPROVALS	DATE	TITLE	AMPHENOL Amphenol European Design Center	
X. ±0.3	DRAWN Roger	12/Jun/2006	Box header, DIP 2.54mm, R/A	Scale N.A.	Sheet 1 of 1
X.X ±0.2	CHECKED Rob K.	13/Jun/2006			
X.XX ±0.15	APPROVED Rob K.	14/Jun/2006			
UNLESS OTHERWISE SPECIFIED	UNIT:	mm	SIZE: A4	DRAWING N° T821X XX XX R100CEU	REV. A