Automotive Electronics **Product Information Surface Mount Piezoresistive Silicon Absolute Pressure Sensor 60...115 kPa**



preliminary



Introduction

Bosch is the world market leader for pressure sensors in automotive applications. The SMD08x are a new family of a wide range of micromachined pressure sensors. They are one of the first pressure sensors for barometric air pressure which comes in an SMD package. It is easy to equip in standard assembly lines.



Customer benefits:

- Pressure range: 60...115 kPa
- Custom specific ranges upon request
- On-chip calibration
- Ratiometric analog output
- Calibrated transfer function
- Temperature compensated
- Surface mount package
- ESD-protection
- Robust bipolar technology
- Fast analog technology
- Short circuit protected
- Inverse polarity protected up to 300 mA supply current
- OBD capability due to high driver output

Function

The SMD08x are high precision barometric pressure sensors for automotive applications. The mess principle is based on piezoresistive technology. With this technology we realized a very robust design and a high accuracy. To reach the cost targets the SMD085 is packaged in a SMD8 Housing. The main application for this device is the barometric air pressure measurement in diesel or gasoline engine management control Units.

The SMD08x schematics consist on an integrated sensing element, a logic control unit, a temperature compensation circuit as well as offset compensation circuit. The Output Voltage will be between 0.3V and 4.8V for a pressure range between 60 kPa and 115 kPa.

Due to the full integrated concept no additional external circuits are necessary. The Bipolar technology of the integrated signal condition circuit guarantees a high ESD protection.



The output circuit is protected against short circuit to Vdd, GND and Vdd,max.

The sensor is protected against inverse polarity up to supply current of 300 mA (the sensor shows diode characteristic, therefore a current limitation is necessary.

The sensor is protected against ESD up to 2 KV human body model and 200 V machine model.

Transfer function



Characteristics

Parameter	Symbol	Value			Upit
		min	typ	max	Unit
Operating Temperature	Та	-40		130	°C
Minimum rated pressure	Pabs,min	601			kPa
Maximum rated pressure	Pabs,max			115	kPa
Output voltage at pabs,min	Vout,min	0,25	0,3	0,35	V
Output voltage at pabs,max	Vout,min	4,75	4,8	4,85	V
Overall accuracy	Acc			1.5	kPa
Supply voltage	VDD	4.75	5.0	5.25	V
Supply current	lin			12.5	mA
Output current					
Sink	lL .	1.0			mA
Source	l.	0.5			mA

1 SMDx88: 50kPa

Contact

Robert Bosch GmbH Sales Semiconductors Postbox 13 42 72703 Reutlingen Germany Tel.: +49 7121 35-2179 Fax: +49 7121 35-2170 Robert Bosch Corporation Component Sales 38000 Hills Tech Drive Farmington Hills, MI 48331 USA Tel.: +1 248 876-7441 Fax: +1 248 848-2818 Robert Bosch K.K. Component Sales 9-1, Ushikubo 3-chome Tsuzuki-ku, Yokohama 224 Japan Tel.: +81 45 9 12-83 01

Fax: +81 45 9 12-95 73

E-Mail: bosch.semiconductors@de.bosch.com

Internet: www.bosch-semiconductors.de

© 08/2006 All rights reserved by Robert Bosch GmbH including the right to file industrial property rights Robert Bosch GmbH retains the sole powers of distribution, such as reproduction, copying and distribution. For any use of products outside the released application, specified environments or installation conditions no warranty shall apply and Bosch shall not be liable for such products or any damage caused by such products.