



Catalog Number: THT-51-426-10

Thermal Transfer Printable Labels

Specifications

Application(s): Circuit Board & Component ID, SMT - Top/Bottom, Through Hole - Bottom, Through Hole - Top

Size: 1.000" W x 0.250" H (25.400 mm W x 6.350 mm H)

Printable Area: 1.000" W x 0.250" H (25.400 mm W x 6.350 mm H)

Web Width: 3.350" (85.09 mm)

Label Type/Style: Label

Vertical Repeat: 0.375" (9.53 mm)

Horizontal Repeat: 1.075" (27.31 mm)

Color: Amber

Finish: Matte

Qty Per Row: 3

Material Type: Polyimide

Material Description: High Temperature Polyimide

Recommended Ribbon Series: 4300

Suggested Ribbon Part#: R4300

After Process: Yes, this material will work with this application

Printer Compatibility: BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300X-Plus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, Brady IP, Tagus T200, Tagus T300, Thermal Transfer Printers

Surface Mount Technology: Yes, this material will work with this application

Through Hole Technology: Top: Yes, Bottom: Yes

Special Properties: Withstands extremely high temperatures

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 10,000/Roll