




▶ Visit us at [Transcat.com](http://Transcat.com)!

35 Vantage Point Drive // Rochester, NY 14624 // Call 1.800.800.5001

▶ **WIRE AND CABLE MARKERS — PERMASLEEVE™ SLEEVES**


These full circle heat-shrink sleeves are the ultimate in marker durability, permanence and aesthetic appearance. Fast-shrink rate saves time & cost during installation. Available as individual 1-inch long markers or cut-to-length continuous supply.

- ▶ **B-342 Heat Shrink Polyolefin material, 3-to-1 shrink ratio, self-extinguishing, meets material & physical properties requirements of MIL-DTL-23053/5C class 1, MIL-M-81531, MIL-STD-202F, method 215 and UL 224. Temp Range: -67°F to 275°F (-55°C to 135°C).**



Wire Gauge*	Wire Diameter Range	Diagram	Part Number	Labels per Cartridge	Dimensions – inches		Dimensions – mm		Color
1.015" MARKER LENGTH									
22-16 Gauge	0.046 - 0.110 dia (1.20 - 2.80 mm)	■	XPS-125-1	100	1.015	0.235	25.78	5.96	BK on WT
18-12 Gauge	0.062 - 0.150 dia (1.60 - 3.80 mm)	■	XPS-187-1	100	1.015	0.335	25.78	8.50	BK on WT
16-10 Gauge	0.094 - 0.215 dia (2.40 - 5.50 mm)	■	XPS-250-1	100	1.015	0.439	25.78	11.15	BK on WT
12-6 Gauge	0.125 - 0.320 dia (3.20 - 8.10 mm)	■	XPS-375-1	100	1.015	0.645	25.78	16.38	BK on WT
CONTINUOUS (CUT TO LENGTH)									
22-16 Gauge	0.046 - 0.110 dia (1.20 - 2.80 mm)	■	XPS-125-CONT	1 roll (cont.)	12 ft.	0.235	3.65 m	5.96	BK on WT
22-16 Gauge	0.046 - 0.110 dia (1.20 - 2.80 mm)	■	XPS-125-CONT-YL-BK	1 roll (cont.)	12 ft.	0.235	3.65 m	5.96	BK on YL
18-12 Gauge	0.062 - 0.150 dia (1.60 - 3.80 mm)	■	XPS-187-CONT	1 roll (cont.)	12 ft.	0.335	3.65 m	8.50	BK on WT
18-12 Gauge	0.062 - 0.150 dia (1.60 - 3.80 mm)	■	XPS-187-CONT-YL-BK	1 roll (cont.)	12 ft.	0.335	3.65 m	8.50	BK on YL
16-10 Gauge	0.094 - 0.215 dia (2.40 - 5.50 mm)	■	XPS-250-CONT	1 roll (cont.)	8 ft.	0.439	2.44 m	11.15	BK on WT
16-10 Gauge	0.094 - 0.215 dia (2.40 - 5.50 mm)	■	XPS-250-CONT-YL-BK	1 roll (cont.)	8 ft.	0.439	2.44 m	11.15	BK on YL
12-6 Gauge	0.125 - 0.320 dia (3.20 - 8.10 mm)	■	XPS-375-CONT	1 roll (cont.)	8 ft.	0.645	2.44 m	16.38	BK on WT

\*Approx based on NEC for THHN wire.







▶ **TERMINAL BLOCK MARKERS**

These specially-designed narrow-width markers automatically set to fixed spacing and separation between legends and rotate to top-down orientation for perfect alignment on terminal blocks. Printer can auto-serialize to save additional time.

- ▶ **B-498 Vinyl Cloth material. Temp Range: -40°F to 175°F (-40°C to 70°C).**

Width of Strip	Diagram	Part Number	Labels per Cartridge	Dimensions – inches		Dimensions – mm		Color
0.240" wide	●	XC-240-498	1 roll (cont.)	0.240	24 ft.	6.10	7.31 m	BK on WT
0.318 wide	●	XC-318-498	1 roll (cont.)	0.318	24 ft.	8.07	7.31 m	BK on WT
0.375" wide	●	XC-375-498	1 roll (cont.)	0.375	24 ft.	9.53	7.31 m	BK on WT



▶ Visit us at [Transcat.com](http://Transcat.com)!

35 Vantage Point Drive // Rochester, NY 14624 // Call 1.800.800.5001

