



**Your experts for
safety, facility
and equipment
identification**

Product Catalog

Microscope Slide Labels (B-481 and B-488)

StainerBondz™ Labels are designed specifically to identify slides and to resist exposure to harsh chemicals during the slide staining process. They perform well in stains such as hematoxylin and eosin.

- **B-481 StainerBondz Polyester:** White polyester with extreme chemical resistance and withstands the rigors of typical deparaffinization, including ethanol, xylene and H and E staining process.
- **B-488 StainerBondz Polyester:** White polyester with moderate chemical resistance for short-term exposure to xylene, DMSO and ethanol.




Figure 2



Fits Printers	Figure	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Roll	Ribbon in Cartridge
B-481 Polyester with extreme chemical-resistance									
BMP51, 53	Fig. 2	M-195-481	B-481	Polyester	Black on White	0.900 (22.8)	0.375 (9.5)	320	R6400
BMP51, 53	Fig. 2	M-194-481	B-481	Polyester	Black on White	0.900 (22.8)	0.750 (19.1)	320	R6400
BMP51, 53	Fig. 2	M-97-481	B-481	Polyester	Black on White	0.900 (22.8)	0.900 (22.9)	280	R6400
B-488 Polyester with moderate chemical-resistance									
BMP51, 53	Fig. 2	M-97-488	B-488	Polyester	Black on White	0.900 (22.8)	0.900 (22.9)	280	R4300
BMP51, 53	Fig. 2	M-81-488	B-488	Polyester	Black on White	1.900 (48.2)	0.250 (6.3)	160	R4300

Microcentrifuge and PCR Tube Labels (B-499 and B-7425)

Designed with ultra-thin material that prevents vials from jamming in centrifuges or racks. These labels withstand harsh temperatures and chemicals without falling off, fading or smearing.

- **B-499 Nylon Cloth:** Thick white nylon cloth for easy handling and conformability.
- **B-7425 Polypropylene:** Ideal for labeling dry, room temperature specimen containers. Temp. range: -196° C to 121° C (-320° F to 248° F). Chemical resistance to ethanol, DMSO, IPS, short term xylene, 10% formalin, 50% acetic acid and toluene.




Figure 2




Figure 24




Figure 26



Figure 33



Fits Printers	Figure	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Label Dia. C Inch (mm)	Labels Per Roll	Ribbon in Cartridge
B-499 Nylon Cloth										
BMP51, 53	Fig. 24	M-118-499	B-499	Nylon Cloth	Black on White	1.000 (25.4)	0.375 (9.5)	0.375 (9.5) dia.	240	R4300
BMP51, 53	Fig. 24	M-120-499	B-499	Nylon Cloth	Black on White	1.000 (25.4)	0.500 (12.7)	0.375 (9.5) dia.	240	R4300
BMP51, 53	Fig. 24	M-117-499	B-499	Nylon Cloth	Black on White	1.000 (25.4)	0.500 (12.7)	0.440 (11.1) dia.	240	R4300
BMP51, 53	Fig. 33	MC-1000-499	B-499	Nylon Cloth	Black on White	1.000 (25.4)	16 ft. (4.8 m)	-	1 roll (cont.)	R4300
BMP51, 53	Fig. 26	M-82-499	B-499	Nylon Cloth	Black on White	0.375 (9.5) dia.	-	-	240	R4300
BMP51, 53	Fig. 26	M-83-499	B-499	Nylon Cloth	Black on White	0.500 (12.7) dia.	-	-	240	R4300
BMP51, 53	Fig. 26	M-82-499-OR-BK	B-499	Nylon Cloth	Black on Orange	0.375 (9.5) dia.	-	-	240	R4300
BMP51, 53	Fig. 26	M-83-499-OR-BK	B-499	Nylon Cloth	Black on Orange	0.500 (12.7) dia.	-	-	240	R4300
BMP51, 53	Fig. 26	M-82-499-RD-BK	B-499	Nylon Cloth	Black on Red	0.375 (9.5) dia.	-	-	240	R4300
BMP51, 53	Fig. 26	M-83-499-RD-BK	B-499	Nylon Cloth	Black on Red	0.500 (12.7) dia.	-	-	240	R4300
BMP51, 53	Fig. 26	M-82-499-YL-BK	B-499	Nylon Cloth	Black on Yellow	0.375 (9.5) dia.	-	-	240	R4300
BMP51, 53	Fig. 26	M-83-499-YL-BK	B-499	Nylon Cloth	Black on Yellow	0.500 (12.7) dia.	-	-	240	R4300
B-7425 Polypropylene										
BMP51, 53	Fig. 24	M-118-7425	B-7425	Polypropylene	Black on White	1.000 (25.4)	0.375 (9.5)	0.375 (9.5) dia.	240	R4300
BMP51, 53	Fig. 2	M-31-7425	B-7425	Polypropylene	Black on White	1.500 (38.10)	1.000 (25.4)	-	250	R4300

Tissue Cassette Labels (B-482 and B-498)

- **B-482 Polyester Material:** White polyester label with superior resistance to tissue processing chemicals and embedding procedures. Use with the BSP™31 Label Attachment System for pre-process tissue cassette ID.
- **B-498 Repositionable Vinyl Cloth Material:** Removable white vinyl cloth for re-identification of post-process tissue cassettes or general lab applications. Can be applied directly onto the cassettes or on top of previous label.




Figure 2



Fits Printers	Figure	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Roll	Ribbon in Cartridge
BMP51, 53	Fig. 2	M-127-482	B-482	Polyester	Black on White	1.05 (26.6)	0.250 (6.3)	360	R6400
BMP41, 51, 53	Fig. 2	M-11-498	B-498	Vinyl Cloth	Black on White	0.750 (12.7)	0.500 (19.1)	220	R6200

Color Polyester Labels (B-494)

Gloss white polyester with a color border printed on the label allows for differentiation of test specimens within user processes. Vial top labels are solid color. Resistant to common lab chemicals like ethanol and xylene.




Figure 2




Figure 24



Fits Printers	Figure	Catalog #	B#	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Secondary Label C Inch (mm)	Labels Per Roll	Ribbon in Cartridge
BMP51	Fig. 24	M-118-494-BL	B-494	Polyester	Black on Blue	1.000 (25.4)	0.375 (9.5)	0.375 (9.5)	240	R6400
BMP51	Fig. 24	M-120-494-BL	B-494	Polyester	Black on Blue	1.000 (25.4)	0.500 (12.7)	0.375 (9.5)	240	R6400
BMP51	Fig. 2	M-131-494-BL	B-494	Polyester	Black on Blue	1.000 (25.4)	0.500 (12.7)	-	180	R6400
BMP51	Fig. 2	M-49-494-BL	B-494	Polyester	Black on Blue	1.000 (25.4)	1.000 (25.4)	-	260	R6400
BMP51	Fig. 24	M-118-494-GN	B-494	Polyester	Black on Green	1.000 (25.4)	0.375 (9.5)	0.375 (9.5)	240	R6400
BMP51	Fig. 24	M-120-494-GN	B-494	Polyester	Black on Green	1.000 (25.4)	0.500 (12.7)	0.375 (9.5)	240	R6400
BMP51	Fig. 2	M-131-494-GN	B-494	Polyester	Black on Green	1.000 (25.4)	0.500 (12.7)	-	180	R6400
BMP51	Fig. 2	M-49-494-GN	B-494	Polyester	Black on Green	1.000 (25.4)	1.000 (25.4)	-	260	R6400
BMP51	Fig. 24	M-118-494-OR	B-494	Polyester	Black on Orange	1.000 (25.4)	0.375 (9.5)	0.375 (9.5)	240	R6400
BMP51	Fig. 24	M-120-494-OR	B-494	Polyester	Black on Orange	1.000 (25.4)	0.500 (12.7)	0.375 (9.5)	240	R6400
BMP51	Fig. 2	M-131-494-OR	B-494	Polyester	Black on Orange	1.000 (25.4)	0.500 (12.7)	-	180	R6400
BMP51	Fig. 2	M-49-494-OR	B-494	Polyester	Black on Orange	1.000 (25.4)	1.000 (25.4)	-	260	R6400
BMP51	Fig. 24	M-118-494-PK	B-494	Polyester	Black on Pink	1.000 (25.4)	0.375 (9.5)	0.375 (9.5)	240	R6400
BMP51	Fig. 24	M-120-494-PK	B-494	Polyester	Black on Pink	1.000 (25.4)	0.500 (12.7)	0.375 (9.5)	240	R6400
BMP51	Fig. 2	M-131-494-PK	B-494	Polyester	Black on Pink	1.000 (25.4)	0.500 (12.7)	-	180	R6400
BMP51	Fig. 2	M-49-494-PK	B-494	Polyester	Black on Pink	1.000 (25.4)	1.000 (25.4)	-	260	R6400
BMP51	Fig. 24	M-118-494-RD	B-494	Polyester	Black on Red	1.000 (25.4)	0.375 (9.5)	0.375 (9.5)	250	R6400
BMP51	Fig. 24	M-120-494-RD	B-494	Polyester	Black on Red	1.000 (25.4)	0.500 (12.7)	0.375 (9.5)	240	R6400
BMP51	Fig. 2	M-131-494-RD	B-494	Polyester	Black on Red	1.000 (25.4)	0.500 (12.7)	-	180	R6400
BMP51	Fig. 2	M-49-494-RD	B-494	Polyester	Black on Red	1.000 (25.4)	1.000 (25.4)	-	260	R6400
BMP51	Fig. 24	M-118-494-YL	B-494	Polyester	Black on Yellow	1.000 (25.4)	0.375 (9.5)	0.375 (9.5)	240	R6400
BMP51	Fig. 24	M-120-494-YL	B-494	Polyester	Black on Yellow	1.000 (25.4)	0.500 (12.7)	0.375 (9.5)	240	R6400
BMP51	Fig. 2	M-131-494-YL	B-494	Polyester	Black on Yellow	1.000 (25.4)	0.500 (12.7)	-	180	R6400
BMP51	Fig. 2	M-49-494-YL	B-494	Polyester	Black on Yellow	1.000 (25.4)	1.000 (25.4)	-	260	R6400



Get the job done for less with a Printer Starter Kit

Voice and DataComm Starter Kit

Kit includes:

- Hard case, USB cable and AC power supply
- Self-laminating cable markers (M-21-427)
- Port, faceplate and general ID labels (M-30-422)
- Non-adhesive slide-in strips for punch blocks (MC-475-412)
- Rack and panel labels (MC-1000-595-YL-BK)
- 1.5 in. white label roll for general ID (MC-1500-595-WT-BK)

Catalog #	Description
BMP51-KIT-VD	Starter Kit with BMP51 Label Printer and Li-Ion Battery

Electrical ID Starter Kit

Kit includes:

- Hard case, USB cable and AC power supply
- Self-laminating wire markers (M-103-427)
- Wrap around wire markers (M-18-498)
- PermaSleeve® PS Heat-Shrink Wire Markers (M-187-1-342)
- Panel identification labels (MC-1500-595-OR-BK)
- 1.5 in. white label roll for general ID (MC-1500-595-WT-BK)

Catalog #	Description
BMP51-KIT-EL	Starter Kit with BMP51 Label Printer and Li-Ion Battery

Facility ID Starter Kit

Kit includes:

- Hard case, USB cable and AC power supply
- 1.5 in. yellow label roll with black ribbon (MC-1500-595-YL-BK)
- 1.5 in. white label roll with red ribbon (MC-1500-595-WT-RD)
- 1.5 in. green label roll with white ribbon (MC-1500-595-GN-WT)
- 1.5 in. white label roll with black ribbon (MC-1500-595-WT-BK)
- 2 in. x 1 in. labels for low surface energy labeling (M-20-483)

Catalog #	Description
BMP51-KIT-GI	Starter Kit with BMP51 Label Printer and Li-Ion Battery

Lab ID Starter Kit

Kit includes:

- Hard case, USB cable and AC power supply
- Vial and tube labels (M-156-492)
- Microplate labels (M-81-488)
- Top and side label set for vials and tubes (M-120-492)
- Removable die-cut labels for bottles, beakers, etc. (M-103-498)
- 1.5 in. white label roll for general ID (MC-1500-595-WT-BK)

Catalog #	Description
BMP51-KIT-LS	Starter Kit with BMP51 Label Printer and Li-Ion Battery