

### Static Shielding Bag\_ANT010SSB

#### **Features:**

- Metal "Faraday cage" layer shields products from electrical energy inside and prevents static build-up
- · Four layer protection guards against charges inside and out
- Semi transparent for easy content identification
- Surface resistance of  $10^8$ - $10^{10}\Omega$
- Conforms to ANSI/ESD S-20.20, EN61340-5-1, ANSI/ESD STM11.31
- Custom sizes and print available on request
- Suitable for packing electronic products which are sensitive to static, eg PCB's, Electronic Components etc






## Bag Opening Seal Seal **Bottom Fold**

#### STATIC SHIELDING BAG ANT010SSB

THIS BAG IS ROHS COMPLIANT

### **ATTENTION** OBSERVE PRECAUTIONS





### **Construction:**

Our static shielding bags are constructed in four layers, consisting of a static dissipative polyester outer layer and a static dissipative polyethylene inner layer with a centre metallised shield layer.

Our bags are manufactured from industry approved polyester and polyethelene laminates. The polyester dielectric works with the metal layer to provide a Faraday effect, the metal layer preventing penetration from damaging electrostatic fields. The specially processed polyethelene keeps tribocharging to a minimum.

### Configuration(s):

Our bags are available in custom sizes or in several industry standard sizes. Bags are offered in a 2-seal configuration and bottom fold, with our standard flexographically printed artwork. Please note any bags that are longer than 24" will have a 3rd seal along the bottom edge. Our bags can also be personalised with your company logo on any bespoke orders.

### **Standard Bag Artwork:**

Our static shielding bags are produced with the following sample artwork as standard. For further information on bespoke/printed orders, please contact one of our sales team. Please note there is a MOQ of 20,000 bags on all printed bags.

Important Notice: This data sheet and its contents (the "Information") belong to Antistat Inc. or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but Antistat Inc. assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where Antistat Inc. was aware of the possibility of such loss or damage arising) is excluded. Antistat Inc. 2017.



### Static Shielding Bag\_ANT010SSB

All bags and film meet the requirements of ANSI/ESD S20.20 ANSI ESD S541

#### **Technical Parameters:**

Item:	Test Standard:	Result:	
Film Thickness	Micron Meter	3mil 75 micron	
Metal Layer Optical Transmission	ASTM D1003	40% +/- 5% optical density	
Surface Resistance	ANSI STM 11.11 @12% & 50% R.H.	10 <sup>8</sup> - 10 <sup>10</sup> Ω	
Time for static removal	FTMS 101B Method 4046 - 5000-0V	<.0.03 Sec	
Static Shielding - Energy Penetration	ANSI ESD-STM-11.31 @12% & 50% R.H.	<20 nJ	
Static Shielding - Capacitive Probe	ANSI / EIA-541 Appendix E	<25V	
Friction Static	ANSI / E1A541 Appendix C Avg.	TriboelectricNanocolombs Quartz +0.01 Teflon -0.09	
Anti-erosion	FTMS 101C Method 3005	No visible spots	
Tensile Strength	ASTM D882-91, Method A	MD 6530 psi TD 5800 psi	
Tear Initiation	ASTM D1004 -94-Notched	MD 2.5 lbs./in TD 2.0 lbs	
Puncture Resistance	ASTM D3420	>10 lbs	
Tear Resistance	ASTM D882	>8 lbs./in	
Burst Strength	FTMS 101 C Method 2065.1	50 psi Nominal	
Heat Seal Temperature	-	250 - 375 °F	
Heat Seal Pressure	-	30-70 psi	
Heat Seal Strength	(D1876-93) Vertrod bar sealer/heat	>12 lbs/in width (room temperature)	
Breaking Elongation Rate	ASTM D882-91 Method A	MD 80% TD 85%	
Appearance	GB/96-04-10	No delamination, burst seal, wrinkle, warp, break, foreign particle adherence, air bubble beyond sealing $\varphi \leq 3$ mm	

Test Conclusion: (Date of Issue: 2009-11-10)

The shielding bag is tested accordance with the relevant test standard and requirements.

Test Item:	Test Method:	Measured Equipment(s):	MDL:
Lead (Pb)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Cadmium (Cd)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Mercury (Hg)	IEC 62321:2008 Ed.1 Sec.7	ICP-OES	2mg/kg
Hexavalent Chromium (Cr(VI))	IEC 62321:2008 Ed.1 Annex C	UV-Vis	2mg/kg
Polybrominated Biphenyls (PBBs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg

### **RoHS and REACH Compliance Statement:**

All of Antistat's products are RoHS and Reach compliant.



### ANTISTAT

Product Code:	Size (Inches):	Size (mm):	Additional Notes:
010-0001	3 x 5	76 x 127	Pack of 100
010-0005	4 x 6	102 x 152	Pack of 100
010-0006	4 x 8	102 x 203	Pack of 100
010-0008	4 x 12	102 x 305	Pack of 100
010-0009	4 x 24	102 x 610	Pack of 100
010-0187	5 x 7	127 x 177.8	Pack of 100
010-0011	5 x 8	127 x 203	Pack of 100
010-0012	5 x 26	127 x 660.4	Pack of 100
010-0014	6 x 8	152 x 203	Pack of 100
010-0120	6 x 9	152 x 228.6	Pack of 100
010-0015	6 x 10	152 x 254	Pack of 100
010-0016	6 x 12	152 x 305	Pack of 100
010-0023	8 x 8	203 x 203	Pack of 100
010-0024	8 x 10	203 x 254	Pack of 100
010-0025	8 x 12	203 x 305	Pack of 100
010-0036	8 x 18	203 x 457	Pack of 100
010-0113	9 x 12	228.6 x 305	Pack of 100
010-0029	10 x 12	254 x 305	Pack of 100
010-0030	10 x 14	254 x 355	Pack of 100
010-0031	10 x 16	254 x 406	Pack of 100
010-0032	10 x 18	254 x 457	Pack of 100
010-0034	10 x 24	305 x 610	Pack of 100
010-0033	10 x 30	305 x 762	Pack of 100
010-0115	11 x 15	305 x 381	Pack of 100
010-0038	12 x 12	305 x 305	Pack of 100
010-0041	12 x 16	305 x 406	Pack of 100
010-0042	12 x 18	305 x 457	Pack of 100
010-0095	12 x 24	305 x 610	Pack of 100
010-0047	14 x 16	355 x 406	Pack of 100
010-0048	14 x 18	355 x 457	Pack of 100
010-0114	15 x 18	381 x 457	Pack of 100
010-0055	16 x 18	406 x 457	Pack of 100
010-0058	18 x 18	457 x 457	Pack of 100
010-0059	18 x 20	457 x 508	Pack of 100
010-0060	18 x 24	457 x 610	Pack of 100
010-0096	20 x 24	508 x 610	Pack of 100

Note: Other sizes available upon request.

Specialists in Materials Testing and Technical Services

## TEST REPORT

### AntiStat Inc Static Shielding Bags

Stock Code: 010-0024

Metal Shield

8" X 10"

203x254mm

Bin A9/F51/F71

Stamp on Sealed Edge of Bags: 011215

### **TESTED FOR**

Surface Resistance per ESD STM 11.11 Static Discharge Shielding per ESD STM 11.31

> Report #: 2016-041 April 25<sup>th</sup>, 2016

### Specialists in Materials Testing and Technical Services

### **SUMMARY**

One-hundred moisture barrier static shielding bags were submitted for testing to industry specifications ANSI/ESD STM11.11 (surface resistance measurements of the inside and outside of the bags) and ANSI/ESD STM11.31 (static discharge shielding). The tested bags meet or exceed the requirements of ANSI/ESD STM541 and ANSI/ESD S20.20.

### **EXPERIMENTAL AND DISCUSSION**

The bags were randomly selected and conditioned for 48 hours at the specified conditions (12% & 50% R.H., & 23°C) before testing was started. Testing was carried out in the conditioning environment.

Surface resistance is reported as "resistance," as specified in ANSI/ESD STM11.11. To obtain resistivity values, multiply the resistance numbers by 10. The data from this testing is included below in Table 1.

The static discharge shielding test was performed using the test methods called out in ANSI/ESD STM11.31. The data from this testing is summarized below in Table 2, detailed data is included as appendix A.

Table 1
Surface Resistance Data
Stock Code: 018-0132S - Metal Moisture Barrier Shielding Bag

Surface Resistance per ANSI/ESD STM11.11				
Sample #	Inside	Outside		
1	8.11 x $10^{9}\Omega$	$4.99 \times 10^{9}Ω$		
2	$8.54 \times 10^{9}\Omega$	$2.93 \times 10^{9}\Omega$		
3	$3.89 \times 10^{9}\Omega$ 7.54 x 10			
4	$6.99 \times 10^{9}\Omega$	$3.07 \times 10^{9}\Omega$		
5	$3.07 \times 10^{9}\Omega$	$5.67 \times 10^{9}\Omega$		
6	$4.32 \times 10^{9}\Omega$	$3.33 \times 10^{9}\Omega$		
Average	$5.41 \times 10^{9}\Omega$	$4.31 \times 10^{9}Ω$		
Median	$5.49 \times 10^{9}\Omega$	$4.07 \times 10^{9}Ω$		
Minimum	$3.07 \times 10^{9}\Omega$	$2.93 \times 10^{9}\Omega$		
Maximum	$8.54 \times 10^{9}\Omega$	7.54 x 10 <sup>10</sup> Ω		



### Specialists in Materials Testing and Technical Services

# Table 2 Static Discharge Shielding Data Summary Stock Code: 018-0132S - Metal Moisture Barrier Shielding Bag

Static Discharge Shielding Per ANSI/ESD STM11.31					
	12%	Data	50% Data		
	Calculat	ted Data	Calculated Data		
	Energy (nJ)	Peak I (mA)	Energy (nJ)	Peak I (mA)	
Average	10.79	64.46	8.44	55.97	
St. Dev.	2.42	19.46	2.43	19.01	
Min	5.61	36.81	5.23	30.41	
Max	14.74 102.43		12.95	98.43	

### **EQUIPMENT USED FOR ELECTRICAL TESTING**

Surface Resistance Measurements:

Keithley Model 6517a Electrometer/High Resistance Meter

ETS Model 803B Resistance Probe

ETS Model 809 Surface Resistance Verification Fixture

Static Discharge Shielding Measurements:

ETS Model 811/412 Electrostatic Discharge Unit/Shielding Bag Tester Tektronix TDS 520A Digital Oscilloscope.

The results provided in this report are accurate within the limits appropriate to each test standard. The results of this report are statistically significant only to the samples submitted for testing. MicroStat Laboratories/River's Edge Technical Service, Inc. has no controls, and assumes no responsibility for the tested product's functionality or use.

Carl E Newberg

April 25th, 2016

Date

Static Shielding Per ESD STM 11.31					
		12% Data		50% Data	
		Calculat	ed Data	Calculat	
Sample #	Test #	Energy (nJ)		Energy (nJ)	Peak I(mA)
1	1	14.23	90.43	11.68	87.23
1	2	11.25	75.22	5.57	43.21
1	3	10.18	66.42	6.12	32.01
1	4	10.46	41.61	10.12	43.21
1	5	10.75	60.02	7.67	53.62
1	6	10.40	64.02	7.96	64.02
2	1	8.65	54.42	7.49	44.81
2	2	7.92	43.21	6.64	45.61
2	3	14.74	100.83	6.64	45.61
2	4	11.14	65.62	7.09	46.41
2	5	10.86	56.82	9.66	33.61
2	6	11.34	51.22	6.32	40.81
3	1 2	10.97	76.02	5.46	44.01
3		6.41 10.25	50.42	9.68	71.22
3	3 4	10.25	42.41 44.81	11.82 8.70	63.22 43.21
3	5	14.55	102.43	8.88	43.21
3	6	13.73	92.83	7.43	56.82
4	1	13.73	76.02	7.43	47.22
4	2	11.41	38.41	12.95	82.43
4	3	14.73	90.43	5.81	46.41
4	4	9.60	40.01	5.99	50.42
4	5	13.71	68.82	11.38	64.02
4	6	7.09	43.21	11.51	72.82
5	1	9.12	56.82	5.45	44.81
5	2	9.38	64.02	11.74	88.83
5	3	6.35	53.62	8.60	68.82
5	4	14.01	88.03	12.47	98.43
5	5	10.17	54.42	10.09	59.22
5	6	10.13	64.82	5.54	32.01
6	1	10.50	81.63	9.04	37.61
6	2	10.40	64.02	5.34	30.41
6	3	13.53	101.63	5.23	44.01
6	4	10.20	75.22	11.70	94.43
6	5	5.61	44.01	11.46	89.63
6	6	9.96	36.81	7.40	61.62
		Calculated Data		Calculat	ed Data
		Energy (nJ) Peak I(mA)		Energy (nJ)	Peak I(mA)
	Average	10.79	64.46	8.44	55.97
	St. Dev.	2.42	19.46	2.43	19.01
	Min	5.61	36.81	5.23	30.41
	Max	14.74	102.43	12.95	98.43