




- ▶ Pin-point rework areas on printed circuit boards
- ▶ Select from five sizes in three different colors — Red, White and Yellow
- ▶ B-500 vinyl cloth material provides a tight bond, yet may be easily removed without leaving an adhesive residue



DIA - Die-Cut Inspection Arrow



EIA - Electronic Inspection Arrow



BIA - Board Inspection Arrow

**Die-Cut Inspection Arrow**

| Part Number | Markers Per Card | Color  | Size Inch (mm)              |
|-------------|------------------|--------|-----------------------------|
| DIA-250-RD  | 564              | Red    | 0.250 x 0.125 (6.35 x 3.18) |
| DIA-250-WT  | 564              | White  | 0.250 x 0.125 (6.35 x 3.18) |
| DIA-250-YL  | 564              | Yellow | 0.250 x 0.125 (6.35 x 3.18) |
| DIA-375-RD  | 280              | Red    | 0.375 x 0.187 (9.53 x 4.75) |
| DIA-375-WT  | 280              | White  | 0.375 x 0.187 (9.53 x 4.75) |
| DIA-375-YL  | 280              | Yellow | 0.375 x 0.187 (9.53 x 4.75) |
| DIA-500-RD  | 138              | Red    | 0.500 x 0.25 (12.70 x 6.35) |
| DIA-500-WT  | 138              | White  | 0.500 x 0.25 (12.70 x 6.35) |
| DIA-500-YL  | 138              | Yellow | 0.500 x 0.25 (12.70 x 6.35) |

**Electronic Inspection Arrow**

| Part Number | Markers Per Card | Color  | Size Inch (mm)              |
|-------------|------------------|--------|-----------------------------|
| EIA-3025-RD | 180              | Red    | 0.300 x 0.250 (7.62 x 6.35) |
| EIA-3025-WT | 180              | White  | 0.300 x 0.250 (7.62 x 6.35) |
| EIA-3025-YL | 180              | Yellow | 0.300 x 0.250 (7.62 x 6.35) |

**Board Inspection Arrow**

| Part Number | Markers Per Card | Color  | Size Inch (mm)              |
|-------------|------------------|--------|-----------------------------|
| BIA-RD      | 576              | Red    | 0.125 x 0.190 (3.18 x 4.83) |
| BIA-WT      | 576              | White  | 0.125 x 0.190 (3.18 x 4.83) |
| BIA-YL      | 576              | Yellow | 0.125 x 0.190 (3.18 x 4.83) |