



Product Number: LAT-7-410-10
Laser Printable Labels

Specifications:

Application(s): Circuit Board & Component ID, General & Industrial Identification, General Identification, Panel Identification, Through Hole - Top

Side: 1.000" W x 0.500" H (25.400 mm W x 12.700 mm H)

Sheet Size: 8.500" x 11.000" (215.9 mm x 279.4 mm)

Printable Area: 1.000" W x 0.500" H (25.400 mm W x 12.700 mm H)

Label Type/Style: Label

Horizontal Repeat: 1.100" (27.94 mm)

Color: White

Finish: Matte

Qty Per Row: 7

Material Type: Polyolefin

Material Description: Tamper-Evident Polyolefin

Brady Material #: B-410

Left Margin: 0.450" (11.43 mm)

Printer Compatibility: Laser Printers

Qty Per Sheet: 133

Through Hole Technology: Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No

Top Margin: 0.875" (22.23 mm)

Special Properties: Tamper-resistant

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 10,000/Package