



PRODUCT, WIRE, CABLE & INDUSTRIAL
IDENTIFICATION

BradyID.com



High-performance
labeling solutions
for the harshest
environments



3" Core Materials - Polyester

3" Core Materials

Polyester

B-461 Self-Laminating Polyester Material

Color: Clear **Finish:** Gloss

Clear film with a matte white printable zone ideal for cables, laboratory ID or general labeling where graphics need to be protected.






Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Print Area C Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 15c	THT-123-461-3	Polyester	Clear/White	0.375 (9.53)	1.800 (45.7)	0.750 (19.1)	1	3,000	R4300, R4500, R6200
Fig. 15c	THT-122-461-3	Polyester	Clear/White	0.500 (12.7)	1.800 (45.7)	0.750 (19.1)	1	3,000	R4300, R4500, R6200
Fig. 15c	THT-127-461-3	Polyester	Clear/White	0.500 (12.7)	2.200 (55.9)	0.750 (19.1)	1	3,000	R4300, R4500, R6200
Fig. 15c	THT-183-461-1	Polyester	Clear/White	1.000 (25.4)	1.750 (44.5)	1.000 (25.4)	1	1,000	R4300, R4500, R6200
Fig. 14c	THT-139-461-2	Polyester	Clear/White	1.000 (25.4)	5.250 (133.4)	1.500 (38.1)	2	2,000	R4300, R4500, R6200
Fig. 15c	THT-134-461-3	Polyester	Clear/White	1.500 (38.1)	3.500 (88.9)	1.250 (31.7)	1	3,000	R4300, R4500, R6200
Fig. 15c	THT-133-461-3	Polyester	Clear/White	1.625 (41.28)	0.600 (15.2)	1.000 (25.4)	1	3,000	R4300, R4500, R6200
Fig. 15c	THT-131-461-3	Polyester	Clear/White	2.625 (66.7)	1.000 (25.4)	1.000 (25.4)	1	3,000	R4300, R4500, R6200
Fig. 15c	THT-153-461-3	Polyester	Clear/White	2.625 (66.7)	1.000 (25.4)	0.600 (15.2)	1	3,000	R4300, R4500, R6200

B-473 Electrostatic Dissipative Polyester Material

Color: White **Finish:** Gloss

White polyester with glossy finish used for printed circuit board and electronic component post-process labeling. Features a permanent static dissipative adhesive and a static dissipative release liner. Surface resistivity values in the recommended range for dissipative ESD packing materials. Also meets requirements of EIA-541 "Packaging Material Standards for ESD Sensitive Items."



Performance Attributes:






Figure 1

Figure 2

Figure 4

Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 4	* THT-11-473-10	Polyester	White	0.250 (6.4)	0.250 (6.4)	3.200 (81.3)	12	10,000	R6002
Fig. 1	* THT-70-473-20	Polyester	White	0.250 (6.4)	0.250 (6.4)	2.370 (60.2)	7	20,000	R6000
Fig. 1	* THT-38-473-10	Polyester	White	0.375 (9.5)	0.375 (9.5)	3.200 (81.3)	7	10,000	R6002
Fig. 1	* THT-12-473-10	Polyester	White	0.500 (12.7)	0.437 (11.1)	3.350 (85.1)	5	10,000	R6002
Fig. 1	* THT-36-473-10	Polyester	White	0.500 (12.7)	0.200 (5.1)	3.200 (81.3)	5	10,000	R6002
Fig. 1	* THT-96-473-10	Polyester	White	0.500 (12.7)	0.275 (7.0)	2.500 (63.5)	4	10,000	R6002
Fig. 2	* THT-97-473-10	Polyester	White	0.500 (12.7)	0.200 (5.1)	0.700 (17.8)	1	10,000	R6011
Fig. 1	* THT-14-473-10	Polyester	White	0.650 (16.5)	0.200 (5.1)	2.950 (74.9)	4	10,000	R6002
Fig. 2	* THT-47-473-10	Polyester	White	0.650 (16.5)	0.200 (5.1)	0.850 (21.6)	1	10,000	R6011
Fig. 1	* THT-57-473-10	Polyester	White	0.700 (17.8)	0.375 (9.5)	3.350 (85.1)	4	10,000	R6007
Fig. 1	* THT-1-473-10	Polyester	White	0.750 (19.1)	0.250 (6.4)	3.350 (85.1)	4	10,000	R6007
Fig. 2	* THT-46-473-10	Polyester	White	0.750 (19.1)	0.250 (6.4)	0.950 (24.1)	1	10,000	R6006
Fig. 1	* THT-2-473-10	Polyester	White	0.900 (22.9)	0.250 (6.4)	3.350 (85.1)	3	10,000	R6007
Fig. 2	* THT-49-473-10	Polyester	White	0.900 (22.9)	0.250 (6.4)	1.100 (27.9)	1	10,000	R6006
Fig. 2	* THT-103-473-10	Polyester	White	1.000 (25.4)	0.250 (6.4)	1.200 (30.5)	1	10,000	R6006
Fig. 1	* THT-3-473-10	Polyester	White	1.000 (25.4)	0.375 (9.5)	3.350 (85.1)	3	10,000	R6007
Fig. 1	* THT-5-473-10	Polyester	White	1.000 (25.4)	0.500 (12.7)	3.350 (85.1)	3	10,000	R6007
Fig. 2	* THT-58-473-10	Polyester	White	1.000 (25.4)	0.375 (9.5)	1.200 (30.5)	1	10,000	R6006
Fig. 2	* THT-59-473-10	Polyester	White	1.000 (25.4)	0.500 (12.7)	1.200 (30.5)	1	10,000	R6006
Fig. 1	* THT-13-473-10	Polyester	White	1.250 (31.8)	0.250 (6.4)	2.750 (69.9)	2	10,000	R6002
Fig. 2	* THT-43-473-10	Polyester	White	1.250 (31.8)	0.250 (6.4)	1.450 (36.8)	1	10,000	R6006
Fig. 1	* THT-4-473-10	Polyester	White	1.500 (38.1)	0.250 (6.4)	3.350 (85.1)	2	10,000	R6007
Fig. 2	* THT-45-473-10	Polyester	White	1.500 (38.1)	0.250 (6.4)	1.700 (43.2)	1	10,000	R6000
Fig. 2	* THT-15-473-2.5	Polyester	White	2.000 (50.8)	0.250 (6.4)	2.200 (55.9)	1	2,500	R6000
Fig. 2	* THT-48-473-10	Polyester	White	2.000 (50.8)	0.250 (6.4)	2.200 (55.9)	1	10,000	R6000

* **WARNING:** Cancer www.P65Warnings.ca.gov

3" Core Materials - Polyester

B-481 StainerBondz™ Polyester Material

Color: White Finish: Matte

Chemical resistant polyester designed for use in the slide staining process and other laboratory ID which requires superior chemical resistance. Permanent acrylic adhesive that performs well in the commonly used H and E (hematoxylin and eosin) slide staining process. Excellent resistance to a wide variety of chemicals, oils and water.




Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 2	THT-195-481-3	Polyester	White	0.900 (22.9)	0.375 (9.5)	-	1	3,000	R6400
Fig. 2	THT-194-481-3	Polyester	White	0.900 (22.9)	0.750 (19.1)	-	1	3,000	R6400
Fig. 25	THT-141-481-3	Polyester	White	0.900 (22.9)	0.900 (22.9)	-	2	3,000	R6400
Fig. 2	THT-164-481-3	Polyester	White	0.900 (22.9)	0.900 (22.9)	-	1	3,000	R6400
Fig. 2	THT-142-481-2.5	Polyester	White	2.500 (63.5)	0.200 (5.1)	-	1	2500	R6400

B-482 Polyester Material

Color: White Finish: Matte

Designed for tissue cassette labeling and identification. This material has superior resistance to processing fluids and conditions and has a permanent acrylic adhesive. RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. B-482 is not recommended for use in conditions where both high temperature (greater than 95° F/35° C) and 80% relative humidity are present.





Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 2	THT-213-482-3	Polyester	Silver	1.050 (26.7)	0.313 (7.95)	-	1	3,000	R6400
Fig. 2	THT-199-482-3	Polyester	White	1.050 (26.7)	0.250 (6.4)	-	1	3,000	R6400

B-483 Polyester Material

Color: White Finish: Gloss

White polyester thermal transfer material with glossy finish and aggressive adhesive specifically designed for powder coated surfaces.



Preprinted with:
 AV = Advertencia
 DA = Danger
 PE = Peligro
 WA = Warning



Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 1	THT-5-483-10	Polyester	White	1.000 (25.4)	0.500 (12.7)	3.350 (85.1)	3	10,000	R6007
Fig. 2	THT-59-483-10	Polyester	White	1.000 (25.4)	0.500 (12.7)	1.200 (30.5)	1	10,000	R6006
Fig. 1	THT-37-483-10	Polyester	White	1.500 (38.1)	0.500 (12.7)	3.350 (85.1)	2	10,000	R6007
Fig. 2	THT-17-483-3	Polyester	White	2.000 (50.8)	1.000 (25.4)	2.200 (55.9)	1	3,000	R6000
Fig. 3	THT-106-483	Polyester	White	2.000 (50.8)	300 ft. (91.4 m)	2.200 (55.9)	1	1 roll (cont.)	R6000
Fig. 2	THT-7-483-3	Polyester	White	2.750 (69.9)	1.250 (31.8)	2.950 (74.9)	1	3,000	R6002
Fig. 2	THT-18-483-3	Polyester	White	3.000 (76.2)	1.000 (25.4)	3.200 (81.3)	1	3,000	R6002
Fig. 2	THT-19-483-1	Polyester	White	3.000 (76.2)	2.000 (50.8)	3.200 (81.3)	1	1,000	R6002
Fig. 2	THT-184-483-1	Polyester	White	3.000 (76.2)	3.000 (76.2)	-	1	1000	R6002
Fig. 3	THT-21-483	Polyester	White	3.000 (76.2)	300 ft. (91.4 m)	3.200 (81.3)	1	1 roll (cont.)	R6002
Fig. 2	THT-55-483-1	Polyester	White	4.000 (101.6)	2.000 (50.8)	4.200 (106.7)	1	1,000	R6007
Fig. 2	THT-76-483-1	Polyester	White	4.000 (101.6)	3.000 (76.2)	4.200 (106.7)	1	1,000	R6007
Fig. 3	THT-107-483	Polyester	White	4.000 (101.6)	300 ft. (91.4 m)	4.200 (106.7)	1	1 roll (cont.)	R6007
Fig. 2	THT-161-483-1	Polyester	White	4.000 (101.6)	4.000 (101.6)	4.200 (106.7)	1	1,000	R6007
Fig. 2	THT-25-483-1	Polyester	White	6.000 (152.4)	4.000 (101.6)	-	1	1000	R6007
Fig. 70	THT-184-483-1-WA	Polyester	Orange on White	3.000 (76.2)	3.000 (76.2)	3.200 (81.3)	1	2 rolls of 500	R6002
Fig. 70	THT-161-483-1-AV	Polyester	Orange on White	4.000 (101.6)	4.000 (101.6)	4.200 (106.7)	1	2 rolls of 500	R6007
Fig. 70	THT-161-483-1-WA	Polyester	Orange on White	4.000 (101.6)	4.000 (101.6)	4.200 (106.7)	1	2 rolls of 500	R6007
Fig. 70	THT-25-483-5-WA	Polyester	Orange on White	6.000 (152.4)	4.000 (101.6)	4.200 (106.7)	1	500	R6007
Fig. 70	THT-25-483-1-AV	Polyester	Orange on White	6.000 (152.4)	4.000 (101.6)	4.200 (106.7)	1	2 rolls of 500	R6007
Fig. 70	THT-25-483-1-WA	Polyester	Orange on White	6.000 (152.4)	4.000 (101.6)	4.200 (106.7)	1	2 rolls of 500	R6007
Fig. 70	THT-184-483-1-DA	Polyester	Red on White	3.000 (76.2)	3.000 (76.2)	3.200 (81.3)	1	2 rolls of 500	R6002
Fig. 70	THT-184-483-1-PE	Polyester	Red on White	3.000 (76.2)	3.000 (76.2)	3.200 (81.3)	1	2 rolls of 500	R6002
Fig. 70	THT-161-483-1-DA	Polyester	Red on White	4.000 (101.6)	4.000 (101.6)	4.200 (106.7)	1	2 rolls of 500	R6007
Fig. 70	THT-161-483-1-PE	Polyester	Red on White	4.000 (101.6)	4.000 (101.6)	4.200 (106.7)	1	2 rolls of 500	R6007
Fig. 70	THT-25-483-5-DA	Polyester	Red on White	6.000 (152.4)	4.000 (101.6)	4.200 (106.7)	1	500	R6007
Fig. 70	THT-25-483-1-DA	Polyester	Red on White	6.000 (152.4)	4.000 (101.6)	4.200 (106.7)	1	2 rolls of 500	R6007
Fig. 70	THT-25-483-1-PE	Polyester	Red on White	6.000 (152.4)	4.000 (101.6)	4.200 (106.7)	1	2 rolls of 500	R6007

Labels By Size Index page 300
 Print Ribbons page 146
 Material Guide page 264