

Catalog Number: M21-750-499

BMP™21 Mobile Printer, ID PAL™ & LABPAL™ Label Printer Labels

Specifications

Application(s): Communications Cables, General Identification, Laboratory

Identification, Panel Identification, Plate, Vial, Voice/Data Identification,

Wire & Cable Marking

Agency Halogen-Free (DIN VDE 0472/parts 815), UL Recognized

Approval(s)/Compliance:

Size: 0.750" W x 16' H (19.050 mm W x 4.88 m H)

Printable Area: 0.750" W x 16' H (19.050 mm W x 4.880 m H)

Label Type/Style: Label

Color: Black on White

Finish: Matte

Qty Per Row: 1

Material Description: Nylon Cloth

Cable Type: 100 Pair Copper, 2 Pair Fiber, 25 Pair Copper, 4 Pair STP, 4 Pair UTP, 4-

12 Pair Fiber, 50 Pair Copper, Backbone Cable, Cable Bundles, CAT 5, CAT 5E, CAT 6, Fiber Strand, Fiber/Coax, RG-59 Coax, RG-6 Coax,

Silver Satin

Environment: Autoclave, Freezer, Liquid Nitrogen

Printer Compatibility: BMP21, ID PAL, LABPAL

Surface: Highly Textured, Low Surface Energy, Powder Coated, Smooth,

Textured/Rough

Special Properties: High adhesion, Low profile

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS

Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information

provided by suppliers of the raw materials used by Brady to

manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection

with the use of this information.

QTY/UOM: 1/Roll