




Catalog Number: THT-46-477-10

Thermal Transfer Printable Labels



Printable, static dissipative polyimide labels for thermal transfer printers. Please Note: This material is UL recognized with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

Specifications:

Application(s): Circuit Board & Component ID, SMT - Top/Bottom, Static Dissipative, Through Hole - Bottom, Through Hole - Top

Agency: EIA-541 "Packaging Material Standards for ESD Sensitive Items",

Approval(s)/Compliance: MIL-STD-202F, Notice 12, Method 215JESD-approved for IEC 61340-5-1 and EN 100015-1, UL Recognized

Size: 0.750" W x 0.250" H (19.050 mm W x 6.350 mm H)

Printable Area: 0.750" W x 0.250" H (19.050 mm W x 6.350 mm H)

Web Width: 0.950" (24.13 mm)

Label Type/Style: Label

Vertical Repeat: 0.350" (8.89 mm)

Color: White

Finish: Gloss

Qty Per Row: 1

Material Type: Polyimide

Material Description: Static Dissipative Polyimide

Recommended Ribbon Series: 6000

Suggested Ribbon Part#: R6011

After Process: Yes, this material will work with this application

Printer Compatibility: BBP81, Brady 200MVP Plus, Brady 300MVP Plus, Brady 300X-Plus

II, Brady 360X-Plus II, Brady 600X-Plus II, Brady IP, Thermal Transfer Printers

Surface Mount Technology: Yes, this material will work with this application

Through Hole Technology: Top: Yes, Bottom: Yes

Special Properties: Static dissipative adhesive & liner

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 10,000/Roll