




M710

LABEL PRINTER

Our fastest, most advanced portable yet
Get more done in less time

Component ID Labels (B-423 and B-428)

Various materials for relays, solenoids, PCBs, electronic components and more.

- **B-423 Harsh Environment Multi-Purpose Polyester Labels:** White glossy polyester
- **B-428 Metallized Matte Gray Polyester Labels:** Metallized matte polyester






Figure	Catalog #	B#	Material	Color	Label width A inch (mm)	Label height B inch (mm)	Labels per roll	Rec. ribbon
B-423 Permanent Polyester Material								
Fig. 2	M7-1-423	B-423	Polyester	White	0.250 (6.35)	0.250 (6.4)	750	M7-R6000
Fig. 2	M7-3-423	B-423	Polyester	White	0.375 (9.53)	0.375 (9.5)	500	M7-R6000
Fig. 2	M7-4-423	B-423	Polyester	White	0.400 (10.2)	0.400 (10.2)	500	M7-R6000
Fig. 33	M7C-500-423	B-423	Polyester	White	0.500 (12.7)	50 ft. (15.24 m)	1 roll (cont.)	M7-R6000
Fig. 2	M7-5-423	B-423	Polyester	White	0.500 (12.7)	0.200 (5.1)	750	M7-R6000
Fig. 2	M7-6-423	B-423	Polyester	White	0.500 (12.7)	0.280 (7.0)	750	M7-R6000
Fig. 2	BM-7-423	B-423	Polyester	White	0.500 (12.7)	0.500 (12.7)	5,000	M7-R6000
Fig. 2	M7-7-423	B-423	Polyester	White	0.500 (12.7)	0.500 (12.7)	500	M7-R6000
Fig. 2	M7-9-423	B-423	Polyester	White	0.650 (16.5)	0.200 (5.1)	750	M7-R6000
Fig. 2	M7-10-423	B-423	Polyester	White	0.750 (19.0)	0.250 (6.4)	750	M7-R6000
Fig. 2	M7-13-423	B-423	Polyester	White	0.900 (22.8)	0.250 (6.4)	750	M7-R6000
Fig. 2	M7-14-423	B-423	Polyester	White	1.000 (25.4)	0.187 (4.8)	750	M7-R6000
Fig. 2	M7-15-423	B-423	Polyester	White	1.000 (25.4)	0.275 (7.0)	750	M7-R6000
Fig. 2	BM-16-423	B-423	Polyester	White	1.000 (25.4)	0.375 (9.53)	5000	M7-R6000
Fig. 2	M7-16-423	B-423	Polyester	White	1.000 (25.4)	0.375 (9.53)	500	M7-R6000
Fig. 2	BM-17-423	B-423	Polyester	White	1.000 (25.4)	0.500 (12.7)	5,000	M7-R6000
Fig. 2	M7-17-423	B-423	Polyester	White	1.000 (25.4)	0.500 (12.7)	500	M7-R6000
Fig. 2	BM-19-423	B-423	Polyester	White	1.000 (25.4)	1.000 (25.4)	2,500	M7-R6000
Fig. 2	M7-19-423	B-423	Polyester	White	1.000 (25.4)	1.000 (25.4)	250	M7-R6000
Fig. 46	M7-24-423-BK	B-423	Polyester	Black Border	1.130 (28.7)	0.500 (12.7)	500	M7-R6000
Fig. 2	M7-25-423	B-423	Polyester	White	1.250 (31.8)	0.250 (6.4)	750	M7-R6000
Fig. 2	M7-27-423	B-423	Polyester	White	1.500 (38.1)	0.125 (3.2)	750	M7-R6000
Fig. 2	M7-28-423	B-423	Polyester	White	1.500 (38.1)	0.250 (6.4)	750	M7-R6000
Fig. 2	BM-29-423	B-423	Polyester	White	1.500 (38.1)	0.500 (12.7)	5,000	M7-R6000
Fig. 2	M7-29-423	B-423	Polyester	White	1.500 (38.1)	0.500 (12.7)	500	M7-R6000
Fig. 2	M7-31-423	B-423	Polyester	White	1.500 (38.1)	1.000 (25.4)	250	M7-R6000
Fig. 2	M7-32-423	B-423	Polyester	White	1.500 (38.1)	1.500 (38.1)	250	M7-R6000
Fig. 2	M7-2-423	B-423	Polyester	White	2.000 (50.8)	0.250 (6.4)	100	M7-R6000
Fig. 2	BM-20-423	B-423	Polyester	White	2.000 (50.8)	1.000 (25.4)	1,000	M7-R6000
Fig. 2	M7-20-423	B-423	Polyester	White	2.000 (50.8)	1.000 (25.4)	100	M7-R6000
Fig. 2	M7-26-423	B-423	Polyester	White	2.750 (69.9)	1.250 (31.8)	100	M7-R6000
Fig. 2	M7-22-423	B-423	Polyester	White	3.000 (76.2)	1.000 (25.4)	100	M7-R6000
Fig. 2	M7-37-423	B-423	Polyester	White	3.000 (76.2)	1.900 (48.3)	100	M7-R6000
Fig. 2	M7-23-423	B-423	Polyester	White	4.000 (101.6)	1.000 (25.4)	100	M7-R6000
Fig. 2	M7-38-423	B-423	Polyester	White	4.000 (101.6)	1.900 (48.3)	100	M7-R6000
B-428 Metallized Polyester Material								
Fig. 2	M7-15-428	B-428	Polyester	Lt Gray	1.000 (25.4)	0.275 (7.0)	750	M7-R4300
Fig. 2	BM-17-428	B-428	Polyester	Lt Gray	1.000 (25.4)	0.500 (12.7)	5,000	M7-R4300
Fig. 2	M7-17-428	B-428	Polyester	Lt Gray	1.000 (25.4)	0.500 (12.7)	500	M7-R4300
Fig. 2	M7-29-428	B-428	Polyester	Lt Gray	1.500 (38.1)	0.500 (12.7)	500	M7-R4300
Fig. 2	BM-20-428	B-428	Polyester	Lt Gray	2.000 (50.8)	1.000 (25.4)	1,000	M7-R4300
Fig. 2	M7-20-428	B-428	Polyester	Lt Gray	2.000 (50.8)	1.000 (25.4)	100	M7-R4300
Fig. 2	M7-26-428	B-428	Polyester	Lt Gray	2.750 (69.9)	1.250 (31.8)	100	M7-R4300
Fig. 2	M7-22-428	B-428	Polyester	Lt Gray	3.000 (76.2)	1.000 (25.4)	100	M7-R4300
Fig. 2	M7-38-428	B-428	Polyester	Lt Gray	4.000 (101.6)	1.900 (48.3)	100	M7-R4300
Fig. 2	M7C-500-428	B-428	Polyester	Lt Gray	0.500 (12.7)	50 ft. (15.24 m)	1 roll (cont.)	M7-R4300

Polyimide Circuit Board Labels (B-724 and B-797)

Various materials for PCBs, electronic components and more.

- **B-724 Matte Amber Ultra Heat Resistant Polyimide Labels:** Amber matte polyimide with permanent adhesive; can survive on the top or bottom side of PCBs through the solder process
- **B-797 Heat Resistant Polyimide Labels:** White glossy polyimide with permanent adhesive; can survive through the solder process




Figure 2



Figure	Catalog #	B#	Material	Color	Label width A inch (mm)	Label height B inch (mm)	Labels per roll	Rec. ribbon
B-724 Matte Polyimide Material								
Fig. 2	M7-9-724	B-724	Polyimide	Amber	0.650 (16.5)	0.200 (5.1)	750	M7-R4300
Fig. 2	M7-13-724	B-724	Polyimide	Amber	0.900 (22.9)	0.250 (6.4)	750	M7-R4300
Fig. 2	M7-16-724	B-724	Polyimide	Amber	1.000 (25.4)	0.375 (9.5)	500	M7-R4300
Fig. 2	M7-17-724	B-724	Polyimide	Amber	1.000 (25.4)	0.500 (12.7)	500	M7-R4300
Fig. 2	M7-28-724	B-724	Polyimide	Amber	1.500 (38.1)	0.250 (6.4)	750	M7-R4300
B-797 Glossy Polyimide Material								
Fig. 2	M7-10-797	B-797	Polyimide	White	0.750 (19.1)	0.250 (6.4)	750	M7-R6300
Fig. 2	M7-16-797	B-797	Polyimide	White	1.000 (25.4)	0.375 (9.5)	500	M7-R6300

Electrostatic Dissipative Labels (B-473, B-767 and B-768)

Low-profile polyimide and polyester materials that have static dissipative properties. Primarily used for circuit board and electronic component labeling.

- **B-473 Electrostatic Dissipative Polyester Material:** White glossy polyester with a permanent static dissipative adhesive and liner
- **B-767 Electrostatic Dissipative Polyimide Material:** High-temperature white glossy polyimide material (2 mil) with a permanent static dissipative adhesive and liner for PCB identification
- **B-768 Electrostatic Dissipative Polyimide Material:** High-temperature low-profile white glossy polyimide material (1 mil) with a permanent static dissipative adhesive and liner for PCB identification




Figure 2



Figure	Catalog #	B#	Material	Color	Label width A inch (mm)	Label height B inch (mm)	Labels per roll	Rec. ribbon
B-473 Glossy White Polyester								
Fig. 2	* M7-6-473	B-473	Polyester	White	0.500 (12.7)	0.275 (7.0)	750	M7-R6000
Fig. 2	* M7-9-473	B-473	Polyester	White	0.650 (16.5)	0.200 (5.1)	750	M7-R6000
Fig. 2	* M7-10-473	B-473	Polyester	White	0.750 (19.1)	0.250 (6.4)	750	M7-R6000
Fig. 2	* M7-16-473	B-473	Polyester	White	1.000 (25.4)	0.375 (9.5)	500	M7-R6000
Fig. 2	* M7-17-473	B-473	Polyester	White	1.000 (25.4)	0.500 (12.7)	500	M7-R6000
Fig. 2	* M7-28-473	B-473	Polyester	White	1.500 (38.1)	0.250 (6.4)	750	M7-R6000
B-767 Glossy White Static Dissipative Polyimide								
Fig. 2	* M7-2-767	B-767	Polyimide	White	2.000 (50.8)	0.250 (6.4)	100	M7-R6300
B-768 Glossy White Low Profile Static Dissipative Polyimide								
Fig. 2	* M7-4-768	B-768	Polyimide	White	0.400 (10.2)	0.400 (10.2)	500	M7-R6300
Fig. 2	* M7-9-768	B-768	Polyimide	White	0.650 (16.5)	0.200 (5.1)	750	M7-R6300
Fig. 2	* M7-25-768	B-768	Polyimide	White	1.250 (31.8)	0.250 (6.4)	750	M7-R6300

*

WARNING: Cancer www.P65Warnings.ca.gov

Metallized Polyester Labels (B-435)

Glossy Metallized Polyester has a permanent acrylic-based adhesive. It withstands numerous solvents while maintaining excellent image quality. Service temp: -40 to 194° F (-40 to 90° C). UL, CSA recognized.




Figure 2



Figure	Catalog #	B#	Material	Color	Label width A inch (mm)	Label height B inch (mm)	Labels per roll	Rec. ribbon
Fig. 2	M7-17-435	B-435	Metallized polyester	Silver	1.000 (25.4)	0.500 (12.7)	500	M7-R6000
Fig. 2	M7-30-435	B-435	Metallized polyester	Silver	1.500 (38.1)	0.750 (19.1)	250	M7-R6000
Fig. 2	M7-31-435	B-435	Metallized polyester	Silver	1.500 (38.1)	1.000 (25.4)	250	M7-R6000
Fig. 2	M7-37-435	B-435	Metallized polyester	Silver	3.000 (76.2)	1.900 (48.3)	100	M7-R6000
Fig. 2	M7-20-435	B-435	Metallized polyester	Silver	1.000 (25.4)	2.000 (50.8)	100	M7-R6000