



PRODUCT, WIRE, CABLE & INDUSTRIAL

IDENTIFICATION

BradyID.com

High-performance
labeling solutions
for the harshest
environments



3" Core Materials - Tamper-Indicating

B-438 Checkerboard Footprint Polyester Material

Color: Silver **Finish:** Matte

Metallized polyester label with matte finish. Leaves a checkerboard footprint on the surface when removed; the pattern also appears on the top of the label to prevent it from being reused. Applications include rating and serial plates or any other application where evidence of label removal is desired.

Performance Attributes:    




Figure 1




Figure 2




Figure 3



Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horiz. Repeat C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 1	THT-12-438-10	Polyester	Silver	0.500 (12.7)	0.437 (11.1)	0.662 (16.8)	0.537 (13.6)	3.350 (85.1)	5	10,000	R4307
Fig. 1	THT-14-438-10	Polyester	Silver	0.650 (16.5)	0.200 (5.1)	0.700 (17.8)	0.300 (7.6)	2.950 (74.9)	4	10,000	R4300
Fig. 1	THT-1-438-10	Polyester	Silver	0.750 (19.1)	0.250 (6.4)	0.800 (20.3)	0.350 (8.9)	3.350 (85.1)	4	10,000	R4307
Fig. 1	THT-5-438-10	Polyester	Silver	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	10,000	R4307
Fig. 1	THT-37-438-10	Polyester	Silver	1.500 (38.1)	0.500 (12.7)	1.650 (41.9)	0.600 (15.2)	3.350 (85.1)	2	10,000	R4307
Fig. 1	THT-6-438-10	Polyester	Silver	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	2	10,000	R4307
Fig. 2	THT-17-438-3	Polyester	Silver	2.000 (50.8)	1.000 (25.4)	-	1.125 (28.6)	2.200 (55.9)	1	3,000	R4302
Fig. 2	THT-53-438-3	Polyester	Silver	2.000 (50.8)	0.500 (12.7)	-	0.600 (15.2)	2.200 (55.9)	1	3,000	R4302
Fig. 2	THT-7-438-3	Polyester	Silver	2.750 (69.9)	1.250 (31.8)	-	1.375 (34.9)	2.950 (74.9)	1	3,000	R4300
Fig. 2	THT-18-438-3	Polyester	Silver	3.000 (76.2)	1.000 (25.4)	-	1.125 (28.6)	3.200 (81.3)	1	3,000	R4300
Fig. 2	THT-19-438-1	Polyester	Silver	3.000 (76.2)	2.000 (50.8)	-	2.125 (54.0)	3.200 (81.3)	1	1,000	R4300
Fig. 3	THT-21-438	Polyester	Silver	3.000 (76.2)	300 ft. (91.4 m)	-	300 ft. (91.4 m)	3.200 (81.3)	1	1 Roll Cont.	R4300

Custom Label Materials

B-335 VOID Footprint Polyester Material

B-335 is a super clear tamper-indicating label material that leaves a dry footprint (no sticky residue) when the label is removed. Upon attempted removal, the material layers split showing a hologram and VOID wallpaper pattern. In addition, the label cannot be stuck back down or reused. This non-typical tamper label material is ideal for an assortment of business issues where visible evidence of product opening or tampering is required.



B-366 Polypropylene

B-366 polypropylene material features diamonds with a clean removability coating that prevents any footprint or residue from being left behind. It's ideal for an improved consumer experience when opening a package or preserving package integrity for reuse when repackaging or inspecting a packaged product is required.



Contact Brady for more information about these custom materials.

3" Core Materials - Tamper-Indicating

B-7546 VOID Footprint Polyester Material

Color: White **Finish:** Gloss

White polyester tamper-indicating material with glossy finish. Leaves a "VOID" footprint when label is removed to prevent it from being reused. The adhesive does not allow for repositioning and requires minimal handling in order to prevent a premature "VOID" pattern.

Performance Attributes: 




Figure 1




Figure 2



Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Horiz. Repeat C Inch (mm)	Vert. Repeat D Inch (mm)	Web Width E Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 1	THT-5-7546-10	Polyester	White	1.000 (25.4)	0.500 (12.7)	1.075 (27.3)	0.600 (15.2)	3.350 (85.1)	3	10,000	R6007
Fig. 2	THT-59-7546-10	Polyester	White	1.000 (25.4)	0.500 (12.7)	-	0.600 (15.2)	1.200 (30.5)	1	10,000	R6006
Fig. 1	THT-37-7546-10	Polyester	White	1.500 (38.1)	0.500 (12.7)	1.650 (41.9)	0.600 (15.2)	3.350 (85.1)	2	10,000	R6007
Fig. 1	THT-6-7546-10	Polyester	White	1.500 (38.1)	0.750 (19.1)	1.650 (41.9)	0.875 (22.2)	3.350 (85.1)	2	10,000	R6007
Fig. 2	THT-53-7546-3	Polyester	White	2.000 (50.8)	0.500 (12.7)	-	0.600 (15.2)	2.200 (55.9)	1	3,000	R6000
Fig. 2	THT-17-7546-3	Polyester	White	2.000 (50.8)	1.000 (25.4)	-	1.125 (28.6)	2.200 (55.9)	1	3,000	R6000
Fig. 2	THT-7-7546-3	Polyester	White	2.750 (69.9)	1.250 (31.8)	-	1.375 (34.9)	2.950 (74.9)	1	3,000	R6002
Fig. 2	THT-18-7546-3	Polyester	White	3.000 (76.2)	1.000 (25.4)	-	1.125 (28.6)	3.200 (81.3)	1	3,000	R6002
Fig. 2	THT-19-7546-1	Polyester	White	3.000 (76.2)	2.000 (50.8)	-	2.125 (54.0)	3.200 (81.3)	1	1,000	R6002

B-7566 VOID Footprint Clear Polyester Material

Color: Clear **Finish:** Gloss

A clear polyester tamper-indicating material with a glossy finish, used for any application requiring high performance with evidence of label removal. Designed to leave a "VOID" footprint when the label is removed. A "VOID" pattern will appear on the top surface of the label to prevent reuse. The adhesive nature of this product does not allow for repositioning and requires minimal handling in order to prevent prematurely exposed VOID pattern.

Performance Attributes: 




Figure 1




Figure 2



Diagram	Catalog #	Material	Color	Label Width A Inch (mm)	Label Height B Inch (mm)	Labels Per Row	Labels Per Pkg	Rec. Ribbon
Fig. 1	THT-149-7566-10	Polyester	Clear	0.500 (12.7)	0.500 (12.7)	4	10,000	R4400, R6000
Fig. 1	THT-39-7566-10	Polyester	Clear	1.000 (25.4)	0.500 (12.7)	3	10,000	R4400, R6000
Fig. 1	THT-147-7566-10	Polyester	Clear	1.500 (38.1)	0.375 (9.5)	2	10,000	R4400, R6000
Fig. 2	THT-17-7566-3	Polyester	Clear	2.000 (50.8)	1.000 (25.4)	1	3,000	R4400, R6000
Fig. 2	THT-7-7566-3	Polyester	Clear	2.750 (69.9)	1.250 (31.8)	1	3,000	R4400, R6000
Fig. 2	THT-18-7566-3	Polyester	Clear	3.000 (76.2)	1.000 (25.4)	1	3,000	R4400, R6000