9000 Series Power Toggle Switches

Features/Benefits

- Power ratings up to 10 AMPS
- Double pole models
- Locking lever options available
- Wide variety of actuator styles
- RoHS compliant and compatible

Typical Applications

- Shut-off switch
- Small equipment







Specifications

CONTACT RATING: 9201 Model: 6 AMPS @ 120 V AC or 28 V DC; 3 AMPS @ 250 V AC. 9221 Model: 10 AMPS @ 125 V AC or 28 V DC; 5 AMPS @ 250 V AC.

ELECTRICAL LIFE: 25,000 make-and-break cycles at full load. CONTACT RESISTANCE: Below 10 m Ω typ. initial @

2-4 V DC, 100 mA.

INSULATION RESISTANCE: $10^9 \Omega$ min.

DIELECTRIC STRENGTH: 2,500 Vrms min. @ sea level.

OPERATING TEMPERATURE: -30°C to 85°C.

SOLDERABILITY: Per MIL-STD-202F method 208D, or EIA RS-186E method 9 (1 hour steam aging).

NOTE: Any models supplied with Q contact material are RoHS compliant and compatible.

NOTE: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

Materials

CASE: Diallyl phthalate (DAP) (UL 94V-0). ACTUATOR: Brass, chrome plated. BUSHING: Brass or zinc, nickel plated.

HOUSING: Stainless steel.

SWITCH SUPPORT: Brass or steel, matte-tin plated. END CONTACTS: 9201 Model: Coin silver, silver plated.

9221 Model: Silver cadmium oxide.

CENTER CONTACTS: Copper alloy, silver plated

ALL TERMINALS: 9201 Model: Copper alloy, silver plated.

9221 Model: Copper alloy, matte-tin plated.


TERMINAL SEAL: Epoxy.

HARDWARE: Nut & Locking ring: Brass, nickel plated.

Lockwasher: Steel, nickel plated.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages G-49 thru G-53. For additional options not shown in catalog, consult Customer Service Center.










SWITCH FUNCTION



^{*} See CONTACT MATERIAL, page G-52, for complete ratings.


All 9000 Series models meet international dimensional and electrical requirements. Representational dimensional and electrical requirements.


9221 model must be ordered with Z4 terminations and D seal option.

	ACTUATOR FINISH
ACTUATOR	
	ACTUATOR

S ANTIROTATION, .410" HIGH

P3 FLATTED, ANTIROTATION, .450" HIGH






OPTION CODE	ACTUATOR FINISH
NONE	NATURAL ALUMINUM—With Nickel Plated Bushing
2	BLACK


NOTE: Black hardware is supplied when either black actuators or bushings are specified. All hardware is available separately, see Section O.


Antirotation is standard on all actuators, provides 'anti-push-in' feature on actuator.

Dress nut part number: 709901201 supplied standard with P3 actuator.

T .687" HIGH, 15/32 BUSHING







OPTION CODE	ACTUATOR FINISH
NONE	BRIGHT CHROME—With Nickel Plated Bushing
2	BLACK

 $\ensuremath{\text{NOTE}}\xspace$: Bushing option code not required for T & T1 actuators unless CW splashproof bushing ordered.

Black hardware is supplied when either black actuators or bushings are specified. All hardware is available separately, see Section O.

Antirotation is standard on all actuators except T & T1, provides 'anti-push-in' feature on actuator.



Dimensions are shown: Inch (mm) Specifications and dimensions subject to change









ACTUATOR -----

LOCKING LEVER, .650" HIGH, THREADED

K1 LOCKING LEVER, .680" HIGH, THREADED







2 Position Lock


NOTE: To prevent accidental actuation, toggles must be lifted before being actuated. When released, toggles again lock in place. Bushing option code not required. Overtightening mounting nut may cause actuator to bind.

OPTION CODE	ACTUATOR CAP FINISH
NONE	NATURAL ALUMINUM-With Nickle Plated Bushing
2	BLACK ANODIZED ALUMINUM

L40 LEVER HANDLE WITHOUT CAP



L43 PLASTIC LEVER HANDLE WITH ANTIROTATION AND CAP, P/N 4812



OPTION CODE	ACTUATOR CAP COLOR
2	BLACK
NONE	No Actuator Color (L40 option)

Other colors available, consult Customer

No color choice required.


NOTE: Lever handle actuator L43 supplied, but not installed. For interchangeability, order L40 actuator option and order lever handles separately, see page G-53. Antirotation is standard on all actuators, provides 'anti-push-in' feature.


BUSHING


H3 .296" HIGH, THREADED, KEYWAY

.296" HIGH, THREADED, FLAT


SPLASHPROOF, 15/32 BUSHING









Finish: Matte







OPTION CODE	BUSHING FINISH		
NONE	NICKEL		
2	BLACK		

Will withstand 12 in./lbs. of torque with no distortion.

NOTE: Two mounting nuts, locking ring and lockwasher supplied standard with threaded bushings. Black hardware is supplied when either black bushings or actuators are specified. Optional mounting nut and locking ring styles and finishes available, see Section O.

Internal actuator seal standard. External bushing seal washer available separately, order from: Multi-Flex Seals, Inc., Hackensack, NJ. Part number: MFS-60064.


For T & T1 actuators only.




Dimensions are shown: Inch (mm)

Specifications and dimensions subject to change








9201 Only

NOTE: Terminal bend radii and lead-in manufacturing option. Terminal spacing greater than 3mm at all points.



Terminal Nos. For Reference Only





Dimensions are shown: Inch (mm) Specifications and dimensions subject to change

CONTACT MATERIAL



OPTION CODE	MODEL	CONTACT MATERIAL	TERMINAL PLATING	RATINGS	
	9201	SILVER 1,2	SILVER OR TIN ^{2,5}	POWER	6 AMPS @120 V AC OR 28 V DC; 3 AMPS @ 250 V AC.
Q	9221 :	SILVER CADMIUM OXIDE 3,4,6	TIN ⁵		10 AMPS @125 V AC OR 28 V DC; 5 AMPS @ 250 V AC.

^{*} Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

- ¹ END CONTACTS: Coin silver, silver plated.
- 2 CENTER CONTACTS & ALL TERMINALS: Copper alloy, silver plated.
- ³ END CONTACTS: Silver cadmium oxide.
- ⁴ CENTER CONTACTS: Copper alloy, silver plated.
- ⁵ Z4 TERMINALS ONLY: Copper alloy, matte-tin plated.
- ⁶ Cadmium in electrical switch contacts is exempt from RoHS.

NOTE: Any models supplied with Q contact material are RoHS compliant.

All 9000 Series models meet international dimensional and electrical requirements. (a) 1000 Series model must be ordered with Z4 terminations and D seal option.



Not available with 9221 model or Z4 terminations.

Must be ordered with 9221 model and Z4 termination.

AVAILABLE HARDWARE

Cap Compatible with S actuator



PART NO. 896801000 WHITE 896802000 BLACK 896803000 RED

Material: Polyethylene Finish: Matte

Cap Compatible with S actuator



PART NO.

706201000 WHITE 706202000 BLACK 706203000 RED

Material: Vinyl Finish: Matte

L43 Actuator




PART NO. 481202000 BLACK

481203000 RED

Material: Nylon Finish: Matte **NOTE:** Additional nuts, locking rings and lockwashers available separately, see Section O.


Other colors available, consult Customer Service Center.

759D02000 Sealing Boot




NOTE: For use with S actuator style when combined with H3 and H bushings

703D02000 Sealing Boot




NOTE: For use with T style actuator

704D02000 Sealing Boot



NOTE: For use with T style actuator



Dimensions are shown: Inch (mm) Specifications and dimensions subject to change

