


1N5283 THRU 1N5314

SILICON CURRENT LIMITING DIODE



www.centrasemi.com



DO-35 CASE

DESCRIPTION:

The CENTRAL SEMICONDUCTOR 1N5283 series types are silicon field effect current regulator diodes designed for applications requiring a constant current over a wide voltage range. These devices are manufactured in the cost effective DO-35 double plug case which provides many benefits to the user, including space savings and improved thermal characteristics. Special selections of I_p (regulator current) are available for critical applications.

FEATURES:

- High Reliability
- Superior Lot To Lot Consistency
- Special Selections Available
- Surface Mount Devices Available

MAXIMUM RATINGS: ($T_L=75^\circ\text{C}$)

Peak Operating Voltage
 Power Dissipation
 Operating and Storage Junction Temperature

SYMBOL

P_{OV} 100
 P_D 600
 T_J, T_{stg} -65 to +200

UNITS

V
 mW
 $^\circ\text{C}$

ELECTRICAL CHARACTERISTICS: ($T_A=25^\circ\text{C}$)

Type	Regulator Current (Note 1) $I_p @ V_T=25\text{V}$			Minimum Dynamic Impedance $Z_T @ V_T=25\text{V}$	Minimum Knee Impedance $Z_K @ V_K=6.0\text{V}$	Maximum Limiting Voltage $V_L @ I_L=0.8 \times I_p \text{ MIN}$
	MIN mA	NOM mA	MAX mA	MΩ	MΩ	V
1N5283	0.198	0.22	0.242	25	2.75	1.0
1N5284	0.216	0.24	0.264	19	2.35	1.0
1N5285	0.243	0.27	0.297	14	1.95	1.0
1N5286	0.270	0.30	0.330	9.0	1.60	1.0
1N5287	0.297	0.33	0.363	6.6	1.35	1.0
1N5288	0.351	0.39	0.429	4.1	1.00	1.05
1N5289	0.387	0.43	0.473	3.3	0.87	1.05
1N5290	0.423	0.47	0.517	2.7	0.75	1.05
1N5291	0.504	0.56	0.616	1.90	0.56	1.10
1N5292	0.558	0.62	0.682	1.55	0.47	1.13
1N5293	0.612	0.68	0.748	1.35	0.40	1.15
1N5294	0.675	0.75	0.825	1.15	0.335	1.20
1N5295	0.738	0.82	0.902	1.00	0.29	1.25
1N5296	0.819	0.91	1.001	0.88	0.24	1.29
1N5297	0.900	1.00	1.10	0.80	0.205	1.35
1N5298	0.990	1.10	1.21	0.70	0.18	1.40

Notes: (1) Pulsed Method: Pulse Width (ms) = 27.5 divided by $I_p \text{ NOM (mA)}$

R3 (24-May 2010)


1N5283 THRU 1N5314
SILICON CURRENT LIMITING DIODE



ELECTRICAL CHARACTERISTICS - Continued: ($T_A=25^\circ\text{C}$)

Type	Regulator Current (Note 1) $I_P @ V_T=25V$			Minimum Dynamic Impedance $Z_T @ V_T=25V$	Minimum Knee Impedance $Z_K @ V_K=6.0V$	Maximum Limiting Voltage $V_L @ I_L=0.8 \times I_P \text{ MIN}$
	MIN mA	NOM mA	MAX mA	MΩ	MΩ	V
1N5299	1.08	1.20	1.32	0.640	0.155	1.45
1N5300	1.17	1.30	1.43	0.580	0.135	1.50
1N5301	1.26	1.40	1.54	0.540	0.115	1.55
1N5302	1.35	1.50	1.65	0.510	0.105	1.60
1N5303	1.44	1.60	1.76	0.475	0.092	1.65
1N5304	1.62	1.80	1.98	0.420	0.074	1.75
1N5305	1.80	2.00	2.20	0.395	0.061	1.85
1N5306	1.98	2.20	2.42	0.370	0.052	1.95
1N5307	2.16	2.40	2.64	0.345	0.044	2.00
1N5308	2.43	2.70	2.97	0.320	0.035	2.15
1N5309	2.70	3.00	3.30	0.300	0.029	2.25
1N5310	2.97	3.30	3.63	0.280	0.024	2.35
1N5311	3.24	3.60	3.96	0.265	0.020	2.50
1N5312	3.51	3.90	4.29	0.255	0.017	2.60
1N5313	3.87	4.30	4.73	0.245	0.014	2.75
1N5314	4.23	4.70	5.17	0.235	0.012	2.90

DO-35 CASE - MECHANICAL OUTLINE



SYMBOL	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.018	0.022	0.46	0.56
B	0.120	0.200	3.05	5.08
C	0.060	0.090	1.52	2.29
D	1.000	-	25.40	-

DO-35 (REV: R1)

R1

R3 (24-May 2010)