LEAD FREE **COMPATIBLE OPTION**

ELUM™ Series Right Angle Illuminated Latching Pushbutton

Features/Benefits

- SPDT (N.O. & N.C.)
- Low height above PCB
- Reliable self-cleaning contact
- Surface-mount or thru-hole PCB
- Standard or custom actuator
- Central LED illumination
- Latching or Momentary
- Long travel. Smooth feel
- RoHS compliant and compatible

Typical Applications

- Telecom network equipment
- Automotive electronics
- Consumer electronics
- Computer, server, modem, data storage
- Professional instrumentation, medical

Patent Numbers 6.974.924 B2 US EP1583118B1 Europe





Materials

FIXED CONTACTS AND TERMINALS: Stainless steel, silver plated with gold flash (STD.)

MOVABLE CONTACTS: Copper alloy, silver plated with gold flash (STD.)

BASE: Glass filled LCP (UL94V-0)

ACTUATOR: Glass filled nylon 4/6 (UL94V-0)

COVER: Stainless steel

Electrical

MAXIMUM POWER: 3.5 VA

MIN./MAX. VOLTAGE: 20 mV - 50 VDC MIN./MAX. CURRENT: 0.01 mA - 250 mA DIELECTRIC STRENGTH: ≥ 250 Vrms CONTACT RESISTANCE: $\leq 50 \text{ m}\Omega$ INSULATION RESISTANCE: ≥ 10° Ω

BOUNCE TIME: <1 ms

LED SPECIFICATIONS: See page A-5

Mechanical

OPERATING FORCE: 2.5 N at Full Travel SWITCHING TRAVEL: .067" (1.7 mm) LATCH TRAVEL: .131" (3.6 mm) FULL TRAVEL: .200" (5.1 mm)

Operating Environment

OPERATING TEMPERATURE: -40°C TO 80°C. STORAGE TEMPERATURE: -40°C TO 80°C RELATIVE HUMIDITY: 90% R.H. @ 80°C. OPERATING LIFE: 30,000 Cycles. VIBRATION: Per EIA 186-E Methods 7 & 8 MECHANICAL SHOCK: Per EIA 186-E Method 12. OVERLOAD: Withstands 40 N for 1 minute without damage

Process Environment

SOLDERABILITY: According to Mil STD 202F Method 208D or EIA RS-

186E Method 9.

LEAD FREE PROCESS COMPATIBLE: 260°C peak, 10 seconds Max.

above 250° C.

WASHING PROCESS: No clean process compatible (SMT)

Bottom wash compatible (Thru-hole) SHEAR TEST (SWITCH/PCB): > 40 N

Packaging

"SA" Terminal Style SMT: Tape and reel per EIA 481-2 (450/reel)


"TH" Terminal Style PC: Tray (60/tray)

NOTE: Any models supplied with Q, contact material are RoHS compliant

NOTE: Specifications and materials listed above are for switches with standard options For information on specific and custom switches, please contact Customer Service

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box.





Dimensions are shown: Inches (mm) Specifications and dimensions subject to change


LED Bi-Color - Amber (Green)




ELUM™ Series Right Angle Illuminated Latching Pushbutton

STANDARD OPTIONS

ELUMEESAQ7C12





ELUMOATHQ6C12



ELUMEESAQ3C22







ACTUATOR SHOWN EXTENDED POSITION

DESIGNATION ELUM------

ELUM ELUM SERIES, Illuminated Latching Pushbutton

SWITCH FUNCTION -----

	POSITION 1			POSITION 2		SCHEMATIC
OPTION CODE	NO. OF POLES	SWITCH FUNCTION	CONNECTED TERMINALS	SWITCH FUNCTION	CONNECTED TERMINALS	3 C 4 NC NO 2
OA	SP Momentary	ON	3 – 4	ON (Mom.)	3 – 2	SPDT 5 1
EE	SP Latching (Push-Push)	ON	3 – 4	ON	3 – 2	+ Anode - Cathode


For SPST N.O. function, only terminals 3 & 2 are used. For SPST N.C. function, only terminals 3 & 4 are used.

Circuit: Make before break

LED pins 1 & 5 are independent of switch function.

NOTF:

For bi-color LED's the polarity must be reversed to alternate the color









Dimensions are shown: Inches (mm) Specifications and dimensions subject to change

ELUM™ Series Right Angle Illuminated Latching Pushbutton




SA RIGHT ANGLE, SURFACE MOUNT






Terminal 5 = LED Anode

TH RIGHT ANGLE, PC THRU-HOLE





Terminal 5 = LED Anode

CONTACT MATERIAL



* Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

FIXED CONTACTS AND TERMINALS: Stainless steel, silver plated with gold flash MOVABLE CONTACTS: Copper alloy, silver plated with gold flash


NOTE: Any models supplied with Q, contact material are RoHS compliant.

ILLUMINATION ----------------

OPTION CODE	ILLUMINATION TYPE	TYPICAL INTENSITY* MIN MAX		PEAK WAVELENGTH	VIEWING ANGLE
		(mcd)		(nm)	
(NONE)	Model without illumination	N/A		N/A	N/A
1	LED Super White	4,000	5,000	N/A	30°
2	LED Bi-Color – Red (Green)	10	20	635/565	60°
3	LED Red	4	8	700	60°
5	LED Amber	35	50	610	60°
6	LED Green	35	50	565	60°
7	LED Super Blue	800	1,500	470	22°
8	LED Bi-Color – Amber (Green)	10	10	585/565	60°

*LED FORWARD CURRENT: 20 mA LED FORWARD VOLTAGE: 2.0 V TYP. LED REVERSE VOLTAGE: 5.0 V MAX









^{*} For information on specific and custom LED, please contact Customer Service.




ELUM™ Series Right Angle Illuminated Latching Pushbutton






C12 BLACK WITH WINDOW



C22 BLACK WITH WINDOW AND SNAP FEATURE TO ACCEPT CUSTOM CAP




^{*} Custom actuators available, please contact Customer Service.

FORCE TRAVEL DIAGRAM

FORCE FULL ACTUATION FORCE 250g± 75g FULL ACTUATION NO ACTUATION SWITCH N.O. ACTUATOR POSITION ACTUATOR POSITION .067 ± .020 1,7 ± 0.5mm SWITCH .131 ± .020 FULL ACTUATION .200 ± .020

TAPE & REEL





Dimensions are shown: Inches (mm) Specifications and dimensions subject to change



AVAILABLE HARDWARE

Сар



Сар



Сар



PART NO.

957C00000 High temperature black cap with universal standby symbol

956C02000 High temperature black cap with no symbol

Material: 4/6 Nylon SMT compatible

PART NO.


181D01000 Paint and Laser Etched with black paint and universal standby symbol

Material: Clear polycarbonate

PART NO.

181D00000 Paint and laser etched with white paint underlay and black paint with universal standby symbol.

Material: Clear polycarbonate



NOTE: Caps are for use with the C22 actuator style. Other colors and symbols available, consult Customer Service Center.



Dimensions are shown: Inches (mm) Specifications and dimensions subject to change





ELUM™ Series Right Angle Illuminated Latching Pushbutton

CAP INSTALLATION

