



	PLA140L	Units
Load Voltage	400	V
Load Current	200	mA
Max R _{ON}	13	Ω

Features

- Small 6 Pin DIP Package
- Low Drive Power Requirements (TTL/CMOS Compatible)
- No Moving Parts
- High Reliability
- Arc-Free With No Snubbing Circuits
- 3750V_{RMS} Input/Output Isolation
- No EMI/RFI Generation
- Machine Insertable, Wave Solderable
- Surface Mount and Tape & Reel Versions Available
- Flammability classification rating of V-0


Applications

- Instrumentation
 - Multiplexers
 - Data Acquisition
 - Electronic Switching
 - I/O Subsystems
 - Meters (Watt-Hour, Water, Gas)
- Medical Equipment—Patient/Equipment Isolation
- Security
- Aerospace
- Industrial Controls
- Automotive

Pin Configuration


PLA140L Pinout

AC/DC Configuration



PLA140L Pinout

DC Only Configuration



Description

PLA140L is a 1-Form-A solid state relay which uses optically coupled MOSFET technology to provide 3750V of input to output isolation. The efficient MOSFET switches and photovoltaic die use Clare's patented Optomos architecture. The optically-coupled input is controlled by a highly efficient GaAlAs infrared LED. The PLA140L also contains a built in load current limiting feature. This combined with a low on resistance and very high load current handling capabilities makes it suitable for a variety of high performance switching applications.


Approvals

- UL Recognized: File Number E76270
- CSA Certified: File Number LR 43639-10
- BSI Certified to:
 - EN 60950
 - EN 41003
 - IEC 950
 - AS/NZS 3260

Ordering Information

Part #	Description
PLA140L	6 Pin DIP (50/Tube)
PLA140LS	6 Pin Surface Mount (50/Tube)
PLA140LSTR	6 Pin Surface Mount (1000/Reel)

Switching Characteristics of Normally Open (Form A) Devices





PLA140L

Absolute Maximum Ratings (@ 25° C)

Parameter	Min	Typ	Max	Units
Input Power Dissipation	-	-	150 ¹	mW
Input Control Current	-	-	50	mA
Peak (10ms)	-	-	1	A
Reverse Input Voltage	-	-	5	V
Total Power Dissipation	-	-	800 ²	mW
Isolation Voltage Input to Output	3750	-	-	V _{RMS}
Operational Temperature	-40	-	+85	°C
Storage Temperature	-40	-	+125	°C
Soldering Temperature DIP Package	-	-	+260	°C
Surface Mount Package (10 Seconds Max.)	-	-	+220	°C

¹ Derate Linearly 1.33 mw/°C

² Derate Linearly 6.67 mw/°C


Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at these or any other conditions beyond those indicated in the operational sections of this data sheet is not implied. Exposure of the device to the absolute maximum ratings for an extended period may degrade the device and effect its reliability.

Electrical Characteristics


Parameter	Conditions	Symbol	Min	Typ	Max	Units
Output Characteristics @ 25°C						
Load Voltage (Peak)	-	V _L	-	-	400	V
Load Current (Continuous)						
AC/DC Configuration	-	I _L	-	-	200	mA
DC Configuration	-	I _L	-	-	350	mA
Peak Load Current	10ms	I _L	-	-	500	mA
On-Resistance						
AC/DC Configuration	I _L =200mA	R _{ON}	-	10	13	Ω
DC Configuration	I _L =350mA	R _{ON}	-	3	4	Ω
Off-State Leakage Current	V _L =400V	I _{LEAK}	-	-	1	μA
Switching Speeds						
Turn-On	I _F =5mA, V _L =10V	T _{ON}	-	-	5	ms
Turn-Off	I _F =5mA, V _L =10V	T _{OFF}	-	-	3	ms
Load current limit	I _F =5mA, T=25°C	I _{CL}	240	-	380	mA
Output Capacitance	50V; f=1MHz	C _{OUT}	-	65	-	pF
Input Characteristics @ 25°C						
Input Control Current	I _L =200mA	I _F	5	-	50	mA
Input Dropout Current	-	I _F	0.4	0.7	-	mA
Input Voltage Drop	I _F =5mA	V _F	0.9	1.2	1.4	V
Reverse Input Voltage	-	V _R	-	-	5	V
Reverse Input Current	V _R =5V	I _R	-	-	10	μA
Common Characteristics @ 25°C						
Input to Output Capacitance	-	C _{I/O}	-	3	-	pF

PERFORMANCE DATA*


PLA140L
Typical LED Forward Voltage Drop
(N=50 Ambient Temperature = 25°C;
I_F = 5mADC)




PLA140L
Typical On-Resistance Distribution
(N=50 Ambient Temperature = 25°C)
(Load Current = 200mADC; I_F = 5mADC)




PLA140L
Typical Blocking Voltage Distribution
(N=50 Ambient Temperature = 25°C)




PLA140L
Typical I_F for Switch Operation
(N=50 Ambient Temperature = 25°C)
(Load Current = 200mADC)




PLA140L
Typical I_F for Switch Dropout
(N=50 Ambient Temperature = 25°C)
(Load Current = 200mADC)




PLA140L
Typical Turn-On Time
(N=50 Ambient Temperature = 25°C)
(Load Current = 200mADC; I_F = 5mADC)




PLA140L
Typical Turn-Off Time
(N=50 Ambient Temperature = 25°C)
(Load Current = 200mADC; I_F = 5mADC)




PLA140L
Typical Load Current vs. Temperature




PLA140L
Typical Leakage vs. Temperature
(Measured across Pins 4 & 6)




PLA140L
Typical Blocking Voltage vs. Temperature



PLA140L
Typical Turn-On vs. Temperature
(Load Current = 200mADC)











PLA140L
Typical Turn-Off vs. Temperature
(Load Current = 200mADC)



* The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.


PERFORMANCE DATA*




* The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.

MECHANICAL DIMENSIONS


6Pin DIP Through Hole (Standard)




PC Board Pattern (Top View)




6Pin DIP Surface Mount ("S" Suffix)



PC Board Pattern (Top View)



Tape and Reel Packaging for 6 Pin Power DIP Surface Mount Package



Dimensions
mm
(inches)



CLARE

For additional information please visit our website at: www.clare.com

Clare, Inc. makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice. Neither circuit patent licenses nor indemnity are expressed or implied. Except as set forth in Clare's Standard Terms and Conditions of Sale, Clare, Inc. assumes no liability whatsoever, and disclaims any express or implied warranty, relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or infringement of any intellectual property right.

The products described in this document are not designed, intended, authorized or warranted for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or where malfunction of Clare's product may result in direct physical harm, injury, or death to a person or severe property or environmental damage. Clare, Inc. reserves the right to discontinue or make changes to its products at any time without notice.

Specification: DS-PLA140L-R4.0
©Copyright 2002, Clare, Inc.
OptoMOS[®] is a registered trademark of Clare, Inc.
All rights reserved. Printed in USA.
4/22/02