



Product Number: CY23FP120XC

Automotive Qualified	N
Output Signal Type	LVC MOS
Min. Operating Voltage (V)	3.13
Max. Operating Voltage (V)	3.45
Temp. Classification	Commercial
No. of PLL	1
Input Signal Type	LVC MOS/LVTTL
Input Frequency Max. (MHz)	200
Core Voltage (V)	3.3
Output Frequency Min. (MHz)	10
Input Frequency Min. (MHz)	10
Output Frequency Max. (MHz)	200
Spread Spectrum	N
No. of Outputs	12
I/O Voltage (V)	2.5/3.3
No. of Pins	28
Package Carrier	TUBE
Standard Pack Quantity	94
Minimum Order Quantity (MOQ)	94
Order Increment	94
Estimated Lead Time (days)	42
HTS Code	8542.31.0000
ECCN	EAR99
Moisture Sensitivity Level (MSL)	3
Peak Reflow Temp. (°C)	260
RoHS Compliant	Y
PB Free	Y
Lead/Ball Finish	Ni/Pd/Au, Pure Sn