



	CPC1135N	Units
Blocking Voltage	350	V
Load Current	120	mA
Max R _{ON}	35	Ω

Features

- Small 4 Pin SOP Package
- Low Drive Power Requirements (TTL/CMOS Compatible)
- No Moving Parts
- High Reliability
- Arc-Free With No Snubbing Circuits
- 1500V_{RMS} Input/Output Isolation
- No EMI/RFI Generation
- Machine Insertable, Wave Solderable
- Tape & Reel Version Available

Applications

- Telecommunications
 - Telecom Switching
 - Tip/Ring Circuits
 - Modem Switching (Laptop, Notebook, Pocket Size)
 - Hookswitch
 - Dial Pulsing
 - Ground Start
 - Ringing Injection
- Instrumentation
 - Multiplexers
 - Data Acquisition
 - Electronic Switching
 - I/O Subsystems
 - Meters (Watt-Hour, Water, Gas)
- Medical Equipment-Patient/Equipment Isolation
- Security
- Aerospace
- Industrial Controls

Description

The CPC1135N is a miniature 1-Form-B solid state relay which uses optically coupled MOSFET technology to provide 1500V of input to output isolation. The efficient MOSFET switches and photovoltaic die use Clare's patented OptoMOS® architecture. The optically-coupled input is controlled by a highly efficient GaAlAs infrared LED. The CPC1135N uses Clare's state of the art double molded vertical construction packaging to produce the world's smallest 4 pin SOP relay. The CPC1135N offers board space savings of at least 20% versus competitive 4 Pin SOP solid state relay.

Approvals


- UL Recognized Component: File #E76270
- Certified to EN60950

Ordering Information


Part #	Description
CPC1135N	4 Pin SOP (100/tube)
CPC1135NTR	4 Pin SOP (2,000/reel)

Pin Configuration

CPC1135N Pinout



Switching Characteristics of Normally Closed (Form B) Devices



Absolute Maximum Ratings (@ 25° C)

Parameter	Min	Typ	Max	Units
Input Power Dissipation	-	-	150	mW
Input Control Current	-	-	50	mA
Peak (10ms)	-	-	1	A
Reverse Input Voltage	-	-	5	V
Blocking Voltage	-	-	350	V
Total Power Dissipation	-	-	400 ¹	mW
Isolation Voltage Input to Output	-	-	1500	V _{RMS}
Operational Temperature	-40	-	+85	°C
Storage Temperature	-40	-	+125	°C
Soldering Temperature (10 Seconds Max.)	-	-	+220	°C

¹ Derate Linearly 3.33 mw / °C

Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.

Electrical Characteristics

Parameter	Conditions	Symbol	Min	Typ	Max	Units
Output Characteristics @ 25°C						
Load Current (Continuous)						
AC Peak ¹		I _L	-	-	120	mA
Peak Load Current	10ms	I _{LPK}	-	-	350	mA
On-Resistance ²	I _L =120mA	R _{ON}	-	-	35	Ω
Off-State Leakage Current	V _L =350V, I _F =2mA	I _{LEAK}	-	-	5	μA
Switching Speeds						
Turn-On	I _F =5mA, V _L =10V	T _{ON}	-	-	2.0	ms
Turn-Off	I _F =5mA, V _L =10V	T _{OFF}	-	-	2.0	ms
Output Capacitance	50V; f=1MHz	C _{OUT}	-	25	-	pF
Capacitance Input to Output	-	-	-	1	-	pF
Input Characteristics @ 25°C						
Input Control Current ³	I _L =120mA	I _F	2	-	50	mA
Input Dropout Current	-	I _F	0.3	0.9	-	mA
Input Voltage Drop	I _F =5mA	V _F	0.9	1.2	1.4	V
Reverse Input Current	V _R =5V	I _R	-	-	10	μA


¹ Load current derates linearly from 120mA @ 25°C to 85mA @ 85°C.

² Within 1 second of on time.


³ For applications requiring high temperature operation (greater than 60°C) an LED drive current of 5mA is recommended.

PERFORMANCE DATA*


CPC1135N
Typical LED Forward Voltage Drop
(Ambient Temperature = 25°C)
 $I_F = 5\text{mA}$




CPC1135N
Typical On-Resistance Distribution
(Ambient Temperature = 25°C)
(Load Current = 120mA)




CPC1135N
Typical Blocking Voltage Distribution
(Ambient Temperature = 25°C)




CPC1135N
Typical I_F for Switch Operation
(Ambient Temperature = 25°C)
(Load Current = 120mA)




CPC1135N
Typical I_F for Switch Dropout
(Ambient Temperature = 25°C)
(Load Current = 120mA)




CPC1135N
Typical Turn-On Time
(Ambient Temperature = 25°C)
(Load Current = 120mA; $I_F = 5\text{mA}$)




CPC1135N
Typical Turn-Off Time
(Ambient Temperature = 25°C)
(Load Current = 120mA; $I_F = 5\text{mA}$)




CPC1135N
Typical Load Current vs. Temperature
($I_F=0$, $I_L=AC$ Peak)




CPC1135N
Typical Leakage vs. Temperature
(Measured across Pins 3 & 4) $I_L = \text{max rated}$




CPC1135N
Typical Blocking Voltage vs. Temperature



CPC1135N
Typical Turn-On vs. Temperature
(Load Current = 50mA)










CPC1135N
Typical Turn-Off vs. Temperature
(Load Current = 50mA)



*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.

PERFORMANCE DATA*



*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.

