



| Parameter | Rating | Units |
|-----------------------|--------|----------------------------------|
| AC Operating Voltage | 260 | V_{rms} |
| Load Current | 1 | A_{rms} |
| On State Voltage Drop | 1.6 | V_{rms} (at $I_L = 1A_{rms}$) |

Features

- Load Current up to $1A_{rms}$
- $600V_p$ Blocking Voltage
- 5mA Sensitivity
- Zero-Crossing Detection
- DC Control, AC Output
- Optically Isolated
- TTL and CMOS Compatible
- Low EMI and RFI Generation
- High Noise Immunity
- Machine Insertable, Wave Solderable
- Flammability classification rating of V-0

Applications

- Programmable Control
- Process Control
- Power Control Panels
- Remote Switching
- Gas Pump Electronics
- Contactors
- Large Relays
- Solenoids
- Motors
- Heaters

Description

The CPC1965Y is an AC Solid State Switch using patented waveguide coupling with dual power SCR outputs to produce an alternative to optocoupler and Triac circuits. The switches are robust enough to provide a blocking voltage of up to $600V_p$. In addition, tightly controlled zero-cross circuitry ensures switching of AC loads without the generation of transients. The input and output circuits are optically coupled to provide $3750V_{rms}$ of isolation and noise immunity between control and load circuits. As a result, the CPC1965Y is well suited for industrial environments where electromagnetic interference could disrupt the operation of electromechanical relays.


Approvals

- UL Recognized Component: File # E69938
- CSA Certified Component: Certificate # 1172007

Ordering Information

| Part # | Description |
|----------|-----------------------------|
| CPC1965Y | 4-Lead, 8-Pin SIP (25/Tube) |

Pin Configuration



Absolute Maximum Ratings (@ 25° C)

| Parameter | Ratings | Units |
|--------------------------------------------|-------------|------------------|
| Blocking Voltage | 600 | V _P |
| Reverse Input Voltage | 5 | V |
| Input Control Current | 100 | mA |
| Peak (10ms) | 1 | A |
| Input Power Dissipation ¹ | 150 | mW |
| PD, Total Package Dissipation ² | 1600 | mW |
| Isolation Voltage Input to Output | 3750 | V _{rms} |
| Operational Temperature | -40 to +85 | °C |
| Storage Temperature | -40 to +125 | °C |

¹ Derate Linearly 1.33 mW/°C

² Derate Linearly 16.6 mW/°C

Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.

Electrical Characteristics

| Parameters | Conditions | Symbol | Min | Typ | Max | Units |
|-------------------------------------------------------|-----------------------------------------|-------------------|-------|-----|-----|------------------|
| Output Characteristics @ 25°C | | | | | | |
| Operating Voltage Range | V _L | - | 20 | - | 260 | V _{rms} |
| Load Current, Continuous | V _L =120-260V _{rms} | I _L | 0.005 | - | 1.0 | A _{rms} |
| Non-Repetitive Single Cycle Surge Current | - | I _{TSM} | - | - | 10 | A |
| Off State Leakage Current | V _L =600V _P | I _{LEAK} | - | - | 1 | mA |
| On-State Voltage Drop | I _L =1A _{rms} | - | - | - | 1.6 | V _{rms} |
| Critical Rate of Rise ³ | - | dV/dt | 1000 | - | - | V/μs |
| Switching Speeds | | | | | | |
| Turn-on | I _F =5 mA | t _{ON} | - | - | 0.5 | cycles |
| Turn-off | | t _{OFF} | - | - | 0.5 | |
| Zero-Cross Turn-On Voltage | 1st half cycle | - | - | 2 | 10 | V |
| | Subsequent half cycle | - | - | 1 | - | V |
| Operating Frequency ¹ | - | - | 20 | - | 400 | Hz |
| Load Power Factor for Guaranteed Turn-On ² | - | PF | 0.25 | - | - | - |
| Input Characteristics @ 25°C | | | | | | |
| Input Control Current ⁴ | - | I _F | - | 0.8 | 5 | mA |
| Input Voltage Drop | I _F =5mA | V _F | 0.9 | 1.2 | 1.4 | V |
| Input Drop-out Voltage | - | - | 0.8 | - | - | V |
| Reverse Input Current | V _R =5V | I _R | - | - | 10 | μA |
| Common Characteristics @ 25°C | | | | | | |
| Input to Output Capacitance | - | C _{I/O} | - | 3 | - | pF |

¹ Zero Cross 1st half cycle @ <100Hz


² Snubber circuits may be required at low power factors.

³ Tested in accordance with EIA/NARM standard RS-443.


⁴ For high noise environments, use I_F=10mA.

PERFORMANCE DATA*


Typical LED Forward Voltage Drop
($T_A=25^\circ\text{C}$, $I_F=5\text{mA}$)




Typical On-State Voltage
($T_A=25^\circ\text{C}$, $I_L=1\text{A}_{\text{rms}}$)




Typical Blocking Voltage Distribution
($T_A=25^\circ\text{C}$)




Typical I_F for Switch Operation
($T_A=25^\circ\text{C}$, $I_L=1\text{A}_{\text{rms}}$)




Typical I_F for Switch Operation vs. Temperature
($I_L=500\text{mA}_{\text{rms}}$)




Typical Leakage vs. Temperature
($V_L=600\text{V}_p$)




Typical Blocking Voltage vs. Temperature




Typical On-State Voltage vs. Temperature
($I_L=500\text{mA}_{\text{rms}}$)




Typical LED Forward Voltage vs. Temperature



Typical Maximum Load Current vs. Temperature



Maximum Surge Current (non-repetitive)
($T_J=50^\circ\text{C max}$)



*The Performance data shown in the graphs above is typical of device performance. For guaranteed parameters not indicated in the written specifications, please contact our application department.

Manufacturing Information

Soldering

For proper assembly, the component must be processed in accordance with the current revision of IPC/JEDEC standard J-STD-020. Failure to follow the recommended guidelines may cause permanent damage to the device resulting in impaired performance and/or a reduced lifetime expectancy.


Washing

Clare does not recommend ultrasonic cleaning or the use of chlorinated solvents.




MECHANICAL DIMENSIONS

4-Lead, 8-Pin, SIP Package



Recommended PCB Hole Pattern



Dimensions
mm
(inches)

For additional information please visit our website at: www.clare.com

Clare, Inc. makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice. Neither circuit patent licenses nor indemnity are expressed or implied. Except as set forth in Clare's Standard Terms and Conditions of Sale, Clare, Inc. assumes no liability whatsoever, and disclaims any express or implied warranty, relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or infringement of any intellectual property right.

The products described in this document are not designed, intended, authorized or warranted for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or where malfunction of Clare's product may result in direct physical harm, injury, or death to a person or severe property or environmental damage. Clare, Inc. reserves the right to discontinue or make changes to its products at any time without notice.

Specification: DS-CPC1965Y-R04
©Copyright 2008, Clare, Inc.
OptoMOS® is a registered trademark of Clare, Inc.
All rights reserved. Printed in USA.
9/16/08