


THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.

ISSUE NUMBER

ORIGINAL ①



SPECIFICATIONS:

- 1- CONTACT MATERIAL: COPPER ALLOY, GOLD PLATED ON CONTACT AREA, TIN ON TAILS
- 2- INSULATOR MATERIAL: THERMOPLASTIC POLYESTER, UL94V-0 BLACK COLOUR
- 3- CURRENT RATING: 3 AMPERES.
- 4- CONTACT RESISTANCE: 10 MILLIOHMS MAXIMUM.
- 5- INSULATION RESISTANCE: 5,000 MEGOHMS MINIMUM.
- 6- DIELECTRIC WITHSTANDING VOLTAGE: 1,200 VAC RMS AT SEA LEVEL.
- 7- INSERTION AND WITHDRAWAL FORCES: 16oz AND 1oz RESPECTIVELY PER CONTACT PAIR.
- 8- OPERATING TEMPERATURE: -40°C TO +125°C



**THIS SERIES FULLY CONFORMS TO THE
EUROPEAN UNION DIRECTIVES 2002/95/EC
AND 2002/96/EC FOR RoHS COMPLIANCY.**

36 PINS CARD
EDGE CONNECTOR 90° BEND

ACAD REFERENCE NO. 395-036-558-201

DRAWN: F.BRIONES DATE: NOV. 27/00

PART NUMBER
395-036-558-201

DRAWING NUMBER
395-036-558-201

ISSUE
1



EDAC INC
TORONTO, ONTARIO
CANADA

YOUR CONNECTION TO QUALITY & SERVICE

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.