



Product Number: CY23FP12OXI

Automotive Qualified	N
Output Signal Type	LVC MOS
Min. Operating Voltage (V)	3.13
Max. Operating Voltage (V)	3.45
Temp. Classification	Industrial
No. of PLL	1
Input Signal Type	LVC MOS/LVTTL
Input Frequency Max. (MHz)	200
Core Voltage (V)	3.3
Output Frequency Min. (MHz)	10
Input Frequency Min. (MHz)	10
Output Frequency Max. (MHz)	200
Spread Spectrum	N
No. of Outputs	12
I/O Voltage (V)	2.5/3.3
No. of Pins	28
Package Carrier	TUBE
Standard Pack Quantity	94
Minimum Order Quantity (MOQ)	94
Order Increment	94
Estimated Lead Time (days)	42
HTS Code	8542.31.0000
Moisture Sensitivity Level (MSL)	3
Peak Reflow Temp. (°C)	260
RoHS Compliant	Y
PB Free	Y
Lead/Ball Finish	Ni/Pd/Au, Pure Sn