



Product Number: **CY23FP12OXIT**

Automotive Qualified	N
Output Signal Type	LVC MOS
Min. Operating Voltage (V)	3.13
Max. Operating Voltage (V)	3.45
Temp. Classification	Industrial
No. of PLL	1
Input Signal Type	LVC MOS/LVTTL
Input Frequency Max. (MHz)	200
Core Voltage (V)	3.3
Output Frequency Min. (MHz)	10
Input Frequency Min. (MHz)	10
Output Frequency Max. (MHz)	200
Spread Spectrum	N
No. of Outputs	12
No. of Pins	28
Package Carrier	REEL
Standard Pack Quantity	1000
Minimum Order Quantity (MOQ)	1000
Order Increment	1000
Estimated Lead Time (days)	42
HTS Code	8542.31.0000
Moisture Sensitivity Level (MSL)	3
Peak Reflow Temp. (°C)	260
RoHS Compliant	Y
PB Free	Y
Lead/Ball Finish	Ni/Pd/Au, Pure Sn