

Endicott Research Group, Inc.

2601 Wayne St., Endicott, NY 13760 607-754-9187 Fax 607-754-9255 http://www.ergpower.com

Specifications and Applications Information

05/10/06 Preliminary


The ERG 8mAD3397 (8m Series) DC to AC inverter features onboard connectors and can be easily dimmed using an external analog control for onboard PWM dimming or external PWM generator.

Powered by a regulated +12 Volt DC source, the 8mAD3397 is designed to power the NEC 10.4" display backlight.

Product Features

- ✓ Small Package Size, less than 9mm in height.
- ✓ High Dimming Ratio
- ✓ High Efficiency
- ✓ Made in U.S.A.


This unit complements our 8m Series of DC to AC Inverters



| | Connectors | | | | |
|---|-------------------------------|--------------------------------------|--|--|--|
| N | Input J1 Molex 532-61-0890 | Output J2 JST SM03(4.0)B-BHS-1-TB | | | |

8mAD3397

Two Lamp
DC to AC Inverter





Absolute Maximum Ratings (Note 1)

| Rating | Symbol | Value | Units | |
|-----------------------|---------------------|-------------------------------|-------|--|
| Input Voltage | V _{in} | V _{in} -0.3 to +13.2 | | |
| Disable | V _{Enable} | -0.3 to +0.3 | Vdc | |
| Operating Temperature | T _a | -0 to +85 | °C | |
| Storage Temperature | T _s | -40 to +85 | °C | |

Recommended Operating Conditions

| Rating | Symbol | Value | Units | |
|--------------------------------|-----------------|---------------|-------|--|
| Input Voltage | V _{in} | +10.8 to 12.6 | Vdc | |
| Operating Temperature (Note 2) | T _a | 0 to +50 | °C | |

Electrical Characteristics

Unless otherwise noted Vin = 12.00 Volts dc and Ta = 25°C

| Characteristic | Symbol | Min | Тур | Max | Units | | | | |
|----------------------------|----------------------------|------|-----|------|---------------------|--|--|--|--|
| Input Current | l in | - | .50 | .57 | A _{DC} | | | | |
| Input Ripple Current | l rip | - | 20 | - | mA _{pk-pk} | | | | |
| Operating Frequency | F _o | 41 | 46 | 51 | KHz | | | | |
| Efficiency | h | - | 86 | - | % | | | | |
| Output Voltage | V _{start} | 1300 | - | - | V | | | | |
| Output Voltage (Note 3) | V _{out} | - | 510 | - | V | | | | |
| Output Current per output | l out | - | 5 | - | mArms | | | | |
| Enable (pin J1-5) (Note 4) | Enable (pin J1-5) (Note 4) | | | | | | | | |
| Turn-off Threshold | V thoff | 0 | - | 1 | V | | | | |
| Turn-On Threshold | V thon | 2.5 | - | Vin | V | | | | |
| Impedance to Vin | R _{Disable} | 44.6 | 47 | 49.4 | kOhms | | | | |

- (Note 1) Reliable and predictable operation of the device is not guaranteed with applied stresses at or beyond those listed in "Absolute Maximum Ratings". Operation at these limits may reduce device reliability and is therefore not recommended. Please refer to "Recommended Operating Conditions" for reliable operation of the device.
- (Note 2) Reliable operation above 50°C is possible if airflow is provided.
- (Note 3) When powering a load simulating the referenced display
- (Note 4) The inverter is always enabled with an internal pullup resistor tied to the enable pin. A ground on the enable input will turn the inverter off.

Application Notes:

- 1) The minimum distance from high voltage areas of the inverter to any conductive material should be .12 inches per kilovolt of starting voltage.
- 2) Mounting hardware should be non-conductive.
- 3) Open framed inverters should not be used in applications at altitudes over 10,000 feet.
- 4) Contact ERG for possible exceptions.



Onboard PWM

Unless otherwise noted Vin = 12.00 Volts DC , Ta = 25 °C and unit has been running for 5 minutes.

| Characteristic | Symbol | Min | Тур | Max | Units |
|----------------------------|------------------|-----|-----|-----|-------|
| Frequency | f _{pwm} | - | 160 | - | Hz |
| Control Input Bias Current | I chias | - | - | 10 | uA |

Pin Descriptions

Vin Input voltage to the inverter.

GND Inverter ground.

Control Analog voltage input to the onboard pulse width modulator. Increasing this voltage increases the off

time of the onboard PWM resulting in decreased brightness. The inverter is full on when this voltage

is near inverter ground.

Enable Inverter Enable. The inverter is always enabled with an internal pullup resistor tied to the enable pin.

Pull this pin low to disable inverter operation. The onboard PWM is always utilized.

Application information


The 8mAD series of inverters is designed to power two cold cathode fluorescent tubes each with four watts. An external analog control interfaces with an onboard pulse width modulator to provide dimming control. The 8mAD inverter can reliably dim to less than 5% duty cycle.

External shutdown of the inverter is accomplished using the Enable pin. Pulling this pin low (below Vthoff) disables the inverter.


If analog voltage dimming is required, the analog voltage is applied to the Control pin. Figure 1 shows how to connect the inverter for onboard PWM operation. Graph 1shows the relationship of PWM duty cycle to input control voltage.

If an external PWM is used, simply connect the Enable pin to the PWM source and connect the Control pin to inverter ground. If the onboard PWM is used, connect the analog voltage to the Control pin.






Graph 1







Endicott Research Group, Inc. (ERG) reserves the right to make changes in circuit design and/or specifications at any time without notice. Accordingly, the reader is cautioned to verify that data sheets are current before placing orders. Information furnished by ERG is believed to be accurate and reliable. However, no responsibility is assumed by ERG for its use.



| ZONE | REV. | DESCRIPTION | DATE | APPROVED |
|------|------|--|----------|----------|
| | _ | RELEASED FOR QUOTE ONLY | 02/21/06 | LRC |
| | 0 | ADDED CUTOUT DIM, REMV'D TAPE NOTE | 03/02/06 | LRC |
| | 1 | WRAP AROUND WAS SINGLE SIDED ONLY | 04/20/06 | LRC |
| | 2 | .28 WAS .25 (ADDED FOR THICKER TAPE) 2.12 WAS 2.00, .45 WAS .39, ADDED .15 CUTBACK | 05/04/06 | LRC |
| | 3 | FOLD\CUT LINES WERE FOLD ONLY LINES, .005" THICK MATERIAL WAS .0075" | 07/04/06 | LRC |
| | 4 | ADDED 3 CORNER CHAMFERS | 07/10/06 | LRC |



FOLD\CUT LINE DETAIL



FOLDED VIEW

| <u>IOLERANCES</u> FRACTION ± 1/32 2 PL. DEC. ±.01 3 PL. DEC. ±.005 | | 8MAD3397 USED ON (APPLY W\ N27030) | | ENDICOTT RESEARCH GROUP, INC. 2601 WAYNE ST., ENDICOTT, NY 13760 607-754-9187 | | | | | |
|--|----------|---|------------|---|------------|----------------------------|-------|----------|------|
| | | APF | PROVALS | DATE | | · | | | 9107 |
| L | IATERIAL | DRAWN | LRC | 02/21/06 | TITLE | SHIELD, SHOCK F | | | |
| " | | CHECKED | LRC | 02/21/06 | P/N | N17031 (DESIGNED FOR TYCO) | | | |
| F | INISH | APPROVED | LRC | 02/21/06 | Δ | DRAWING NUMBER A | 00984 | <u> </u> | REV. |
| \vdash | | <u></u> | | | <i>L</i> 1 | 5 | FT 4 | 05 4 | |
| DO NOT SCALE | | SCA | E FULL SHE | EI 1 | OF 1 | | | | |