


REVISIONS			DATE	NAME
REV	DESCRIPTION			
A	Initial Release.		06-07-07	AMH
B	Updated temp spec and balling		08-17-09	AMH



PIN #	Assignment
1	Right Excite
2	Right Sense
3	Top Sense
4	Top Excite
5	Left Excite
6	Left Sense
7	Bottom Sense
8	Bottom Excite

- NOTES:
1. Operation Temperature: -20°C--+60°C  
Storage Temperature: -20°C--+70°C
  2. Life Time: >5,000,000 times.
  3. Linearity: ≤ 1.5%.
  4. ITO Film: Anti-glare & Hardening Coating Anti-Newton Ring  
Sheet Resistance: 400±100 Ω/square;  
ITO Film: Clear- Anti-Newton Ring  
Sheet Resistance: 400±100 Ω/square
  5. Tail Type :Gold plated FPC
  6. All Tolerance Without Marked:±0.3
  7. All Materials and Components must be RoHS compliant
  8. No Material is allowed to be larger than the glass size

**DawarTouch**

1016 North Lincoln Avenue - Pittsburgh, PA 15239-2002  
 1-800-581-1941 - F: 412-252-2500 - Fax: 412-252-2599  
 e-mail: sales@swinfr.com - www.dawartouch.com

THIS DOCUMENT IS THE PROPERTY OF DAWAR TECHNOLOGIES, INC. AND SHALL NOT BE COPIED, REPRODUCED, DISCLOSED, AND/OR USED AS THE BASIS FOR MANUFACTURING OR SALE WITHOUT PERMISSION OF A DULY AUTHORIZED REPRESENTATIVE OF DAWAR TECHNOLOGIES, INC.

CUSTOMER NAME		UNIT	DAWAR PIN	REV
Standard product offering		mm	PL8_8.4-00001	B
DESCRIPTION		REV	DRAWN BY	DATE
8.4" 8-Wire Resistive Touch Screen		REV	Jason Liao	08-17-09
SHEET		MANUFACTURING NO.		REV
1 OF 1				