



POWER ENTRY MODULES

SNAP-IN MOUNTING

INTRODUCTIONS


- 1. Designed to meet globally accepted IEC publication 320 Class 1, that allows users to comply with industry standard in power entry requirement.
- 2. Connector for cold condition, with pin temperature 70°C max.
- 3. Nickel-plated brass pins and soldering terminals.
- 4. Snap-in mount (panel thickness: 0.04 inch to 0.07 inch).
- Power module in plastic or metal case that incorporates an IEC connector, fuse holder, power switch and voltage selector switch, all-in-one easy-to-install unit.
 - Part numbers 06A1, 06A2, 06A2D and 06A5 are power modules in plastic case; part numbers 06AN2, 06AN2D, 06AN3, 06AN3D and 06AN5 are power modules in metal case.
- Fuse holder designed for one fuse. Safety interlock prevents fuse removal with line plug inserted.
- 7. Adapts to 110V or 220V input voltage with voltage selector switch.
- Compact design and high volume production provide maximum flexibility and significant savings in space and cost over assembly of individual components.
- 9. All part numbers are UL recognized. CSA certified and SEMKO approved.

SPECIFICATIONS

- 1. Rated voltage: 115VAC/250VAC
- Maximum leakage current each line-to-ground 2uA AT 115VAC/60Hz 5uA AT 250VAC/50Hz
- 3. Dielectric strength (one minute) line-to-ground: 2250VDC line-to-line: 1450VDC
- 4. Flammability class: UL 94V-0

ELECTRICAL SCHEMATIC

FIG. C



TYPE & RATED CURRENT

DELTA PART NUMBE	DELTA PART NUMBER		06A2	06A2D	06A5	
DATED OUDDENT	UL/CSA (115VAC/250VAC)	6A	6A	4A	6A	
RATED CURRENT	SEMKO	UA	UA			
CONNECTOR TYPE	MALE	\triangle	\triangle	\triangle	\triangle	
	FEMALE					
FUSE HOLDER		S	S	S	S	
POWER SWITCH		-	SP *1	DP *2	-	
VOLTAGE SELECTOR		-	-	-	FRONT *3	
ELECTRICAL SCHEMATIC		FIG. A	FIG. C	FIG. D	FIG. B	

REMARKS:

* 1. SINGLE-POLE POWER SWITCH UL/CSA APPROVED AT 6A, 125VAC/250VAC VDE APPROVED AT 6A/250VAC ELECTRICAL LIFETIME: 50,000 CYCLES MAXIMUM IN-RUSH CURRENT: 70A

FIG. D


- * 2. DOUBLE-POLE POWER SWITCH ELECTRICAL LIFETIME: 10,000 CYCLES MAXIMUM IN-RUSH CURRENT: 50A
- * 3. VOLTAGE SELECTOR SWITCH UL/CSA APPROVED AT 6A/125VAC & 250VAC VDE APPROVED AT 6A/250VAC

DELTA PART NUMBER		06AN2	06AN2D	06AN3	06AN3D	06AN5	REMARKS: * 1. SINGLE-POLE POWER SWITCH
RATED CURRENT	UL/CSA (115VAC/250VAC)		6A 6A 4A		6A	UL/CSA APPROVED AT 6A, 125VAC/250VAC VDE APPROVED AT 6A/250VAC ELECTRICAL LIFETIME: 50,000 CYCLES	
CONNECTOR TYPE	SEMKO MALE	\triangle		Δ	\triangle	\triangle	MAXIMUM IN-RUSH CURRENT: 70A * 2. DOUBLE-POLE POWER SWITCH ELECTRICAL LIFETIME: 10,000 CYCLES
COMMECTOR TIPE	FEMALE						MAXIMUM IN-RUSH CURRENT: 50A * 3. VOLTAGE SELECTOR SWITCH (FRONT)
FUSE HOLDER		S	S	S	S	S	UL/CSA APPROVED AT 6A, 125VAC/250VAC VDE APPROVED AT 6A/250VAC
POWER SWITCH		SP*1	DP *2	SP *1	DP *2	-	* 4. VOLTAGE SELECTOR SWITCH (REAR) UL/CSA/VDE APPROVED AT 10A/125VAC&
VOLTAGE SELECTOR		-	-	REAR*4	REAR*4	FRONT *3	E 1 (0 E 0) (1 0
ELECTRICAL SCHEMATIC		FIG. C	FIG. D	FIG. C	FIG. D	FIG. B	

MECHANICAL CONSTRUCTION




06A5 06A1 (Without voltage selector switch)






06A2








06A2D





UNIT: INCH mm

MECHANICAL CONSTRUCTION




06AN2 06AN2D





06AN3 06AN3D



06AN5







XAMARSOT, XAMARS

The "0" "1" marking of Single and double-pole power on/off switches are reversed in position.

 $\text{UNIT:} \frac{\text{INCH}}{\text{mm}}$