


SERIES LC SWITCHES

PUSHBUTTON SWITCHES



FEATURES & BENEFITS

- ▶ Latching & momentary functions
- ▶ Shorting or non-shorting versions
- ▶ Variety of housing styles available

APPLICATIONS/MARKETS

- ▶ Telecommunications
- ▶ Networking
- ▶ Computers/servers
- ▶ Performance audio
- ▶ Instrumentation
- ▶ Low power on/off designs
- ▶ External hard drives and modems


SPECIFICATIONS

Contact Rating:	300mA @ 30 VDC
Life Expectancy:	10,000 cycles typical
Contact Resistance:	20mΩ max. initial @ 2-4 VDC, 100mA
Insulation Resistance:	100MΩ min.
Dielectric Strength:	1,000 V rms @ sea level
Actuation Force:	Dependent upon model number
Operating Temperature:	-20° to +85°C

MATERIALS

Housing:	Tin over Steel
Actuator:	Acetal
Terminal Base:	Phenolic
Spring:	Spring steel
Terminals:	Silver over brass
Contacts:	Silver over phosphor bronze

HOW TO ORDER



Example Ordering Number

LC-1258-EE-N-P


Specifications subject to change without notice.

ACTUATION OPTIONS


Model No.	Actuation Force
1258	230 ± 100 gf
2254	300 ± 150 gf
2255	300 ± 150 gf
2259	330 ± 100 gf

**LC 1258**

Shaft End Style A





SCHEMATIC




P.C. MOUNTING

LC 2254

Shaft End Style □2.7mm




SCHEMATIC




P.C. MOUNTING

LC 2255

Shaft End Style B





SCHEMATIC




P.C. MOUNTING

LC 2259



Shaft End Style A



SCHEMATIC



P.C. MOUNTING

SHAFT END STYLES**A****B****P****PC PIN**