


TWN4 MULTITECH 2

PROGRAMMABLE RFID READER/WRITER FOR LF/HF/NFC



TWN4 MultiTech 2
PCB top view



Desktop version
(inlay customizable)

Elatec's TWN4 family of transponder readers and writers allows users to read and write to almost any 125 kHz, 134.2 kHz and 13.56 MHz tags and/or labels. It supports all major transponders from various suppliers like ATMEL, EM, ST, NXP, TI, HID etc. and ISO standards like ISO14443A/B (T=CL), ISO15693, ISO18092 / ECMA-340 (NFC).

The TWN4 MultiTech 2 reader has integrated RFID (LF & HF) and NFC, which is supported by mobile phones with Android version 4.3 or greater. The app on the reader communicates with the NFC module with easy commands.

Special features:

- + powerful SDK for writing apps which are executed directly on the reader
- + firmware update in the field possible
- + onboard 18 kB flash storage, e.g. for storing user accessible non-volatile data
- + direct chip-commands support
- + two onboard SAM sockets (Secure Access Module)
- + CCID and PC/SC 2.01
- + 4 GPIOs
- + supports quick centralized (re)configuration over network and over wireless interface with TWN4 CONFIG Card
- + 3D construction data (STEP) available on request



Elevator



EV Chargers



Access



Shop POS



Fitness
Equipment



Ticket POS



PC Log-on



Document
Management



Driver ID



Vending



Parking



Gaming



Locker Locks



Time
Attendance



Industrial
PC

TECHNICAL DATA

FREQUENCY	125 kHz/134.2 kHz (LF) / 13.56 MHz (HF)
ANTENNA	Integrated
HOUSING	Material: ABS UL94-V0, color: black or white
DIMENSIONS (L X W X H)	Desktop Reader: 88 mm x 56 mm x 18 mm / 3.5 inch x 2.2 inch x 0.7 inch OEM Board: 76 mm x 49 mm x 9 mm / 3.0 inch x 1.9 inch x 0.4 inch
POWER SUPPLY	4.3 V - 5.5 V via USB or RS-232; RS232 requires 5 V external power supply; via connector CNB 3.3 V +/- 5%
CURRENT CONSUMPTION	RF field on: 120 mA typically / Sleep: 500 µA typ. / Cyclic Operation: TBD
TEMPERATURE RANGE	Desktop, Operating: -25 °C up to +70 °C (-13 °F up to +158 °F) Desktop, Storage: -45 °C up to +75 °C (-49 °F up to +167 °F) PCB, Operating: -25 °C up to +80 °C (-13 °F up to +176 °F) PCB, Storage: -45 °C up to +85 °C (-49 °F up to +185 °F)
RELATIVE HUMIDITY	5% to 95% non-condensing
READ- / WRITE DISTANCE	LF and HF: Up to 100 mm / 4 inch, depending on environment and transponder
TRANSMISSION SPEED	Host: USB Full speed (12 Mbit/s), RS-232: up to 115.200 baud; HF Air: up to 848 kbit/s
OPERATING MODES (USB)	USB keyboard emulation – USB virtual COM port – CCID / PC/SC 2.01
MTBF	500,000 hours
WEIGHT	Approx. 20 g (without housing)
SUPPORTED TRANSPONDERS (STANDARD)	<p><u>ISO14443A:</u> LEGIC Advant¹⁾, MIFARE Classic EV1²⁾, MIFARE Classic, MIFARE Mini, MIFARE DESFire EV1, MIFARE DESFire EV2²⁾, MIFARE Plus S, X, MIFARE Pro X³⁾, MIFARE Smart MX³⁾, MIFARE Ultralight, MIFARE Ultralight C, MIFARE Ultralight EV1</p> <p><u>ISO14443B:</u> Calypso³⁾, Calypso Innovatron protocol³⁾, CEPAS³⁾, HID iCLASS¹⁾, Moneo³⁾, Pico Pass⁴⁾, SRI4K, SRIX4K, SRI512, SRT512</p> <p><u>ISO18092 ECMA-340:</u> NFC Forum Tag 1-5, NFC Peer-to-Peer, Sony FeliCa⁵⁾, NFC Active and passive communication mode</p> <p><u>ISO15693:</u> EM4x33³⁾, EM4x35³⁾, HID iCLASS¹⁾, HID iCLASS SE/SR¹⁾, ICODE SLI, LEGIC Advant¹⁾, M24LR16/64, MB89R118/119, SRF55Vxx (my-d vicinity)³⁾, Tag-it, PicoPass⁴⁾</p> <p><u>125 kHz, 134.2 kHz:</u> AWID, Cardax, CASI-RUSCO, Deister⁶⁾, EM4100, 4102, 4200⁷⁾, EM4050, 4150, 4450, 4550, EM4305⁸⁾, FDX-B, EM4105, HITAG 1⁹⁾, HITAG 2⁹⁾, HITAG S⁹⁾, ICT⁸⁾, IDTECK, Isonas⁸⁾, Keri, Miro, Nedap⁶⁾, PAC, Pyramid, Q5, T5557, T5567, T5577, TIRIS/HDX, TITAN (EM4050), UNIQUE, ZODIAC</p>
SUPPORTED TRANSPONDERS (OPTION P)	All Standard Transponders, Cotag, G-Prox ⁶⁾ , HID DuoProx II, HID ISO Prox II, HID Micro Prox, HID ProxKey III, HID Prox, HID Prox II, Indala, ioProx, Nexwatch
SUPPORTED TRANSPONDERS (OPTION PI)	Requires external TWN4 SIO Card, All Standard Transponders, All Version P Transponders, HID iCLASS ¹⁰⁾ , HID iCLASS SE/SR/SEOS(CSN and Facility Code/PAC) ¹⁰⁾ , HID iCLASS Elite & SE Elite
OS SUPPORT	Windows XP, Vista, Embedded CE ⁸⁾ , 7 (32-/64-bit), 8, 8.1, 10, Linux, Android ⁸⁾ , iOS ⁸⁾ , MAC OS X ⁸⁾
PERIPHERAL INTERFACES	USB, RS232, TTL serial (logic level 3.3 V, CMOS, 5 V tolerant), I ² C, 4 GPIOs, Clock/Data, Wiegand, 1-Wire ⁸⁾
CERTIFICATION NAME	TWN4 MultiTech 2
CERTIFICATION(S)	ACA, ANATEL, CE/RED, FCC Single Modular Approval, IC, Israel, RoHS-II compliant

ORDER CODE(S)	T4BO-F6	OEM Board
	T4BT-FB2BEL6	USB Black
	T4BT-FB2WEL6	USB White
	T4BO-F6-P	OEM Board Version P
	T4BT-FB2BEL6-P	USB Version P Black
	T4BT-FB2WEL6-P	USB Version P White
	T4BO-F6-PI	OEM Board Version PI
	T4BT-FB2BEL6-PI	USB Version PI Black
	T4BT-FB2WEL6-PI	USB Version PI White

¹UID only ²r/w enhanced security features on request ³r/w in direct chip command mode ⁴UID only, read/write on request ⁵UID + r/w public area ⁶Hash value only ⁷Only emulation of 4100, 4102 ⁸On request ⁹Without encryption ¹⁰UID + PAC (CSN & Facility Code), r/w on request

ACCESSORIES

HOLDER(S)	HKSI-B: Snap-In Holder black
	HKSI-W: Snap-In Holder white
	HKBR-B: Bracket Holder black
	HKBR-W: Bracket Holder white
POWER SUPPLY	PWA-EU: Power Supply (EU)
	PWA-US: Power Supply (US)
	PWA-UK: Power Supply (UK)
	PWA-AU: Power Supply (AU)
	PWA-JP: Power Supply (JP)
CABLES	CAB-B2: USB cable type A 200 cm / 78.74 inch
	CAB-B3: USB cable type A 12 cm / 4.72 inch
	CAB-B4: USB cable type A 45 cm / 17.72 inch
	CAB-B7: USB cable type A 120 cm / 47.24 inch
	CAB-M1: USB cable mini 12 cm / 4.72 inch
	CAB-M2: USB cable mini 25 cm / 9.84 inch
	CAB-R2: RS232 cable 200 cm / 78.74 inch