



SAW Components

Data Sheet B3581





SAW Components

B3581

Low Loss Filter

315,00 MHz

Data Sheet


Ceramic package **QCC8B**

Features

- RF low-loss filter for remote control receivers
- Package for **Surface Mounted Technology (SMT)**
- Hermetically sealed ceramic package
- No matching network required for operation at 50 Ω

Terminals


- Ni, gold plated



Dimensions in mm, approx. weight 0,07 g

Pin configuration

- 2 Input
- 1,3 Input Ground
- 6 Output
- 5,7 Output Ground
- 4,8 to be grounded



Type	Ordering code	Marking and Package according to	Packing according to
B3581	B39321-B3581-Z810	C61157-A7-A46	F61074-V8037-Z000

Electrostatic Sensitive Device (ESD)

Maximum ratings

Operable temperature range	T	-40/+85	°C	source impedance 50 Ω
Storage temperature range	T_{stg}	-45/+90	°C	
DC voltage	V_{DC}	0	V	
Source power	P_S	10	dBm	



SAW Components

B3581

Low Loss Filter

315,00 MHz

Data Sheet

Characteristics

Operating temperature range: $T = -40^{\circ}\text{C}$ to 85°C

Terminating source impedance: $Z_S = 50 \Omega$


Terminating load impedance: $Z_L = 50 \Omega$

		min.	typ.	max.	
Center frequency	f_c	—	315,00	—	MHz
Maximum insertion attenuation	α_{\max}				
	314,50 ... 315,50 MHz	—	2,7	3,7	dB
Amplitude ripple (p-p)	$\Delta\alpha$				
	314,80 ... 315,20 MHz	—	0,4	1,0	dB
	314,50 ... 315,50 MHz	—	0,8	2,0	dB
Relative attenuation (relative to α_{\max})	α_{rel}				
	10,00 ... 250,00 MHz	55	60	—	dB
	250,00 ... 295,00 MHz	47	53	—	dB
	295,00 ... 307,00 MHz	36	41	—	dB
	307,00 ... 310,00 MHz	32	40	—	dB
	320,00 ... 328,00 MHz	16	20	—	dB
	328,00 ... 335,00 MHz	39	44	—	dB
	335,00 ... 410,00 MHz	44	49	—	dB
	410,00 ... 480,00 MHz	40	45	—	dB
	480,00 ... 1000,00 MHz	49	54	—	dB
Temperature coefficient of frequency	TC_f	—	-30	—	ppm/K




Data Sheet

Transfer function



Transfer function (wideband)





SAW Components

B3581

Low Loss Filter

315,00 MHz

Data Sheet

Published by EPCOS AG

Surface Acoustic Wave Components Division, SAW CE AE PD

P.O. Box 80 17 09, D-81617 München

© EPCOS AG 2001. All Rights Reserved.

As far as patents or other rights of third parties are concerned, liability is only assumed for components per se, not for applications, processes and circuits implemented within components or assemblies.

The information describes the type of component and shall not be considered as assured characteristics.

Terms of delivery and rights to change design reserved.

For questions on technology, prices and delivery please contact the sales offices of EPCOS AG or the international representatives.

Due to technical requirements components may contain dangerous substances. For information on the type in question please also contact one of our sales offices.