




REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
0		RELEASED	12/01/08	CC

H7605XXX	"L" (length)
305	12"
460	18"



- NOTE:
1. WIRES TO BE #26 AWG MIL STD W16878 TYPE B (BELDEN #8504 OR EQUIVELANT) IN COLORS AND LENGTHS LISTED.
 2. CABLE INSULATION TO BE CAPTIVATED BY CRIMP TERMINAL, SEE IPC/WHMA-A-620 FOR ACCEPTABILITY.
 3. PLACE HARNESS ASSEMBLY IN BAG CALLED OUT ON BUILD SHEET.
 4. WIRES ARE BLACK (N29058).
 5. WIRES ARE WHITE (N29059).
 6. CONNECTOR N22230 IS POPULATED IN POSITIONS 1,2 AND 3 (STRIP LENGTH OF WIRE IS 2.5 ± .3mm).
 7. CONNECTOR N22231 IS POPULATED IN POSITIONS 1 AND 2 (STRIP LENGTH OF WIRE IS 2.5 ± .3mm).
 8. CONNECTOR N22216 IS POPULATED IN POSITIONS 1,2,3,4 AND 5 (STRIP LENGTH OF WIRE IS 1.65 ± .25mm).

TOLERANCES		USED ON		MA PRODUCTS	
FRACTION	± 1/8	APPROVALS	DATE		
PL.	DEC. ± .01	DRAWN	CC	12/01/08	
	3 PL. DEC. ± .005	CHECKED	CC	12/01/08	
MATERIAL		APPROVED	CC	12/01/08	
FINISH					
DO NOT SCALE					

ENDICOTT RESEARCH GROUP, INC.
 2601 WAYNE ST., ENDICOTT, NY 13760 607-754-9187

TITLE: WIRING HARNESS
 H7605
 DRAWING NUMBER: H7605
 SCALE: 1 OF 1
 REV: 0