






REV.	ECN NO.	APPD.
X1	TBD	Simon Chen 6/16/11
X2	TBD	Jerry Wu 4/27/12



WIRE TABLE

J1	CONNECTION	J2	REMARK
	COLOR		
1	RED	1	VBUS
2	WHITE	2	D-
3	GREEN	3	D+
4	BLACK	5	GRN
5	BLUE	6	SDP1-
6	YELLOW	7	SDP1+
7	DRAIN	8	GRN
8	PURPLE	9	SDP2-
9	ORANGE	10	SDP2+
SHELL	BRAID	SHELL	

Tab1. RAW CABLE SPEC.

ITEM	RAW CABLE P/N	SDP AWG	UTP AWG	Power AWG	OD. mm	Color
1	791-1017-035	30	30	24	4.8	DARK GREY

8	USB 3.0 Micro B PLUG HOUSING	1	UN2298C-B02-7F-H	Housing:LCP E6807LHFZ BLACK
7	USB 3.0 Micro B PLUG REAR SHELL	1	024-0001-9672	C5191, T=0.30mm Tin 50~100u"
6	USB 3.0 Micro B PLUG OVER MOLD	A/R	901-C301-024	UL 94V-0, PVC DARK GREY
5	RAW CABLE	A/R	791-1017-035	SHOWN AS Tab1. RAW CABLE SPEC.
4	USB 3.0 A PLUG OVER MOLD	A/R	901-C301-024	UL 94V-0, PVC DARK GREY
3	USB 3.0 A PLUG HOUSING	1	UE10103-K01-4F-H	HOUSING: PBT, COLOR BLUE. CONTACT: Au 30u"
2	USB 3.0 A PLUG REAR SHELL	1	023-02F0-9214	BRASS C2680R-H, Ni 50~90u" Sn 100~200u" OVER Ni SURFACE
1	USB 3.0 A PLUG FRONT SHELL	1	023-00F0-9215	SUS304-H/2, SHELL PLATED Ni 50~90u"
NO	DESCRIPTION	Q'TY	P/N	REMARK

- NOTES:
- DIM. MARKED ∇ TO BE CHECKED.
 - ELECTRICAL CHARACTER:
 - ANY OPEN,MISS WIRING&SHORT ARE NOT PERMITTED, PRODUCT 100% TEST.
 - INSULATION RESISTANCE: 100M OHMS(MIN)/300VDC, 40ms.
 - CONDUCT RESISTANCE: 2.0 OHMS(MAX).
 - HARMFUL MATERIAL CONTROL PLEASE FOLLOW Doc.No."EPI12".

X.±	X°.±	UNITS	mm	NAME<INTENDED USE>	FOXCONN HON HAI PRECISION IND. CO.,LTD. TAIPEI, TAIWAN, R.D.C.
X.± 0.25	.X°±	MAT'L		CUSTOMER DRAWING	
.XX±0.25	.XX°±	FINISH		PART NO.<INTENDED USE>	TITLE:
.XXX±	.XXX°±		Q'TY		CUED005F-M26-0F
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON HAI PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON HAI PRECISION IND. CO., LTD.				APPD:	DWG NO.:
				Jerry Wu 4/27/12	605-0000-*
				CHKD:	SCALE
				Vincent 4/27/12	SHEET
				DR:	REV.
				Xianhui Lei 4/27/12	NONE
					1/1
					X2