

LTE Module

NL668-LA-05 MiniPCle



4 Modes

50Mbps LTE Uplink

150Mbps LTE Downlink

Temperature Range
-40°C~+85°C

Fibocom NL668-LA MiniPCle is a MiniPCle form factor LTE wireless communication module which supports LTE FDD/TDD/WCDMA / GSM 4 modes. The highest speed can reach Cat 4 150Mbps DL and 50Mbps UL. It can be used in industries such as industrial routing, security, and Internet of Vehicles.



LTE Module

NL668-LA-05 MiniPCle



Product Features

- Memory: 2Gb ROM+1Gb RAM
- LTE FDD: B1/2/3/4/5/7/8/12/17/28/66
- LTE TDD: B38/40
- WCDMA: B1/2/3/4/5/8
- GSM/GPRS/EDGE: 850/900/1800/1900MHz
- MiniPCle: 51x30x3.7mm
- Temperature :
 - Normal Operation: -30~+75°C
 - Extended operation: -40~+85°C
 - Storage Temperature: -40~+90°C
- Operating Voltage: 3.3V~4.3V typical 3.8V
- AT Command Set: 3GPP TS 27.007 and 27.005, and proprietary FIBOCOM AT commands
- TX Power
 - GSM900: 32.5 dBm±1dBm
 - DCS1800: 29.5dBm±1dBm
 - WCDMA: 23.5dBm±1dBm
 - LTE FDD: 23.0dBm±1dBm
 - LTE TDD: 23.0dBm±1dBm

Data

- LTE FDD: 150Mbps DL/50Mbps UL
- LTE TDD: 130Mbps DL/30.5Mbps UL
- WCDMA: 384 kbps DL/384 kbps UL
- DC-HSPA+: 42Mbps DL/5.76Mbps UL
- EDGE: 296Kbps DL/236.8Kbps UL
- GPRS: 107Kbps DL/85.6Kbps UL

Function

- MUX: Basic Mode
- SMS: MO/MT Text and PDU modes
- TCP/UDP(S)/HTTP(S)/FTP(S)/IPv4/IPv6/SSL/TLS/MQTT/PIN G/NTP/FFS/NITZ/PPP/ECM/RNDIS/GobiNet/QMI_WWAN
- DFOTA/FOAT
- VoLTE/TTS/Recording/FFS/BIP
- GNSS/LBS/A-GPS

Interface

- SIM Card: 1.8V/3.0V
- USB 2.0
- UART
- PCM/I2S
- GPIO
- System Indicator
- Analog Audio
- Antenna: Main/Div/GNSS

Driver

- Linux/Android/Windows

Approval

- Industry: HF
- Regulation: RoHS/FCC*/ANATEL

Note : * = Planning / In progress

Copyright©FibocomWirelessInc. | Subject to changes in technology, design and availability | E-mail: market@fibocom.com | Tel: +86 755-2673 3555