


Recommended PCB Layout

As viewed from component side Tolerance: ±0.05mm

■ Solder Area □ Component Outline



Pin	Signal	Mating Sequence	Pin	Signal	Mating Sequence
A1	GND	First	B12	GND	First
A4	Vbus	First	B9	Vbus	First
A5	CC1	Second	B8	SBU2	Second
A6	Dp1	Second	B7	Dn2	Second
A7	Dn1	Second	B6	Dp2	Second
A8	SBU1	Second	B5	CC2	Second
A9	Vbus	First	B4	Vbus	First
A12	GND	First	B1	GND	First
SHELL	GND		SHELL	GND	

Specifications

Material

Insulator: PA9T, UL 94V-0, Black
Terminal: Copper Alloy
Shell: Stainless steel
Mid Plate: Stainless Steel

Plating

Terminal:
Contact Area: 3µ" Gold
Solder Tails: Gold Flash
Underplating: 50µ" min. Nickel All Over
Shell: 30µ" min. Nickel
Mid Plate: Clear




Electrical

Current Rating: 5,00A collectively for Vbus pins
6.25A collectively for GND pins
1.25A for A5/B5 pin
0.25A per pin for all other pins



Voltage Rating: 48V DC
Power Rating: 240W
Contact Resistance: 40mΩ max. initial
50mΩ max. after test
Dielectric Withstanding Voltage: 100V AC
Insulation Resistance 100MΩ min.

Mechanical & Environmental

Operating Temperature: -25°C to +85°C
Mating Force: 5 to 20 N.
Unmated Force: 6 to 20 N after test
Durability: 20,000 cycles




Section: A-A



Plug and Receptacle Mating View

Ordering Grid



Contact Plating
03 = 3µ" Gold

Packing Options
A = Tape & Reel
(1200pcs per reel)


Part Number		Product Description	
USB4215		USB Type C Receptacle for USB 2.0, SMT Type, PCB Top Mount, Horizontal, 16Pin	
Drawing Date		26th April 2024	
By	CC	Tolerances (Except as Noted)	Units:
Detail	Drawing Release	Length	Metric (mm)
Revision	A	X.X ± 0.30	3rd Angle Projection
Date	26/04/24	X.XX ± 0.25	
		X.XXX ± 0.10	






This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent, E & OE



Not to Scale	Drawn By CC	Sheet No. 1/2
--------------	----------------	------------------



Direction of Unreeling →



Pcs / Reel	Reels / Carton	Total Quantity
1200	10	12000 pcs

Part Number		Product Description	
USB4215		USB Type C Receptacle for USB 2.0, SMT Type, PCB Top Mount, Horizontal, 16Pin	
Drawing Date		26th April 2024	
By	CC	Tolerances (Except as Noted)	Units:
Detail	Drawing Release	Length	Metric (mm)
Revision	A	Angle	3rd Angle Projection
Date	26/04/24		



This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent, E & OE

GCT
www.gct.co

Not to Scale | Drawn By CC | Sheet No. 2/2