

M12 PCB female D-coded angled IP20




Image is for illustration purposes only. Please refer to product description.

| | |
|--------------------|---|
| Part number | 21 03 381 4434 |
| Specification | M12 PCB female D-coded angled IP20 |
| HARTING eCatalogue | https://b2b.harting.com/21033814434 |

Identification

| | |
|----------------|-----------------------------|
| Category | Connectors |
| Series | Circular connectors M12 |
| Identification | PushPull |
| Element | PCB adapter |
| Specification | Angled for rear mounting |

Version

| | |
|--------------------|------------------------------------|
| Termination method | Reflow soldering termination (THR) |
| Gender | Female |
| Locking type | Screw locking PushPull |
| Shielding | Shielded |
| Number of contacts | 4 |
| Coding | D-coding |

Technical characteristics

| | |
|------------------------------|------------------------------|
| Rated current | 4 A |
| Rated voltage | 250 V |
| Rated impulse voltage | 1.5 kV |
| Pollution degree | 3 |
| Transmission characteristics | Cat. 5 Class D up to 100 MHz |
| Overvoltage category | III |
| Insulation resistance | $>10^8 \Omega$ |



Pushing Performance

Technical characteristics

| | |
|--|----------------|
| Contact resistance | ≤10 mΩ |
| Tightening torque | 2 Nm Lock nut |
| Ambient temperature | -40 ... +85 °C |
| Mating cycles | ≥100 |
| Degree of protection acc. to IEC 60529 | IP20 |
| Isolation group | I (600 ≤ CTI) |

Material properties

| | |
|-----------------------------|--|
| Material (insert) | Liquid crystal polymer (LCP) |
| Material (contacts) | Copper alloy |
| Surface (contacts) | Gold plated |
| Material (hood/housing) | Zinc die-cast |
| RoHS | compliant with exemption |
| RoHS exemptions | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status | compliant with exemption |
| China RoHS | 50 |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | Yes |
| REACH SVHC substances | Lead |
| ECHA SCIP number | 0d7d3693-d625-47ab-934a-d241bf72c86e |

Specifications and approvals

| | |
|----------------|-----------------|
| Specifications | IEC 61076-2-101 |
| PROFINET | Yes |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 10 |
| Net weight | 21.75 g |
| Country of origin | Romania |
| European customs tariff number | 85366990 |
| eCl@ss | 27460201 PCB connector (board connector) |