


Shielded Low Leakage Speakers* (continued)


Metal Round Frame Types

Part Number	Frame Diameter (mm)	Frame Depth (mm)	Rated Power (watts)		Resonant Frequency (Hz)	Frequency Response (Hz)	SPL (dB)	Cone Material	Net Weight (Ounces)
			Nom.	Max.					
S200RFS-2W	50	30.0	2.0	3.0	220 ± 20%	Fo ~ 20000	82	Paper	3.50
S300RFS-3W	77	35.2	3.0	5.0	200 ± 20%	Fo ~ 15000	82	Paper	4.07
S400RFS-3W	102	44.8	3.0	5.0	140 ± 20%	Fo ~ 20000	87	Paper	7.39
S400RFS-5W	102	47.5	5.0	8.0	140 ± 20%	Fo ~ 12000	85	Paper	14.70
S500RFS-4W	119	53.2	4.0	6.0	130 ± 20%	Fo ~ 10000	87	Paper	12.28


S200RFS




S300RFS



S400RFS Series



S500RFS




Micro-Miniature Low Profile Speakers*

Height Less Than 5.0 mm


Round Metal Frame Types

Part Number	Frame Diameter (mm)	Frame Depth (mm)	Rated Power (Watts)		Cone Material	Resonant Frequency (Hz)	Frequency Response (Hz)	SPL (dB)	Magnet Type	Net Weight (Grams)
			Nom.	Max.						
SR500RS-M	13.6	4.6	0.05	0.1	Mylar	1000 ± 20%	Fo ~ 20000	83	Rare Earth	1.6
SR600RS-M	15	3.5	0.3	0.5	Mylar	780 ± 20%	Fo ~ 5000	78	Rare Earth	1.8
SR600RSL-M	15	2.2	0.1	0.2	Mylar	760 ± 20%	Fo ~ 5000	70	Rare Earth	1.2
SR630RS-M	16	3.8	0.2	0.4	Mylar	650 ± 20%	Fo ~ 6000	73	Rare Earth	1.6
SR800RS-M	20	2.4	0.3	0.6	Mylar	490 ± 20%	Fo ~ 6000	76	Rare Earth	2.1
SR800RS-M-1	20	3.2	0.5	1.0	Mylar	650 ± 20%	Fo ~ 20000	78	Rare Earth	2.8
SR800RS-M-2	20	4.0	0.5	1.0	Mylar	850 ± 20%	Fo ~ 9000	82	Rare Earth	2.6
S100RS-M	26	4.4	0.5	1.0	Mylar	540 ± 20%	Fo ~ 20000	83	Rare Earth	4.6
S110RS-M-R5W	28	4.8	0.5	1.0	Mylar	530 ± 20%	Fo ~ 20000	82	Rare Earth	4.8
S110RMSS	28	4.7	0.5	1.0	Mylar	630 ± 20%	Fo ~ 11000	83	Rare Earth	4.8
S125RSL-M-R5W	30	4.0	0.5	1.0	Mylar	650 ± 20%	Fo ~ 3000	87	Rare Earth	5.6
S125RS-M-R5W	32	4.6	0.5	1.0	Mylar	600 ± 20%	Fo ~ 5000	87	Rare Earth	7
S150RS-M-R5W	36	4.8	0.5	1.0	Mylar	550 ± 20%	Fo ~ 6000	87	Rare Earth	7.5
S150RS-M	36	4.8	0.2	0.5	Mylar	480 ± 20%	Fo ~ 12000	80	Rare Earth	7.5
S160RS-M-R2W	40	4.9	0.2	0.4	Mylar	350 ± 20%	Fo ~ 6000	83	Rare Earth	9.2
S160RS-M-1W	40	4.9	1.0	1.5	Mylar	430 ± 20%	Fo ~ 5000	84	Rare Earth	9.2

SR800RS-M-2



All Others



*Standard voice coil impedance 8 ohms ± 15%. These speakers can be supplied with a variety of voice coil impedances. The most common impedances are 4, 16, 32, 45 and 100 ohms.