HFV11

AUTOMOTIVE RELAY



Typical Applications

Headlight control, Fuel pump control, Horn control, A/C compressor clutch

Features

- Miniaturized package: (15.6 x 15.2 x 16.4) mm
- Extended temperature range: -40°C to 125°C
- 1 Form A contact arrangement
- 2.8mm QC terminals available
- RoHS & ELV compliant

CHARACTERISTICS

Contact arrangement	1A			
Voltage drop (initial)	Typ.: 30mV (at 10A)			
voltage drop (illitial)	Max.: 250mV (at 10A)			
Max.continuous current 1)	20A			
	Make (NO): 100A ²⁾			
Max.switching current	Break (NO): 30A (at 14VDC)			
Min. contact load	1A 6VDC			
Electrical endurance	See "CONTACT DATA"			
Mechanical endurance	1x10 ⁶ OPS 300OPS/min			
Initial insulation resistance	100MΩ (at 500VDC)			
District (1, 3)	between contacts: 500VAC			
Dielectric strength 3)	between coil & contacts: 500VAC			
O	Typ.: 5ms (at nomi. vol.)			
Operate time	Max.: 10ms (at nomi. vol.)			
Release time 4)	Typ.: 3ms			
Nelease time	Max.: 10ms			
Ambient temperature	-40°C to 125°C			

	10Hz to 40Hz 1.27mm DA				
Vibration	40Hz to 70Hz 49m/s ²				
resistance 5)	70Hz to 100Hz 0.5mm DA				
	100Hz to 500Hz 98m/s ²				
Shock resistance 5)	196m/s ²				
Flammability ⁶⁾	UL94-HB or better (meets FMVSS 302				
Termination	2.8mm QC				
Construction	Plastic sealed, Flux proofed				
Unit weight	Approx. 11g				
	cover retention (pull & push): 200N min.				
Mechanical data	terminal retention (pull & push): 100N min.				
	terminal resistance to bending				
	(front & side): 10N min. 7)				

- 1) For NO contacts, measured when applying 100% rated votage on coil.
- 2) Inrush peak current under lamp load, at 14VDC.
- 3) 1min, leakage current less than 1mA.
- 4) The value is measured when voltage drops suddenly from nominal voltage to 0 VDC and coil is not paralleled with suppression circuit.
- 5) When energized, opening time of NO contacts shall not exceed 100µs. 6) FMVSS: Federal Motor Vehicle Safety Standard.
- 7) Test point is at 2mm away from teminal end, and after removing testing force, the terminal transfiguration shall not exceed 0.5mm.

CONTACT DATA 1)

Load voltage	Load type		Load current A	On/Off ratio		Electrical	Contact	Ambient
			1A	On	Off	endurance OPS	Contact material	temp.
			NO	S	S			
13.5VDC Indi	Resistive	Make	20	2	2	1×10 ⁵	AgSnO ₂	See Ambient Temp. Curve
	1100001110	Break	20					
	Inductive	Make	40	2	2	1.5×10 ⁵	AgSnO ₂	
	inductive	Break	20					
	Lamp	Make	100	2	2	1.5×10 ⁵	AgSnO₂	
		Break	20					

¹⁾ Loads mentioned in this chart is for relays with no parallel diode or Zener Diode. For those with parallel diode, Zener Diode or other components, please contact Hongfa for more technical supports.

Please also contact Hongfa if the actual application load is diffrent from what mentioned aboved.



HONGFA RELAY

ISO9001, ISO/TS16949, ISO14001, OHSAS18001, IECQ QC 080000 CERTIFIED

COIL DATA at 23°C


Nominal voltage VDC	Pick-up voltage VDC max.	Drop-out voltage VDC min.	Coil resistance x(1±10%)Ω	Parallel resistance x(1±5%)Ω	Equivalent resistance Ω	Power consumption W
12	7.2	1.2	155			0.95
12	7.2	1.2	155	1000	135	1.1


ORDERING INFORMATION								
	HFV11 /	12	-H	S	R	(XXX)		
Туре								
Coil voltage	12 : 12VDC							
Contact arrange	ement H: 1 Form	Α						
Construction S: Plastic sealed 1) Nil: Flux proofed								
Parallel coil components R: Parallel transient supression resistors NiI: Without parallel components								
Customer special code								


¹⁾ If water cleaning is required, please contact us for suggestion about suitable parts.

OUTLINE DIMENSIONS AND WIRING DIAGRAM

Unit: mm








Remark: Terminal vertical deviation tolerance is 0.3mm.

CHARACTERISTIC CURVES

Ambient temperature curve of the electrical endurance test



- 1) The minimum temperature is -40°C.
- 2) The maximum temperature is 125°C.

Disclaimer

This datasheet is for the customers' reference. All the specifications are subject to change without notice.

We could not evaluate all the performance and all the parameters for every possible application. Thus the user should be in a right position to choose the suitable product for their own application. If there is any query, please contact Hongfa for the technical service. However, it is the user's responsibility to determine which product should be used only.

© Xiamen Hongfa Electroacoustic Co., Ltd. All rights of Hongfa are reserved.