



CFPX-104

ISSUE 3; 24 JANUARY 2006

Delivery Options

Please contact our sales office for current leadtimes

Holder Style

 CFPX-104 surface mount crystals are encapsulated in a hermetically sealed ceramic package with a seam sealed metal lid.

General Specifications

- Load Capacitance (C_L): 18pF standard
- Drive Level: 0.1mW max
- Static Capacitance (Co): 7pF max
- Ageing: ±5ppm max per year @ 25°C

Packaging

 CFPX-104 surface mount crystals are available packaged individually or on tape and reel

Standard Frequency Tolerances and Stability

■ ±10ppm to ±50ppm

Operating Temperature Range

■ -10 to 60°C

Storage Temperature Range

■ -30 to 85°C

Solder Condition

 For typical soldering conditions, please see the relevant page in Application Notes


Marking


■ Frequency only

Minimum Order Information Required

- Frequency + Holder + Frequency Tolerance @ 25°C
 - + Frequency Stability + Operating Temperature Range
 - + Circuit Condition

Outline in mm





Solder pad layout



Europe Tel: +44 (0)1460 270200 Americas Tel: +1 919 941 9333 Asia Tel: +86 755 8826 5991

Fax: +1 919 941 9371 Fax: +86 755 8826 5990

Europe Tel: +44 (0)1460 270200 Fax: +44 (0)1460 72578

Website: www.cmac.com




Electrical Specification - maximum limiting values


Frequency Range	Frequency Tolerance @ 25°C ±2°C	Operating Temperature Range	Frequency Stability Available Over Operating Temperature		ESR max.	Vibration Mode
			Minimum	Maximum		
12.0 to <16.0MHz	±10ppm to ±50ppm	-10 to 60°C	±10ppm	±50ppm	60Ω	Fundamental AT cut
16.0 to 67MHz	±10ppm to ±50ppm	-10 to 60°C	±10ppm	±50ppm	40Ω	Fundamental AT cut

 $\textbf{Note: For any other frequencies} \, / \, \textbf{specification combinations, please contact our sales of fice.} \,$

Outline in mm - Tape



Outline in mm - Reel



Website: www.cmac.com

Europe Tel: +44 (0)1460 270200 Fax: +44 (0)1460 72578 Americas Tel: +1 919 941 9333 Fax: +1 919 941 9371

Asia Tel: +86 755 8826 5991 Fax: +86 755 8826 5990