



Description

- A standard 5.0V crystal oscillator in an 8-pin DIL hermetically sealed package without a standby function
- Model IQXO-22
- Model Issue number 20

Frequency Parameters

- Frequency 4.0MHz
- Frequency Tolerance @ 25°C INCLUSIVE
- Frequency Stability ±100.00ppm
- Operating Temperature Range 0.00 to 70.00°C
- Ageing ±5ppm max per year

Electrical Parameters

- Supply Voltage 5.0V
- Supply Voltage Tolerance ±0.25V
- Current Draw 20mA max

Output Details

- Output Compatability HCMOS/TTL
- Output Load 50pF max or 10TTL
- Rise and Fall time (20% - 80%) 15ns max
- Duty Cycle 45/55%

Environmental Parameters

- Shock: 981m/s², 6ms, 3 times in each of 3 mutually perpendicular planes
- Vibration: 0.76mm displacement, 10Hz-55Hz, 1min in 3 mutually perpendicular planes, duration 2hrs each plane
- Storage Temperature Range: -55 to 125°C
- Solderability: MIL-STD-202E, Method 208C

Compliance

- RoHS Status Compliant
- REACH Status Compliant

Packaging


- Pack Type: Bulk Loose in bulk pack
- Pack Size 40

- Alternative packing option available


This document is correct at the time of printing; please contact your local office for the latest version.



Outline (mm)



Test Circuit



*Inclusive of jigging and equipment capacitance

Note: Pin 1 = No connection on non standby option models

Sales Office Contact Details:


UK: +44 (0)1460 270200
Germany: +49 (0)7264 9145-0

France: +33 (0)5 34 50 91 18
USA: +1 (0) 408 455 2426

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com



Wave Form



Sales Office Contact Details:

UK: +44 (0)1460 270200

Germany: +49 (0)7264 9145-0

France: +33 (0)5 34 50 91 18

USA: +1 (0) 408 455 2426

Email: info@iqdfrequencyproducts.com

Web: www.iqdfrequencyproducts.com