

Features

- High Efficiency (Up to 84%)
- Active Power Factor Correction (Typical 0.92)
- Constant Output Voltage
- Waterproof (IP66)
- All-Round Protection: OVP, SCP, OCP
- Comply With UL8750 & EN61347 Safety Regulations
- Comply With ANSI/IEEE C62.41, Class A Operation



Description

The EUV-025SxxxPS Series operate from a 90 ~ 305 Vac input range. These units will provide up to a 48 V of output voltage and a maximum output current of 2080 mA for 25 W maximum output power. They are designed to be highly efficient and highly reliable. Features include over voltage protection, short circuit protection and over current protection.

Models

Output Voltage	Input Voltage	Max. Output Current	Max. Output Power	Typical Efficiency (1)	Power Factor		Model Number (2)
					110Vac	220Vac	
12 Vdc	90 ~ 305 Vac	2080 mA	25 W	80%	0.98	0.92	EUV-025S012PS (3)
18 Vdc	90 ~ 305 Vac	1400 mA	25 W	80%	0.98	0.92	EUV-025S018PS (3)
24 Vdc	90 ~ 305 Vac	1050 mA	25 W	81%	0.98	0.92	EUV-025S024PS (3)
36 Vdc	90 ~ 305 Vac	700 mA	25 W	83%	0.98	0.92	EUV-025S036PS (3)
48 Vdc	90 ~ 305 Vac	520 mA	25 W	84%	0.98	0.92	EUV-025S048PS (4)

Notes: (1) Measured at full load and 220 Vac input.

(2) A suffix –xxxx may be added to denote variations or modifications to the base product, where x can be any alphanumeric character or blank.

(3) Class 2 output (USR & CNR).

(4) Class 2 output (USR), Non-Class 2 output (CNR).

Input Specifications

Parameter	Min.	Typ.	Max.	Notes
Input Voltage	90 V	-	305 V	
Input Frequency	47 Hz	-	63 Hz	
Leakage Current	-	-	0.5 mA	At 277Vac 50Hz input
Input AC Current	-	-	0.32 A	Measured at full load and 100 Vac input.
	-	-	0.15 A	Measured at full load and 220 Vac input.
Inrush Current	-	-	60 A	At 230Vac input 25°C Cold Start.

Specifications are subject to changes without notice.

Output Specifications

Parameter	Min.	Typ.	Max.	Notes
Output Voltage Range				
Vo = 12 V	10.80 V	12 V	13.20 V	
Vo = 18 V	16.20 V	18 V	19.80 V	
Vo = 24 V	21.60 V	24 V	26.40 V	
Vo = 36 V	32.40 V	36 V	39.60 V	
Vo = 48 V	43.20 V	48 V	52.80 V	
Output Current Range				
Vo = 12 V	0 A	-	2.08 A	
Vo = 18 V	0 A	-	1.40 A	
Vo = 24 V	0 A	-	1.05 A	
Vo = 36 V	0 A	-	0.70 A	
Vo = 48 V	0 A	-	0.52 A	
Ripple and Noise				
Vo = 12 V	-	-	3 V	Measured by 20 MHz bandwidth oscilloscope and the output paralleled a 0.1 uF ceramic capacitor and a 10 uF electrolytic capacitor.
Vo = 18 V	-	-	3 V	
Vo = 24 V	-	-	3 V	
Vo = 36 V	-	-	4 V	
Vo = 48 V	-	-	5 V	
Line Regulation	-	-	±3%	
Load Regulation	-	-	±10%	
Turn-on Delay Time	-	2.5 S	3.0 S	Measured at 110Vac input.
	-	1.5 S	2.0 S	Measured at 220Vac input.
Output Overshoot / Undershoot	-	-	40%	When power on or off.

Note: All specifications are typical at 25 °C unless otherwise stated.

Protection Functions

Parameter	Min.	Typ.	Max.	Notes
Over Voltage Protection				
Vo = 12 V	15 V	16 V	17 V	Hiccup mode. The power supply shall be self-recovery when the fault condition is removed.
Vo = 18 V	21 V	22 V	23V	
Vo = 24 V	26 V	28 V	30 V	
Vo = 36 V	38 V	40 V	42 V	
Vo = 48 V	51 V	53 V	55 V	
Over Current Protection	1.30 Io	1.50 Io	1.7 Io	Hiccup mode. The power supply shall be self-recovery when the fault condition is removed.
Short Circuit Protection	No damage shall occur when any output operating in a short circuit condition. The power supply shall be self-recovery when the fault condition is removed.			

Specifications are subject to changes without notice.

General Specifications

Parameter	Min.	Typ.	Max.	Notes
Efficiency Vo = 12 V Vo = 18 V Vo = 24 V Vo = 36 V Vo = 48 V	78% 78% 79% 81% 82%	79% 79% 80% 82% 83%	- - - - -	Measured at full load and 110 Vac input.
Efficiency Vo = 12 V Vo = 18 V Vo = 24 V Vo = 36 V Vo = 48 V	79% 79% 80% 82% 83%	80% 80% 81% 83% 84%	- - - - -	Measured at full load and 220 Vac input.
No Load Power Dissipation	≤4 W			
MTBF	484,000 hours			For 12V output model, measured at 110Vac input, 80%Load and 25° C ambient temperature (MIL-HDBK-217F).
Life Time	79,000 hours			For 12V output model, measured at 110Vac input, 80%Load and 45° C ambient temperature
Dimensions Inches (L x W x H) Millimeters (L x W x H)	3.07 x 3.15 x 1.06 78 x 80 x 27			
Net Weight	-	200 g	-	

Note: All specifications are typical at 25 °C unless otherwise stated.

Environmental Specifications

Parameter	Min.	Typ.	Max.	Notes
Operating Temperature	-20 °C	-	+70 °C	Humidity: 10% RH to 100% RH Derating: 1.5% per °C from 50°C to 70°C
Storage Temperature	-40 °C	-	+85 °C	Humidity: 5% RH to 100% RH



Safety & EMC Compliance

Safety Category	Country	Standard
CUL	USA & Canada	UL8750, UL935, UL1012, UL1310 Class 2, CSA-C22.2 No. 107.1, CSA C22.2 NO. 223-M91 Class 2
CE	Europe	EN 61347-1, EN61347-2-13
EMI Standards	Country	Notes
EN 55015	Europe	Conducted emission Test & Radiated emission Test with 6 dB margin
EMS Standards	Notes	
EN 61000-3-2	Harmonic current emissions	
EN 61000-3-3	Voltage fluctuations & flicker	
EN 61000-4-2	Electrostatic Discharge (ESD): 8 kV air discharge, 4 kV contact discharge	
EN 61000-4-3	Radio-Frequency Electromagnetic Field Susceptibility Test-RS	
EN 61000-4-4	Electrical Fast Transient / Burst-EFT	
EN 61000-4-6	Conducted Radio Frequency Disturbances Test-CS	
EN 61000-4-8	Power Frequency Magnetic Field Test	
EN 61000-4-11	Voltage Dips	
EN 61547	Electromagnetic Immunity Requirements Applies To Lighting Equipment	


Specifications are subject to changes without notice.

ENERGY STAR Standards	Notes
ANSI/IEEE C62.41-1991	Transient Protection, power supply shall comply with Class A operation. The line transient shall consist of seven strikes of a 100 kHz ring wave, 2.5 kV level, for both common mode and differential mode.

Derating Curve



Mechanical Outline



RoHS Compliance

Our products comply with the European Directive 2002/95/EC, calling for the elimination of lead and other hazardous substances from electronic products.

Specifications are subject to changes without notice.

Revision History

Change Date	Rev.	Description of Change							
		Item	From			To			
2009-09-02	V1.1	Change MTBF and Life Time							
2009-09-11	V1.2	Change Turn-on Delay Time							
2009-12-15	A	Change Ripple and Noise							
2010-01-13	B	Modify the derating curve							
2010-04-12	C	Change the Power Factor 110Vac	0.99			0.98			
		Add Leakage Current in Input Specifications	/			Max. 0.5 mA At 277Vac 50Hz input			
		Change Inrush Current	20A			60A			
		Change Ripple and Noise	Max. 25% V _O			The max. value of every model.			
		Change Turn-on Delay Time 110Vac 220Vac	Typ. 1.7S	Max. 2.0S		Typ. 2.5S	Max. 3.0S		
		Change Output Overshoot / Undershoot	Max. 10%			Max. 40%			
		Change Over Current Protection	1.1Io	1.30 Io	1.70 Io		1.3Io	1.50 Io	1.70 Io
		Change the efficiency (110Vac) V _O = 18 V V _O = 24 V	Min. 80%	Typ. 81%		Min. 78%	Typ. 79%		
		Change the efficiency (220Vac) V _O = 18 V V _O = 24 V	Min. 81%	Typ. 82%		Min. 79%	Typ. 80%		
		Change No Load Power Dissipation	≤3 W			≤4 W			
		Standardize the tolerance in Mechanical Outline	/			/			
2010-06-04	D	Change Dimensions and Mechanical Outline (The height)	25 cm			27 cm			
2010-10-14	E	Update the Standard of the CUL	/			UL8750, UL935, UL1310 Class 2, CSA-C22.2 No. 107.1, CSA C22.2 NO. 223-M91 Class 2			
		Add Energy Star Standard	/			Comply With ANSI/IEEE C62.41, Class A Operation			
2011-1-10	F	Change Over Voltage Protection	Min.	Typ.	Max.		Min.	Typ.	Max.
		V _O = 12 V	13V	15V	18V		15V	16V	17V
		V _O = 18 V	21V	23V	24V		21V	22V	23V
		V _O = 24 V	26V	28V	30V		26V	28V	30V
		V _O = 36 V	42V	44V	46V		38V	40V	42V
V _O = 48 V	58V	59V	60V		51V	53V	55V		

Specifications are subject to changes without notice.