

## Features

- High Efficiency (Up to 87%)
- Active Power Factor Correction (Typical 0.92)
- Constant Output Current
- Lightning Protection
- Waterproof (IP66)
- Dimming Control
- All-Round Protection: OVP, SCP, OLP
- Comply With UL8750 & EN61347 Safety Regulations
- Comply With ANSI/IEEE C62.41, Class A Operation
- Comply With FCC Part15 Class B



## Description

The EUV-040SxxxPS Series operate from a 90 ~ 305 Vac input range. These units will provide up to a 48 V of output voltage and a maximum output current of 3330 mA for 40 W maximum output power. They are designed to be highly efficient and highly reliable. Features include over voltage protection, short circuit protection and over current protection.

## Models

Output Voltage	Input Voltage	Max. Output Current	Max. Output Power	Typical Efficiency (1)	Power Factor		Model Number (2)
					110Vac	220Vac	
12 Vdc	90 ~ 305 Vac	3000 mA	36 W	84%	0.98	0.92	EUV-040S012PS (3)
18 Vdc	90 ~ 305 Vac	2000 mA	36 W	85%	0.98	0.92	EUV-040S018PS (3)
24 Vdc	90 ~ 305 Vac	1500 mA	36 W	86%	0.98	0.92	EUV-040S024PS (3)
36 Vdc	90 ~ 305 Vac	1050 mA	38 W	87%	0.98	0.92	EUV-040S036PS (3)
48 Vdc	90 ~ 305 Vac	800 mA	38 W	87%	0.98	0.92	EUV-040S048PS (4)

- Notes:**
- (1) Measured at full load and 220 Vac input.
  - (2) A suffix –xxx may be added to denote variations or modifications to the base product, where x can be any alphanumeric character or blank.
  - (3) Class 2 output (USR & CNR).
  - (4) Class 2 output (USR), Non-Class 2 output (CNR).

## Input Specifications

Parameter	Min.	Typ.	Max.	Notes
Input Voltage	90 V	-	305 V	
Input Frequency	47 Hz	-	63 Hz	
Leakage Current	-	-	0.6 mA	At 277Vac 50Hz input
Input AC Current	-	-	0.48 A	Measured at full load and 100 Vac input.
	-	-	0.23 A	Measured at full load and 220 Vac input.
Inrush Current	-	-	60 A	At 230Vac input 25°C Cold Start .

Specifications are subject to changes without notice.

## Output Specifications

Parameter	Min.	Typ.	Max.	Notes
Output Voltage Range				
Vo = 12 V	10.80 V	12 V	13.20 V	
Vo = 18 V	16.20 V	18 V	19.80 V	
Vo = 24 V	21.60 V	24 V	26.40 V	
Vo = 36 V	32.40 V	36 V	39.60 V	
Vo = 48 V	43.20 V	48 V	52.80 V	
Output Current Range				
Vo = 12 V	0 A	-	3.00 A	
Vo = 18 V	0 A	-	2.00 A	
Vo = 24 V	0 A	-	1.50 A	
Vo = 36 V	0 A	-	1.05 A	
Vo = 48 V	0 A	-	0.80 A	
Ripple and Noise				
Vo = 12 V	-	-	3 V	Load conditions, Measured by 20 MHz bandwidth oscilloscope and the output paralleled a 0.1 uF ceramic capacitor and a 10 uF electrolytic capacitor.
Vo = 18 V	-	-	3 V	
Vo = 24 V	-	-	3 V	
Vo = 36 V	-	-	4 V	
Vo = 48 V	-	-	5 V	
Line Regulation	-	-	±3%	
Load Regulation	-	-	±10%	
Turn-on Delay Time	-	2.5 S	3.0 S	Measured at 110Vac input.
	-	1.5 S	2.0 S	Measured at 220Vac input.
Output Overshoot / Undershoot	-	-	40%	When power on or off.

**Note:** All specifications are typical at 25 °C unless otherwise stated.

## Protection Functions

Parameter	Min.	Typ.	Max.	Notes
Over Voltage Protection				
Vo = 12 V	14 V	15 V	18 V	Hiccup mode. The power supply shall be self-recovery when the fault condition is removed.
Vo = 18 V	20 V	21 V	23 V	
Vo = 24 V	28 V	30 V	32 V	
Vo = 36 V	39 V	41 V	43 V	
Vo = 48 V	50 V	52 V	54 V	
Over Current Protection	1.1 Io	1.5 Io	1.7 Io	Hiccup mode. The power supply shall be self-recovery when the fault condition is removed.
Short Circuit Protection	No damage shall occur when any output operating in a short circuit condition. The power supply shall be self-recovery when the fault condition is removed.			

Specifications are subject to changes without notice.

## General Specifications

Parameter	Min.	Typ.	Max.	Notes
Efficiency Vo = 12 V Vo = 18 V Vo = 24 V Vo = 36 V Vo = 48 V	82% 83% 84% 85% 85%	83% 84% 85% 86% 86%	- - - - -	Measured at full load and 110 Vac input.
Efficiency Vo = 12 V Vo = 18 V Vo = 24 V Vo = 36 V Vo = 48 V	83% 84% 85% 86% 86%	84% 85% 86% 87% 87%	- - - - -	Measured at full load and 220 Vac input.
No Load Power Dissipation	≤ 4 W			
MTBF	487,000 hours			For 12V output model, measured at 110Vac input, 80%Load and 25°C ambient temperature (MIL-HDBK-217F).
Life Time	77,000 hours			For 12V output model, measured at 110Vac input, 80%Load and 45°C ambient temperature
Dimensions Inches (L x W x H) Millimeters (L x W x H)	3.74 x 2.76 x 1.26 95 x 70 x 32			
Net Weight	-	300 g	-	

**Note:** All specifications are typical at 25 °C unless otherwise stated.

## Environmental Specifications



Parameter	Min.	Typ.	Max.	Notes
Operating Temperature	-20 °C	-	+60 °C	Humidity: 10% RH to 100% RH
Storage Temperature	-40 °C	-	+85 °C	Humidity: 5% RH to 100% RH

Specifications are subject to changes without notice.

## Safety & EMC Compliance


Safety Category	Country	Standard
CUL	USA & Canada	UL8750, UL935, UL1012, UL1310 Class 2, CSA-C22.2 No. 107.1, CSA C22.2 NO. 223-M91 Class 2
CE	Europe	EN 61347-1, EN61347-2-13
EMI Standards	Country	Standard
EN 55015	Europe	Conducted emission Test & Radiated emission Test with 6 dB margin
FCC	USA	FCC Part 15 Class B, ANSI C63.4: 2009.
EMS Standards	Notes	
EN 61000-3-2	Harmonic current emissions	
EN 61000-3-3	Voltage fluctuations & flicker	
EN 61000-4-2	Electrostatic Discharge (ESD): 8 kV air discharge, 4 kV contact discharge	
EN 61000-4-3	Radio-Frequency Electromagnetic Field Susceptibility Test-RS	
EN 61000-4-4	Electrical Fast Transient / Burst-EFT	
EN 61000-4-6	Conducted Radio Frequency Disturbances Test-CS	
EN 61000-4-8	Power Frequency Magnetic Field Test	
EN 61000-4-11	Voltage Dips	
EN 61547	Electromagnetic Immunity Requirements Applies To Lighting Equipment	
ENERGY STAR Standards	Notes	
ANSI/IEEE C62.41-1991	Transient Protection, power supply shall comply with Class A operation. The line transient shall consist of seven strikes of a 100 kHz ring wave, 2.5 kV level, for both common mode and differential mode.	

## Derating Curve



Specifications are subject to changes without notice.

## Mechanical Outline



## RoHS Compliance

Our products comply with the European Directive 2002/95/EC, calling for the elimination of lead and other hazardous substances from electronic products.

Specifications are subject to changes without notice.

## Revision History

Change Date	Rev.	Description of Change		
		Item	From	To
2009-09-02	V2.1	Change MTBF and Life Time		
2009-09-11	V2.2	Change Turn-on Delay Time		
2009-12-03	A	Modify the output current range		
2010-04-12	B	Change the Power Factor 110Vac	0.99	0.98
		Add Leakage Current in Input Specifications	/	Max. 0.6 mA At 277Vac 50Hz input
		Change Inrush Current	20A	60A
		Change Ripple and Noise	Max. 25% V <sub>o</sub>	The max. value of every model.
		Change Turn-on Delay Time 110Vac 220Vac	Typ. 1.7S Max. 2.0S 0.7S 1.0S	Typ. 2.5S Max. 3.0S 1.5S 2.0S
		Change Output Overshoot / Undershoot	Max. 10%	Max. 40%
		Change Over Current Protection	1.1I <sub>o</sub> 1.30 I <sub>o</sub> 1.70 I <sub>o</sub>	1.3I <sub>o</sub> 1.50 I <sub>o</sub> 1.70 I <sub>o</sub>
		Change No Load Power Dissipation	≤ 3 W	≤ 4 W
		Change Operating Temperature	Max. +70 °C	Max. +60 °C
		Change the Max. Ambient Temperature in Derating Curve	+70 °C	+60 °C
		Standardize the tolerance in Mechanical Outline	/	/
2010-07-30	C	Add Energy Star Standard	/	Comply With ANSI/IEEE C62.41, Class A Operation
2010-10-14	D	Update the Standard of the CUL	/	UL8750, UL935, UL1012, UL1310 Class 2, CSA-C22.2 No. 107.1, CSA C22.2 NO. 223-M91 Class 2
		Add FCC Part15 Class B	/	FCC Part 15 Class B, ANSI C63.4: 2009.

Specifications are subject to changes without notice.