



Description

- Industry standard leaded package
Resistance welded, hermetically sealed in an inert atmosphere, glass to metal seals on leads
- Model HC49
- Model Issue number 15

Frequency Parameters

- Frequency 1.84320MHz
- Frequency Tolerance @ 25°C ±20.00ppm
- Frequency Stability ±50.00ppm
- Operating Temperature Range -10.00 to 60.00°C
- Overtone Order Fundamental
- Ageing ±3ppm typical per year

Electrical Parameters

- Load Capacitance (C_L) 30.00pF
- Shunt Capacitance (C₀) 7pF max
- Drive Level 1mW max
- ESR 800Ω max

Environmental Parameters

- Shock: 981m/s², 6ms, 3 times in each of 3 mutually perpendicular planes
- Vibration: 10Hz-60Hz, 0.75mm amplitude, 60Hz-500Hz, 98.1m/s², 30mins in 3 mutually perpendicular planes
- Storage Temperature Range: -55 to 125°C


Compliance

- RoHS Status Compliant
- REACH Status Compliant


Packaging

- Pack Type: Bulk Loose in bulk pack
- Pack Size 100
- Alternative packing option available

This document is correct at the time of printing; please contact your local office for the latest version.



Outline (mm)



Sales Office Contact Details:

UK: +44 (0)1460 270200
Germany: +49 (0)7264 9145-0

France: +33 (0)5 34 50 91 18
USA: +1 (0) 408 455 2426

Email: info@iqdfrequencyproducts.com
Web: www.iqdfrequencyproducts.com