

CFPS-302, 303 CLOCK OSCILLATORS

ISSUE 5; 20 NOVEMBER 2008 - RoHS 2002/95/EC

Description

- 8-pin DIL compatible resistance welded enclosure, hermetically sealed with glass to metal seal

Fast Make Capability

- Please see CFPP-303 series Programmable Oscillators for nearest equivalent fast make parts

Package Outline

- 8-pin DIL

Frequency Range

- 500kHz to 125MHz

Output Compatibility & Load

- HCMOS/LSTTL
- Drive Capability 15pF max or 10LSTTL
- Non tri-state (CFPS-302)
- Tri-state (CFPS-303)

Frequency Stabilities

- $\pm 25\text{ppm}$, $\pm 50\text{ppm}$, $\pm 100\text{ppm}$
(over operating temperature range)

Operating Temperature Range

- 0 to 70°C (CFPS-302, -303)
- 40 to 85°C (CFPS-302I, -303I)

Storage Temperature Range

- 55 to 125°C

Tri-state Operation (CFPS-303, -303I)

- No connection or Logic '1' to pin 1 enables oscillator output
- Logic '0' to pin 1 disables oscillator output; when disabled the oscillator output goes to the high impedance state
- Maximum 'pull-down' resistance required to disable output = 20k Ω
- Disable current 50 μA typical


Environmental

- Terminal Strength: 0.91kg max force perpendicular to top and bottom
- Hermetic Seal: not to exceed 1×10^{-8} mBar litres of Helium leakage
- Solderability: MIL-STD-202E, Method 208C
- Vibration: 10 to 55Hz 0.76mm displacement, sweep 60 seconds, duration 2 hours
- Rapid Change of Temperature over Operating Temperature Range: 10 cycles
- Shock: 981m/s² for 6ms, three shocks in each direction along the three mutually perpendicular planes


Marking Includes

- Model Number + Operating Temperature Code (if applicable) + Frequency Stability Code + Frequency + Date Code


Outline (mm)



- Pin Connections
- N/C or Enable/Disable.
 4. GND
 5. Output
 8. +Vs



Output Waveform



Packaging

- Bulk

Minimum Order Information Required

- Frequency + Model Number + Operating Temperature (if applicable) + Frequency Stability

Electrical Specifications - maximum limiting values


Frequency Range	Frequency Stability	Supply Voltage	Supply Current	Rise Time (tr)	Fall Time (tf)	Duty Cycle	Model Number
500.0kHz to <20.0MHz	±25ppm, ±50ppm, ±100ppm	3.3V ±0.33V	10mA	10ns	10ns	40/60%	CFPS-302, 302I, 303, 303I
20.0MHz to <25.0MHz			20mA				
25.0MHz to 40.0MHz				6ns	6ns		
>40.0MHz to <70.0MHz			25mA				
70.0MHz to <125.0MHz			30mA	3ns	3ns		

Ordering Example 22.0MHz CFPS-302 B
 Frequency _____
 Model number: -302 = Non tri-state, -303 = Tri-state
 Operating Temperature Code: I = -40 to 85°C Not applicable for 0 to 70°C _____
 Frequency Stability: A = ±25ppm, B = ±50ppm, C = ±100ppm _____

Please note that the rise and fall times listed are the maximum values we specify to cover various frequency breaks. In practice the actual values are generally lower depending upon the spot frequency chosen. For typical values please contact our sales office.

CLOCK OSCILLATORS

Test Circuit



*Inclusive of jigging and equipment capacitance

Note: Pin 1 = No connection on non tri-state models