

MOC8101X,MOC8102X,MOC8103X,MOC8104X,MOC8105X
MOC8101, MOC8102, MOC8103,MOC8104,MOC8105



**NON-BASE LEAD
OPTICALLY COUPLED ISOLATOR
PHOTOTRANSISTOR OUTPUT**

APPROVALS

- UL recognised, File No. E91231
- 'X' SPECIFICATION APPROVALS
- VDE 0884 in 3 available lead forms : -
 - STD
 - G form
 - SMD approved to CECC 00802
- Certified to EN60950 by the following Test Bodies :-
 - Nemko - Certificate No. P96101299
 - Fimko - Registration No. 190469-01..22
 - Semko - Reference No. 9620076 01
 - Demko - Reference No. 305567

DESCRIPTION



The MOC8101, MOC8102, MOC8103, MOC8104, MOC8105 series of optically coupled isolators consist of infrared light emitting diode and NPN silicon photo transistor in a standard 6 pin dual in line plastic package with the base pin unconnected.

FEATURES

- Options :-
 - 10mm lead spread - add G after part no.
 - Surface mount - add SM after part no.
 - Tape&reel - add SMT&R after part no.
- High Isolation Voltage (5.3kV_{RMS}, 7.5kV_{PK})
- Base pin unconnected for improved noise immunity in high EMI environment

APPLICATIONS

- DC motor controllers
- Industrial systems controllers
- Signal transmission between systems of different potentials and impedances



**ABSOLUTE MAXIMUM RATINGS
(25°C unless otherwise specified)**

Storage Temperature	-55°C to + 150°C
Operating Temperature	-55°C to + 100°C
Lead Soldering Temperature (1/16 inch (1.6mm) from case for 10 secs)	260°C

INPUT DIODE

Forward Current	60mA
Reverse Voltage	6V
Power Dissipation	105mW

OUTPUT TRANSISTOR

Collector-emitter Voltage BV _{CEO}	30V
Emitter-collector Voltage BV _{ECO}	6V
Power Dissipation	160mW

POWER DISSIPATION

Total Power Dissipation	200mW
(derate linearly 2.67mW/°C above 25°C)	

ISOCOM COMPONENTS LTD

Unit 25B, Park View Road West,
Park View Industrial Estate, Brenda Road
Hartlepool, Cleveland, TS25 1YD
Tel: (01429) 863609 Fax :(01429) 863581

ISOCOM INC

1024 S. Greenville Ave, Suite 240,
Allen, TX 75002 USA
Tel:(214)495-0755 Fax:(214)495-0901
e-mail info@isocom.com
<http://www.isocom.com>

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ Unless otherwise noted)


PARAMETER		MIN	TYP	MAX	UNITS	TEST CONDITION
Input	Forward Voltage (V_F) Reverse Voltage (V_R) Reverse Current (I_R)	1.0 6	1.15	1.5 10	V V μA	$I_F = 10\text{mA}$ $I_R = 10\mu\text{A}$ $V_R = 6\text{V}$
Output	Collector-emitter Breakdown (BV_{CEO}) (Note 2) Emitter-collector Breakdown (BV_{ECO}) Collector-emitter Dark Current (I_{CEO})	30			V nA	$I_C = 1\text{mA}$ $I_E = 100\mu\text{A}$ $V_{CE} = 10\text{V}$
Coupled	Output Collector Current (I_C) (Note 3) MOC8101 MOC8102 MOC8103 MOC8104 MOC8105 Collector-emitter Saturation Voltage $V_{CE(SAT)}$ Input to Output Isolation Voltage V_{ISO} Input-output Isolation Resistance R_{ISO} Turn-on Time t_{on} Turn-off Time t_{off} Output Rise Time t_r Output Fall Time t_f	5.0 7.3 10.8 16 6.5 5300 7500 5×10^{10}		8.0 11.7 17.3 25.6 13.3 0.15 7.5 5.7 3.2 4.7	mA mA mA mA mA V_{RMS} V_{PK} Ω μs μs μs μs	10mA I_F , 10V V_{CE} 10mA I_F , 10V V_{CE} 10mA I_F , 10V V_{CE} 10mA I_F , 10V V_{CE} 10mA I_F , 10V V_{CE} See note 1 See note 1 $V_{IO} = 500\text{V}$ (note 1) $V_{CC} = 10\text{V}$, $I_C = 2\text{mA}$, $R_L = 100\Omega$

Note 1 Measured with input leads shorted together and output leads shorted together.


Note 2 Special Selections are available on request. Please consult the factory.

Note 3 Production testing - limits verified with pulse test


Collector Power Dissipation vs. Ambient Temperature




Collector Current vs. Collector-emitter Voltage




Forward Current vs. Ambient Temperature



Current Transfer Ratio vs. Forward Current



Relative Current Transfer Ratio vs. Ambient Temperature



Collector-emitter Saturation Voltage vs. Ambient Temperature

