



2.5mm
(.098") pitch



This 2.5mm (.098") pitch connector is used to interconnect printed circuit boards. It easily resists distortion during mating, thus ensuring reliable contact, even under adverse conditions.



Features

• High contact pressure

This vibration-resistant, double-beam contact provides high contact pressure and thus eliminates contact bounce during vibration or shock.

• Box-shaped shroud

The four-sided shrouded header prevents the socket housing from being misinserted or distorted during mating. The slots in the header's shroud fit snugly into the receptacle housing, guaranteeing a vibration-proof coupling. And the serrated square posts are pressure-fit to prevent flux from entering during soldering.

• Secure locking on printed circuit boards

The solder tails of both the plug and receptacle have board retention features. This ensures secure mounting and accurate location during soldering.

• Vertical, horizontal and parallel mounting

Both top-entry and side-entry receptacles and shrouded headers are available, thus allowing printed circuit boards to be connected vertically, horizontally or parallel to the mother board.


• Interchangeability

The shrouded header is interchangeable with the XH wire-to-board crimp style connectors, the NR, NRD and BR wire-to-board insulation displacement connectors.

Specifications

- Current rating: 3.0A AC, DC
 - Voltage rating: 250V AC, DC
 - Temperature range: -25°C to +85°C
(including temperature rise in applying electrical current)
 - Contact resistance: Initial value/10mΩ max.
After environmental testing/20mΩ max.
 - Insulation resistance: 1,000MΩ min.
 - Withstanding voltage: 1,000V AC/minute
 - Applicable PC board thickness: 1.6mm(.063")
- * Contact JST for details.

Standards


 Recognized file No. E60389

 Certified file No. LR20812

 File No. R75085 (conforms to DIN/VDE 0627)

JQ CONNECTOR

Receptacle



Circuits	Model No.		Dimensions mm(in.)			Q'ty / box	
	Top entry type	Side entry type	A	B	C	Top entry type	Side entry type
3	03JQ-BT	03JQ-ST	5.0(.197)	10.0(.394)	8.2(.323)	500	500
4	04JQ-BT	04JQ-ST	7.5(.295)	12.5(.492)	10.7(.421)	500	500
5	05JQ-BT	05JQ-ST	10.0(.394)	15.0(.591)	13.2(.520)	500	500
6	06JQ-BT	06JQ-ST	12.5(.492)	17.5(.689)	15.7(.618)	500	500
7	07JQ-BT	07JQ-ST	15.0(.591)	20.0(.787)	18.2(.717)	250	250
8	08JQ-BT	08JQ-ST	17.5(.689)	22.5(.886)	20.7(.815)	200	250
9	09JQ-BT	09JQ-ST	20.0(.787)	25.0(.984)	23.2(.913)	200	250
10	10JQ-BT	10JQ-ST	22.5(.886)	27.5(1.083)	25.7(1.012)	250	250
11	11JQ-BT	11JQ-ST	25.0(.984)	30.0(1.181)	28.2(1.110)	250	250
12	12JQ-BT	12JQ-ST	27.5(1.083)	32.5(1.280)	30.7(1.209)	200	200
13	13JQ-BT	13JQ-ST	30.0(1.181)	35.0(1.387)	33.2(1.307)	200	200
15	15JQ-BT	15JQ-ST	35.0(1.378)	40.0(1.574)	38.2(1.504)	100	100

Material and Finish


Contact: Phosphor bronze, tin-plated
Housing: Nylon 66, UL94V-0, natural (white)

Note: 13JQ-BT, 13JQ-ST, 15JQ-BT & 15JQ-ST are not TÜV approved.

Shrouded header

The shrouded headers are interchangeable with the XH crimp style connectors, the NR, the NRD and the BR insulation displacement connectors (see pages 27, 152, 154 & 150).

PC board layout (viewed from soldering side)



Note:

1. Tolerances are non-cumulative: $\pm 0.05\text{mm}(\pm .002")$ for all centers.
2. Hole dimensions differ according to the kind of PC board and piercing method. The dimensions above should serve as a guideline. Contact JST for details.

		Receptacle	
		Top entry type	Side entry type
Shrouded header	Top entry type		
	Side entry type S()B-XH-A-1		