

IT FIT 180/220-240/24

ICUTRONIC FIT 24V | Constant voltage ECG for LED modules



Product family features

- Wide Ta range -20 – +50 °C
- 24 V constant output voltage
- Output power up to 250 W
- High efficiency up to 93% (depend on different wattage)
- PF >0.98
- Screw terminal
- Suitable for Class I/II luminaires
- Build-in and independent installation
- 5 years guarantee*
- Cable clamp integrated
- SELV
- Overload protection
- Overtemperature protection
- Mains voltage: 220 – 240 VAC
- Lifetime: up to 50,000 h (temperature at max. t_c)
- Short circuit protection

Product family benefits

- Class II design for wide application
- Well design for Flex and Signage
- Excellent price/quality/watt ratio

Areas of application

- Hospitality – decorative lighting, night light
- Residential – cove lighting, under cabinet lighting
- Shops – decorative lighting, shelf lighting
- Restaurants – decorative lighting

Technical data

Electrical data

Nominal input voltage	220...240 V
Mains frequency	50/60 Hz
Input voltage AC	198...264 V
Power factor λ	0.98
Efficiency in full-load	92 % ¹⁾
Device power loss	17.8 W ²⁾
Inrush current	59 A ³⁾
Max. ECG no. on circuit breaker 10 A (B)	2
Max. ECG no. on circuit breaker 10 A (C)	4
Max. ECG no. on circuit breaker 16 A (B)	5
Max. ECG no. on circuit breaker 16 A (C)	7
Max. ECG no. on circuit breaker 25 A (B)	8
Surge capability (L-N)	2 kV
Nominal output voltage	24 V
Nominal output power	180 W
Maximum output power	180 W
Output ripple Voltage (100 Hz)	< 3 %

¹⁾ at 230 V, 50 Hz

²⁾ Full load, 230 Vac, 50Hz / 60Hz

³⁾ $t_{width} = 216 \mu s$ (measured at 50 % I_{peak})

Dimensions & weight



Mounting hole spacing, length	291 mm
Product weight	543.00 g
Cable cross-section, input side	0.75...1.5 mm ²
Cable cross-section, output side	0.75...1.5 mm ²

Product datasheet

Wire preparation length, input side	5.0 mm
Length	324.0 mm
Width	40.0 mm
Height	30.0 mm

Colors & materials

Casing material	Plastic
-----------------	---------

Temperatures & operating conditions

Ambient temperature range	-20...+50 °C
Maximum temperature at tc test point	90 °C
Max.housing temperature in case of fault	110 °C
Temperature range at storage	-40...+85 °C
Permitted rel. humidity during operation	5...85 % ¹⁾

¹⁾ Non-condensing

Lifespan

ECG lifetime	50000 h ¹⁾
--------------	-----------------------

¹⁾ At maximum $T_c = 90^\circ\text{C}$ / 10% failure rate

Capabilities

Dimmable	No
Dimming interface	-
Dimming range	-
Overheating protection	Yes
Overload protection	Yes
Short-circuit protection	Yes
Intended for no-load operation	No
Suitable for fixtures with prot. class	I / II
No-load proof	Yes
Number of channels	1

Certificates & standards

Approval marks – approval	CE / CCC / RCM ¹⁾
Standards	Acc. to EN 61347-1/Acc. to EN 61347-2-13/Acc. to EN 62384/Acc. to EN 61000-3-2/Acc. to EN 61000-3-3/Acc. to EN 61547/Acc. to IEC 61347-1/Acc. to IEC 61347-2-13/Acc. to IEC 61000-3-2/Acc. to IEC 61000-3-3/Acc. to IEC 62384/Acc. to IEC 61547
Type of protection	IP20

¹⁾ In preparation

Product datasheet



Logistical data

Commodity code	850440839000
----------------	--------------

Environmental information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	14-04-2022
Primary Article Identifier	4062172168069
Candidate List Substance 1	Lead
CAS No. of substance 1	7439-92-1
Declaration No. in SCIP database	In work

Download Data

File	
	Certificates IT FIT 24V UK CE 4281065 210121
	Declarations of conformity IT FIT CE 4242539 01 190121

Ecodesign regulation information:

Intended for use with LED modules.
The forward voltage of the LED light source shall be within the defined operating window of the control gear in all operating conditions including dimming if applicable.

Separate control gear and light sources must be disposed of at certified disposal companies in accordance with Directive 2012/19/EU (WEEE) in the EU and with Waste Electrical and Electronic Equipment (WEEE) Regulations 2013 in the UK. For this purpose, collection points for recycling centres and take-back systems (CRSO) are available from retailers or private disposal companies, which accept separate control gear and light sources free of charge. In this way, raw materials are conserved and materials are recycled.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4062172168069	IT FIT 180/220-240/24	Shipping carton box 20	485 mm x 340 mm x 105 mm	17.31 dm ³	11694.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Product datasheet

References / Links

* For more information on the multi-level guarantee and the terms and conditions of the guarantee visit

▶ www.osram.com/system-guarantee

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.