



Date: 10/23/2008

MAIDA STYLE NUMBER D69ZOV321RA90

MAIDA ITEM NUMBER 01-0743

VARISTOR SPEC SHEET

Electrical Specifications


Continuous AC Voltage	320	VAC
Continuous DC Voltage	420	VDC
Maximum DC Leakage @ 420 VDC	200	uA
Low Varistor Voltage Limit	453	VDC
High Varistor Voltage Limit	553	VDC
Nominal Varistor Voltage	503	VDC
Current for Varistor Voltage	1	mA
Maximum Clamp Voltage	850	V
Maximum Clamp Voltage Test Current	50	A
Peak Current Rating (1 Pulse)	6000	A
Peak Current Rating (2 Pulse)	4500	A
Energy Rating (8X20us)	190	J
Energy Rating (10X1000us)	190	J
Typical Capacitance	520	pF
Impulse Response Time	< 50	ns
Minimum Hipot of Coating	2500	VDC
Minimum I.R. of Coating	1000	MΩ

Physical Specifications

Lead Style	082J1
X Nominal	0.3 in.
X Tolerance	0.04 in.
Lead Length Nominal	1.00 in.
Lead Length Tolerance	min. in.
Y Nominal	0.151 in.
Y Tolerance	0.03 in.
d Nominal	0.032 in.
Wire Gauge	20 AWG
Minimum Marking	Z321-90UL
Nominal Disk Size	14 mm
D Maximum	0.65 in.
T Maximum	0.276 in.
H Maximum	0.775 in.

Thermal Specifications

Minimum Operating Temperature	-40	°C
Maximum Operating Temperature	85	°C
Varistor Voltage Temperature Coeff	-0.05	%/°C
Minimum Storage Temperature	-50	°C
Maximum Storage Temperature	125	°C
Current/Energy Derating Above 85°C	-2.5	%/°C



* Contact Maida for a more detailed configuration drawing.

Notes

Lead Free - Complies with RoHS

Safety Agency Recognitions

UL 1449 File Number	E86730
UL 1414 File Number	E38785
CSA File Number	LR33468
VDE File Number	40017480
SEV File Number	96.7 70250.01



DEVELOPMENT COMPANY

P.O. Box 3529

Hampton, Virginia 23663

(757) 723-0785 Fax (757) 722-1194