



Spec No. :DS30-2021-0030 Effective Date: 04/02/2022

Revision: -

LITE-ON DCC

RELEASE

BNS-OD-FC001/A4



LED DISPLAY

LTP-757KG-01

Rev	<u>Description</u>	<u>By</u>	<u>Date</u> DD/MM/YYYY
01	Preliminary Spec	Supornrat K.	17/03/2021
	Above data for PD and Customer tracking	g only	
-	NPPR Received and Upload to system	Supornrat K.	14/12/2021



1. Description

The LTP-757KG-01 is a 0.7-inch (17.22 mm) matrix height 5 x 7 dot matrix display This device utilizes AllnGaP Green LED chips, which are made from AllnGaP on a non-transparent GaAs substrate. The display has gray face and white dots.

1.1 Features

- 0.7-inch (17.22 mm) DIGIT HEIGHT
- CONTINUOUS UNIFORM SEGMENTS
- LOW POWER REQUIREMENT
- EXCELLENT CHARACTERS APPEARANCE
- HIGH BRIGHTNESS & HIGH CONTRAST
- WIDE VIEWING ANGLE
- SOLID STATE RELIABILITY
- CATEGORIZED FOR LUMINOUS INTENSITY

LEAD-FREE PACKAGE (ACCORDING TO ROHS)


1.2 Device

Part No	Description
Green	Cathode Column
LTP-757KG-01	Anode Row

Part No.: LTP-757KG-0 BNS-OD-FC002/A4



2. Package Dimensions




Notes:

- 1. All dimensions are in millimeters. Tolerances are ± 0.25 mm (0.01") unless otherwise noted.
- 2. Pin tip's shift tolerance is \pm 0.4 mm.
- 3. Foreign material on segment ≤ 10 mil.
- 4. Ink contamination (surface) \leq 20mil.
- 5. Bubble in segment ≤ 10 mil.
- 6. Bending \leq 1% of reflector length.
- 7. Recommend the best PCB hole: Diameter 1.0 mm.



3. Internal Circuit Diagram



4. Pin Connection

No	Connection
1	CATHODE COLUMN 1
2	ANODE ROW 3
3	CATHODE COLUMN 2
4	ANODE ROW 5
5	ANODE ROW 6
6	ANODE ROW 7
7	CATHODE COLUMN 4
8	CATHODE COLUMN 5
9	ANODE ROW 4
10	CATHODE COLUMN 3
11	ANODE ROW 2
12	ANODE ROW 1



5. Rating and Characteristics

5.1 Absolute Maximum Rating at Ta=25℃

Maximum Rating	Unit	
70	mW	
60	mA	
25	mA	
0.28	mA/℃	
-35℃ to +105℃		
-35℃ to +105℃		
	70 60 25 0.28 -35℃ to +105℃	

Solder Condition: 1/16 inch below seating plane for within 5 second at 260° C or temperature of unit (d uring assembly) not over max. temperature rating above

5.2 Electrical / Optical Characteristics at Ta=25℃

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Test Condition
Average Luminous Intensity Per DP	IV	3901	7800		μcd	IP=80mA, 1/16Duty
Peak Emission Wavelength	λр		571		nm	IF=5mA
Spectral Line Half-Width	Δλ		15		nm	IF=5mA
Dominant Wavelength	λd		572		nm	IF=5mA
Forward Voltage Per Chip	VF		2.10	2.60	V	IF=5mA
Reverse Current Per Segment (*2)	IR			100	μΑ	VR=5V
Luminous Intensity Matching Ratio (Similar Light Area)	IV-m			2:1		IP=80mA, 1/16Duty
Dominant Wavelength Matching Delta (Similar Light Area)	Δλd			4	nm	IF=5mA


Notes:

- 1. Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commission International De L'Eclariage) eye-response curve.
- 2. Reverse voltage is only for IR test. It cannot continue to operate at this situation.
- 3. Cross talk specification $\leq 2.5\%$.




5.3 Typical Electrical / Optical Characteristics Curves

(25℃ Ambient Temperature Unless Otherwise Noted)



KG 160 140 ORWARD CURRENT, If (mA) 120 100 80 60 40 20 0 0 1.0 4.0 5.0 3.0 2.0 FORWARD VOLTAGE, Vf (Volts)

Fig2. Forward Current vs. Forward Voltage









Fig3. Relative Luminous Intensity vs. DC Forward Current



vs. Duty Cycle %



6. Reliability Test

Classification	Test Item		Test Condition	Reference Standard	
Endurance Test	Operation Life	RTOL	Ta=Under Room Temperature	MIL-STD-750D:1026 (1995)	
			IF=As per data sheet maximum Rating	MIL-STD-883E:1005 (1996)	
			* Test Time= 1000Hrs (-24Hrs, +72Hrs)	JIS C 7021: B-1 (1982)	
	High Temperature High	THS	Ta= 65±5°C	MIL-STD-202G:103B (2002)	
	Humidity Storage		RH=90 ~ 95%	JIS C 7021: B-11 (1982)	
			Test Time=500Hrs (±2Hrs)		
	High Temperature	HTS	Ta= 105±5°C	MIL-STD-883E:1008 (1996)	
	Storage		Test Time=1000Hrs (-24Hrs, +72Hrs)	JIS C 7021: B-10 (1982)	
	Low Temperature	LTS	Ta= -35±5°C	JIS C 7021: B-12 (1982)	
	Storage		Test Time=1000Hrs (-24Hrs, +72Hrs)		
Environmental Test	Temperturre Cycling	TC	105°C ~ 25°C ~ -35°C ~ 25°C	MIL-STD-202G:107D (2002)	
			30mins ~ 5mins ~ 30mins ~ 5mins	MIL-STD-750D:1051 (1995)	
			30 Cycles	MIL-STD-883E:1010 (1996)	
				JIS C 7021: A-4 (1982)	
	Thermal Shock	TS	105 ±5°C ~ -35 ±5°C	MIL-STD-202G:107D (2002)	
			30mins ~ 30mins	MIL-STD-750D:1051 (1995)	
			30 Cycles	MIL-STD-883E:1011 (1996)	
	Solder Resistance	SR	T.Sol=260 ±5°C	MIL-STD-202G:210A (2002)	
			Dwell Time= 10 ±1 secs	MIL-STD-750D:2031 (1995)	
			(For solder pin only)	JIS C 7021: A-1 (1982)	
	Solderability	SA	T.Sol=245 ±5°C	MIL-STD-202G:208D (2002)	
			Dwell Time= 5 ±1 secs	MIL-STD-750D:2026 (1995)	
			(For solder pin only)	MIL-STD-883E:2003 (1996)	
				JIS C 7021: A-2 (1982)	

^{* (}Check point: 0th, 168th, 500th, 800th, 1000th Hrs)
Follow as : QS-00TP-RELBE-0001 Reliability Test Conditions




7. Soldering Profile

7.1 Auto Soldering



LITE-ON TECHNOLOGY CORPORATION

** Flow(=Wave soldering) condition with temperature for Pb free Soldering



7.2 Manual Soldering

Solder Conditions: 1/16 inch below seating plane for within 5 seconds at 350℃ (not over 380℃ max), or temperature of unit (during assembly) not over max. Temperature rating above.



8. CAUTIONS

8.1. Application

- The display described here are intended to be used for ordinary electronic equipment (such as office equipment, communication equipment and household applications). Consult Liteon's Sales in advance for information on applications in which exceptional reliability is required, particularly when the failure or malfunction of the display may directly jeopardize life or health (such as in aviation, transportation, traffic control equipment, medical and life support systems, and safety devices).
- When using this LED display, please make sure absolute maximum ratings and the instructions for using outlined in these specification sheets. LITEON will not be responsible for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- Excess driving current and/or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.
- The driving circuit should be designed to protect the LEDs inside the display against reverse voltages and transient voltage spikes when the circuit is powered up or shut down.
- Constant current driving is recommended to ensure consistent performance.
- Circuit design must cater to the whole range of forward voltage (VF) of the LEDs inside the display to ensure the intended drive current can always be achieved.
- The safe operating current should be chosen after considering the maximum ambient temperature of the operating environment.
- Reverse bias should be avoided, as it could cause metal migration, leading to an increase in leakage current or causing a short circuit.
- Avoid rapid changes in ambient temperatures, especially in high-humidity environments, because they cause condensation on the LED/LED display.
- Do not use unsuitable tool or assembly method to have abnormal force on display body cause damage.
- Printing/pattern film is using pressure sensitive glue to stick on LED display surface, not recommend to let LED display pattern film side close contact with front panel/cover, since the printing/pattern film may shift or moved from original position by external force.



8.2. Storage conditions

LED Display standard storage condition.

Product in the original packaging material state is recommended storage conditions.

Temperature Condition: 5°C~30°C Humidity Condition: Below 60%RH

If the storage conditions do not meet specification standards, the LED display pins may become oxidized requiring re-plating and re-sorting before use. Suggest customers consume display as soon as possible and avoid long-term storage of large inventories.

LED SMD Display standard storage condition

When the package is in factory original sealed bag.

Temperature Condition: 5°C~30°C Humidity Condition: Below 60%RH

When the package is opened and not in factory original sealed bag.

Temperature Condition: $5^{\circ}\text{C} \sim 30^{\circ}\text{C}$ Humidity Condition: Below 60°RH

Storage time: Within 168Hr (MSL as level 3)

If the storage conditions do not meet specification standards, the LED display pins, or soldering pads may become oxidized requiring re-plating and re-sorting before use. Suggest customers consume display as soon as possible and avoid long-term storage of large inventories.

- Recommend to baking the LEDs at 60 °C for 24hrs before soldering process if the LED SMD Display were unpacked more than 168hrs.
- The Displays recommend to used within 12 months from shipping date.
- The Displays should not be exposed to an environment where high level of moisture or corrosive gases are present.
- LED display pins and soldering pads are plated with gold, tin, or other metals. Under long-term exposure to open air, the exposed pins and pads may become oxidized causing poor solderability. Therefore, opened but unused parts must be stored in sealed containers or controlled environment. Suggest to store unused SMD Display parts in the original moisture barrier bag and sealed.
- Moisture control for components already mounted on PCB If the PCB will not undergo additional reflow soldering or high-temperature processes, then no special treatment is required for the mounted moisture-sensitive SMD components. If the PCB will undergo multiple reflow soldering or other high-temperature processes, including rework, then the SMD component's cumulative exposure time until the final high-temperature process must be controlled to within the specified time limit.



8.3. Cleaning

Do not use unspecified chemical liquid to clean display they could harm the package.

8.4. ESD (Electrostatic Discharge)

Static Electricity or power surge will damage LED inside the display.

Suggestions to prevent ESD damage:

- Use of a conductive wrist band or anti-electrostatic glove when handling these LED displays.
- All devices, equipment, and machinery, working tables, storage racks, etc. must be properly grounded.
- Use ion blower to neutralize the static charge which might have built up on surface of the LED display plastic as a result of friction between LED display during storage and handling.

8.5. Terms and conditions for the usage of this document

- The appearance and specifications of the product may be modified for improvement without prior notice.
- The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, LITEON will not be responsible for any subsequent issues.
- Excess driving current and/or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.
- The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with LITEON representative for further assistance.
- The contents and information of this document may not be reproduced or re-transmitted without permission by LITEON.
- When any special process such as potting is required for LED display assembly, please consult with LITEON representative before proceeding.
- Over-current-proof
 Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out