



Date: 11/14/2008

MAIDA STYLE NUMBER D7580ZOV551RA960

MAIDA ITEM NUMBER 01-1081

VARISTOR SPEC SHEET

Electrical Specifications


Continuous AC Voltage	550	VAC
Continuous DC Voltage	700	VDC
Maximum DC Leakage @ Rated VDC	200	uA
Low Varistor Voltage Limit	778	VDC
High Varistor Voltage Limit	950	VDC
Nominal Varistor Voltage	864	VDC
Current for Varistor Voltage	1	mA
Maximum Clamp Voltage	1400	V
Maximum Clamp Voltage Test Current	300	A
Peak Current Rating (1 Pulse)	40000	A
Peak Current Rating (2 Pulse)	32000	A
Energy Rating (8X20us)	960	J
Energy Rating (10X1000us)	960	J
Typical Capacitance	1300	pF
Impulse Response Time	< 50	ns
Minimum Hipot of Coating	2500	VDC
Minimum I.R. of Coating	1000	MΩ

Physical Specifications

Lead Style	165
X Nominal	1 in.
X Tolerance	0.02 in.
Lead Length Nominal	in.
Lead Length Tolerance	in.
Y Nominal	0.225 in.
Y Tolerance	0.04 in.
d Nominal	0.02 in.
Wire Gauge	24 AWG
Minimum Marking	Z551-960UL
Nominal Disk Size	40 mm
D Maximum	1.89 in.
T Maximum	0.373 in.
H Maximum	2.37 in.

Thermal Specifications

Minimum Operating Temperature	-40	°C
Maximum Operating Temperature	85	°C
Varistor Voltage Temperature Coeff	-0.05	%/°C
Minimum Storage Temperature	-50	°C
Maximum Storage Temperature	125	°C
Current/Energy Derating Above 85°C	-2.5	%/°C



* Contact Maida for a more detailed configuration drawing.

Notes

Lead Free - Complies with RoHS



DEVELOPMENT COMPANY

P.O. Box 3529

Hampton, Virginia 23663

(757) 723-0785 Fax (757) 722-1194

Safety Agency Recognitions

UL 1449 File Number	E86730
UL 1414 File Number	E38785
CSA File Number	LR33468
VDE File Number	
SEV File Number	